

1. Model : CL05A475MP5NRNC


2. Description

Part no.	Size (inch(mm))	Thickness (mm)	Temperature characteristics	Capacitance value	Capacitance tolerance(%)	Voltage (V)
CL05A475MP5NRNC	0402/1005	0.5mm	X5R	4.7uF	± 20 %	10

3. Characteristics data


1) Frequency characteristics

Agilent E4294A, 0.5Vrms, 1kHz to 110MHz




2) Temperature characteristics of capacitance(TCC)


Agilent 4284A, 1kHz, 0.5Vrms




3) DC Bias characteristics (Agilent 4284A, 1kHz, 0.5Vrms)



4) Bias TCC characteristics (Agilent 4284A, 1kHz, 0.5Vrms, 5Vdc)



5) AC voltage characteristics (Agilent 4284A, 1kHz)



Any data in this sheet are subject to change, modify or discontinue without notice

The data sheets include the typical data for design reference only. If there is any question regarding the data sheets, please contact our sales personnel or application engineers