





LCD-MID-FB Mid-Size Flat Panel Flush Mount

Product Features:

Holds 27" – 42" flat panels

Maximum flat panel hole pattern - 410mm x 340mm

Distance from wall to back of panel - 1"

Accommodates double gang box

Load capacity - 125 lbs

Silver powder coat finish

Also available in silver finish (LCD-MID-F)

Product Specifications:

(for Architects & Engineers)

The wall flush mount for the mid-size flat panel display shall be the Video Mount Products (VMP) model LCD-MID-F. The mount shall be designed to attach to 2 studs up to 16" apart or other suitable support surface. The mount shall be primarily constructed of formed steel and shall include spot welds. The mount shall be a universal style mount capable of adjusting to the dimensions of a variety of popular 27" to 42" flat panel displays and not necessarily be model specific. The adjustable mounting brackets shall be able to accommodate a maximum hole pattern of 410mm horizontal and 340mm vertically. The load capacity shall be 125 lbs.

Video Mount Products

345 Log Canoe Circle Stevensville, MD 21666 Toll Free: 877.281.2169 Telephone: 410.643.6390 Facsimile: 410.643.6615 **www.videomount.com**