



VE-6001

VE-10001

► **Features**



- High contrast LCD screen.
- Large stainless steel pan.
- Leveling feet.
- RS 232 interface.
- Multiple weighing units.
- Capacity tracker

► **Standard Functions**

- Weighing.
- Counting function.
- Percentage weighing.
- Accumulation function.
- Dynamic weighing.
- Density weight
- Peak holding function.
- Weigh - Below function.
- Computing function.
- High low limit alarm.
- Gross/Net/Tare weight

► **Accessories Included**

- 110-220V with US plug.
- RS-232 cable
- Rechargeable battery.
- An underhook.
- Dust cover and clear cover

► **TECHNICAL DATA**

	VE-6001	VE-10001
Model		
Capacity	6200g/10kg	10000 g
Readability	0.1g/0.2g	0.1 g
Repeatability	±0.1g/0.2g	±0.1 mg
Linearity	±0.2g/0.2g	±0.2 g
Weighing Units	g, ct, oz, ozt, dwt, GN, lb, N, dr, tIT, tIS, tIH, T, T/A/R, /A/R, ms, kg, bat, mom, /lb, total 20 units	
Calibration	External CAL	
Pan Size	168 x 168 mm / 6.6" x 6.6"	
Stabilization Time	≤ 3 seconds	
Interface	RS232, Can communicate with computer and printer simultaneously	
Display size	LCD, digit height 23 mm / 1"	
Housing	Metal base and ABS plastic	
Operating Environment	5° to 35°C / 41° to 95°F / Humidity 20% - 80%	
Overall Dimensions	295 x 208 x 88 mm / 11.6" x 8.1" x 3.4"	
Underhook mechanism	Hook included.	
Power Supply	110/240V, 50/60 AC Adapter.	
Net Weight	4.1 kg / 9 lb.	
Warranty	2 years.	