

## Data sheet | Item number: 258-5000

Thermal transfer printer; Smart Printer; for complete control cabinet marking; 300 dpi; With marking material

[www.wago.com/258-5000](http://www.wago.com/258-5000)



### Data

#### System requirements

Memory	4 GB
Supported operating systems	Windows 7 Windows 8 Windows 10

#### Technical data

Marking method	Thermal transfer
Print head	Glass layer, spring-mounted
Print resolution	300 dpi
Print resolution	300 dpi (12 pixels/mm)
Print speed (max.)	max. 127 mm/s (WAGO recommends 50.8 mm/s)
Print width	47 mm
Print length (max.)	762 mm
See-through/reflective sensor	yes, centrally fixed
Memory	8 MB

Subject to changes. Please also observe the further product documentation!

WAGO Corporation  
Germantown, WI 53022  
Phone: 1-800-DIN-RAIL (346-7245) | Fax: (262) 255-6222  
Email: [info.us@wago.com](mailto:info.us@wago.com) | Web: [www.wago.us](http://www.wago.us)

Do you have any questions about our products?  
We are always happy to take your call at (262) 255-6222 or 1 800-DIN-RAIL.



Beschriftungssoftware	Smart Script
Interfaces	USB, RS-232, ETHERNET 10/100 Mbps
Operating voltage	100 ... 240 VAC, 50 ... 60 Hz (automatic adjustment)
Safety approvals	CE (EMC)
Operating display	Color TFT LCD with navigation button
Ink ribbon	Reel outside diameter: 40 mm; core inside diameter 12.7 mm (0.5 inch); max. length 110 m; max. width 58 mm
Ink ribbon (width)	50 mm / 1.969 inch
Ink ribbon (length)	74 m / 360.9
Ink ribbon roll outside diameter	33 mm / 1.299 inch
Ink ribbon core inside diameter	12.5 mm / 0.492 inch
Scope of delivery	Power supply + cable, 2 x roller (258-5006 + 258-5007), 1 x reel holder, 1 x ink ribbon (258-5005), Smart Script marking software and driver, USB cable, external unwinder, 2 empty cardboard roller cores, 1 x roll of marking strips (2009-110) and WMB Inline markers (2009-115)

### Physical data

Height	175 mm / 6.89 inch
Width	135 mm / 5.315 inch
Depth	245 mm / 9.646 inch

### Material data

Weight	3840 g
--------	--------

### Environmental requirements

Surrounding air temperature (storage)	-20 ... 50 °C
Surrounding air temperature (operation)	5 ... 40 °C

### Commercial data

Product Group	14 (Tools)
PU (SPU)	1 Stück
Packaging type	box
Country of origin	TW
GTIN	4050821520993
Customs tariff number	8443321050

### Approvals / Certificates

Subject to changes. Please also observe the further product documentation!


WAGO Corporation  
 Germantown, WI 53022  
 Phone: 1-800-DIN-RAIL (346-7245) | Fax: (262) 255-6222  
 Email: [info.us@wago.com](mailto:info.us@wago.com) | Web: [www.wago.us](http://www.wago.us)

Do you have any questions about our products?  
 We are always happy to take your call at (262) 255-6222 or 1 800-DIN-RAIL.

**Ex-Approvals**

Logo	Approval	Additional Approval Text	Certificate name
	CCC CQC	-	2020010904320138

**UL-Approvals**

Logo	Approval	Additional Approval Text	Certificate name
	UL Underwriters Laboratories Inc.	UL 60950-1	E482462

**Optional accessories**

**Marking accessories**

Marking strip		
	<b>Item no.: 2009-110</b> Marking strips; for Smart Printer; on reel; not stretchable; plain; snap-on type; white	<a href="http://www.wago.com/2009-110">www.wago.com/2009-110</a>
	<b>Item no.: 210-877</b> Marking strips; for Smart Printer; permanent adhesive; 46 mm; silver-colored	<a href="http://www.wago.com/210-877">www.wago.com/210-877</a>
	<b>Item no.: 210-702</b> Marking strips; for Smart Printer; permanent adhesive; 15 mm; white	<a href="http://www.wago.com/210-702">www.wago.com/210-702</a>
	<b>Item no.: 210-831</b> Marking strips; on reel; 2.3 mm wide; plain; Self-adhesive; white	<a href="http://www.wago.com/210-831">www.wago.com/210-831</a>
	<b>Item no.: 210-833</b> Marking strips; on reel; 6 mm wide; plain; Self-adhesive; white	<a href="http://www.wago.com/210-833">www.wago.com/210-833</a>
	<b>Item no.: 210-834</b> Marking strips; on reel; 5 mm wide; plain; Self-adhesive; white	<a href="http://www.wago.com/210-834">www.wago.com/210-834</a>
	<b>Item no.: 210-832</b> Marking strips; on reel; 3 mm wide; plain; Self-adhesive; white	<a href="http://www.wago.com/210-832">www.wago.com/210-832</a>
	<b>Item no.: 210-870</b> Marking strips; for Smart Printer; permanent adhesive; 10 mm; white	<a href="http://www.wago.com/210-870">www.wago.com/210-870</a>

Subject to changes. Please also observe the further product documentation!



**Item no.: 210-873**

Marking strips; for Smart Printer; permanent adhesive; 20 mm; silver-colored

[www.wago.com/210-873](http://www.wago.com/210-873)



**Item no.: 210-874**

Marking strips; for Smart Printer; permanent adhesive; 30 mm; white

[www.wago.com/210-874](http://www.wago.com/210-874)



**Item no.: 210-871**

Marking strips; for Smart Printer; permanent adhesive; 10 mm; silver-colored

[www.wago.com/210-871](http://www.wago.com/210-871)



**Item no.: 210-876**

Marking strips; for Smart Printer; permanent adhesive; 46 mm; white

[www.wago.com/210-876](http://www.wago.com/210-876)



**Item no.: 210-872**

Marking strips; for Smart Printer; permanent adhesive; 20 mm; white

[www.wago.com/210-872](http://www.wago.com/210-872)



**Item no.: 210-875**

Marking strips; for Smart Printer; permanent adhesive; 30 mm; silver-colored

[www.wago.com/210-875](http://www.wago.com/210-875)



**Item no.: 709-178**

Marking strips; on reel; 7.5 mm wide; not stretchable; plain; snap-on type; white

[www.wago.com/709-178](http://www.wago.com/709-178)



**Item no.: 757-901/000-050**

Marking strips; on reel; not stretchable; plain; snap-on type

[www.wago.com/757-901/000-050](http://www.wago.com/757-901/000-050)



**Item no.: 210-880**

Marking strips; for Smart Printer; permanent adhesive; 12.7 mm; white

[www.wago.com/210-880](http://www.wago.com/210-880)



**Item no.: 210-882**

Marking strips; for Smart Printer; permanent adhesive; 22.6 mm; white

[www.wago.com/210-882](http://www.wago.com/210-882)



**Item no.: 2009-110/020-002**

Marking strips; for Smart Printer; on reel; not stretchable; plain; yellow

[www.wago.com/2009-110/020-002](http://www.wago.com/2009-110/020-002)

#### Type plate



**Item no.: 210-803**

Type labels; 99 x 44 mm; white

[www.wago.com/210-803](http://www.wago.com/210-803)



**Item no.: 210-801**

Type labels; 70 x 33 mm; white

[www.wago.com/210-801](http://www.wago.com/210-801)

Subject to changes. Please also observe the further product documentation!



**Item no.: 210-802**  
Type labels; 70 x 33 mm; silver-colored

[www.wago.com/210-802](http://www.wago.com/210-802)



**Item no.: 210-804**  
Type labels; 99 x 44 mm; silver-colored

[www.wago.com/210-804](http://www.wago.com/210-804)



**Item no.: 210-812**  
Type labels; 50 x 25 mm; silver-colored

[www.wago.com/210-812](http://www.wago.com/210-812)

Push-button label

**Item no.: 210-847**  
Push-button marker; 22 x 22 mm; silver-colored

[www.wago.com/210-847](http://www.wago.com/210-847)



**Item no.: 210-848**  
Push-button marker; 27 x 27 mm; silver-colored

[www.wago.com/210-848](http://www.wago.com/210-848)



**Item no.: 210-850**  
Push-button marker; 26.5 x 18 mm; silver-colored

[www.wago.com/210-850](http://www.wago.com/210-850)



**Item no.: 210-856**  
Push-button marker; 27.5 x 17.5 mm; silver-colored

[www.wago.com/210-856](http://www.wago.com/210-856)



**Item no.: 210-852**  
Push-button marker; 27 x 19 mm; silver-colored

[www.wago.com/210-852](http://www.wago.com/210-852)



**Item no.: 210-854**  
Push-button marker; 28 x 28 mm; silver-colored

[www.wago.com/210-854](http://www.wago.com/210-854)



**Item no.: 210-858**  
Push-button marker; 22 x 22 mm; silver-colored

[www.wago.com/210-858](http://www.wago.com/210-858)



**Item no.: 210-860**  
Push-button marker; 27 x 27 mm; silver-colored

[www.wago.com/210-860](http://www.wago.com/210-860)



**Item no.: 210-862**  
Push-button marker; 27 x 12.5 mm; silver-colored

[www.wago.com/210-862](http://www.wago.com/210-862)



**Item no.: 210-855**  
Push-button marker; 27 x 18 mm; silver-colored

[www.wago.com/210-855](http://www.wago.com/210-855)

Subject to changes. Please also observe the further product documentation!



**Item no.: 210-836**

Push-button marker; for frames, to be snapped in or glued in place; 27 x 17.5 mm; silver-colored

[www.wago.com/210-836](http://www.wago.com/210-836)



**Item no.: 210-840**

Push-button marker; for frames, to be snapped in or glued in place; 27 x 27 mm; silver-colored

[www.wago.com/210-840](http://www.wago.com/210-840)



**Item no.: 210-842**

Push-button marker; for frames, to be snapped in or glued in place; 27 x 12.5 mm; silver-colored

[www.wago.com/210-842](http://www.wago.com/210-842)

Wire marker for thread-on mounting



**Item no.: 211-863**

Conductor markers for thread-on mounting; for Smart Printer; 10 x 17 mm; white

[www.wago.com/211-863](http://www.wago.com/211-863)



**Item no.: 211-862**

Conductor markers for thread-on mounting; for Smart Printer; 7 x 10.5 mm; white

[www.wago.com/211-862](http://www.wago.com/211-862)



**Item no.: 211-861**

Conductor markers for thread-on mounting; for Smart Printer; 5 x 10.5 mm; white

[www.wago.com/211-861](http://www.wago.com/211-861)

Shrink tube



**Item no.: 211-501**

Shrink tube; for Smart Printer; Unshrunk diameter: 3.2 mm; white

[www.wago.com/211-501](http://www.wago.com/211-501)



**Item no.: 211-502**

Shrink tube; for Smart Printer; Unshrunk diameter: 4.8 mm; white

[www.wago.com/211-502](http://www.wago.com/211-502)



**Item no.: 211-504**

Shrink tube; for Smart Printer; Unshrunk diameter: 9.5 mm; white

[www.wago.com/211-504](http://www.wago.com/211-504)



**Item no.: 211-500**

Shrink tube; for Smart Printer; Unshrunk diameter: 2.4 mm; white

[www.wago.com/211-500](http://www.wago.com/211-500)



**Item no.: 211-503**

Shrink tube; for Smart Printer; Unshrunk diameter: 6.4 mm; white

[www.wago.com/211-503](http://www.wago.com/211-503)



**Item no.: 211-505**

Shrink tube; for Smart Printer; Unshrunk diameter: 12.7 mm; white

[www.wago.com/211-505](http://www.wago.com/211-505)















**Item no.: 211-506**

Shrink tube; for Smart Printer; Unshrunk diameter: 19.0 mm; white

[www.wago.com/211-506](http://www.wago.com/211-506)

Subject to changes. Please also observe the further product documentation!










Label		
	<b>Item no.: 210-805</b> Labels; for Smart Printer; permanent adhesive; 6 x 15 mm; white	<a href="http://www.wago.com/210-805">www.wago.com/210-805</a>
	<b>Item no.: 210-807</b> Labels; for Smart Printer; permanent adhesive; 8 x 20 mm; white	<a href="http://www.wago.com/210-807">www.wago.com/210-807</a>
	<b>Item no.: 210-810</b> Labels; for Smart Printer; 5 x 35 mm; white	<a href="http://www.wago.com/210-810">www.wago.com/210-810</a>
	<b>Item no.: 210-813</b> Labels; for Smart Printer; permanent adhesive; 40 mm; white	<a href="http://www.wago.com/210-813">www.wago.com/210-813</a>
	<b>Item no.: 210-806</b> Labels; for Smart Printer; permanent adhesive; 9 x 15 mm; white	<a href="http://www.wago.com/210-806">www.wago.com/210-806</a>
	<b>Item no.: 210-808</b> Labels; for Smart Printer; 9.5 x 25 mm; white	<a href="http://www.wago.com/210-808">www.wago.com/210-808</a>
	<b>Item no.: 210-811</b> Textile labels; for Smart Printer; permanent adhesive; 7 x 20 mm; white	<a href="http://www.wago.com/210-811">www.wago.com/210-811</a>
	<b>Item no.: 210-814</b> Labels; for Smart Printer; permanent adhesive; 40 mm; white	<a href="http://www.wago.com/210-814">www.wago.com/210-814</a>
Marker		
	<b>Item no.: 2009-113</b> WMB-Inline; for Smart Printer; 2300 pieces on roll; plain; snap-on type; white	<a href="http://www.wago.com/2009-113">www.wago.com/2009-113</a>
	<b>Item no.: 2009-145</b> Mini-WSB Inline; for Smart Printer; 1700 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; white	<a href="http://www.wago.com/2009-145">www.wago.com/2009-145</a>
	<b>Item no.: 2009-114</b> WMB-Inline; for Smart Printer; 2000 pieces on roll; stretchable 4 - 4.2 mm; plain; snap-on type; white	<a href="http://www.wago.com/2009-114">www.wago.com/2009-114</a>
	<b>Item no.: 2009-115</b> WMB-Inline; for Smart Printer; 1500 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; white	<a href="http://www.wago.com/2009-115">www.wago.com/2009-115</a>
	<b>Item no.: 2009-515</b> WMB-Inline; for Smart Printer; 900 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; white	<a href="http://www.wago.com/2009-515">www.wago.com/2009-515</a>

Subject to changes. Please also observe the further product documentation!

	<b>Item no.: 2009-615</b> WMB-Inline; for Smart Printer; on reel; stretchable 5 - 5.2 mm; plain; snap-on type; white	<a href="http://www.wago.com/2009-615">www.wago.com/2009-615</a>
	<b>Item no.: 211-821</b> Marker card; for Smart Printer; for use in nozzles; Length: 23 mm; white	<a href="http://www.wago.com/211-821">www.wago.com/211-821</a>
	<b>Item no.: 211-811</b> Marker card; for Smart Printer; for use in nozzles; Length: 12 mm; white	<a href="http://www.wago.com/211-811">www.wago.com/211-811</a>
Self-laminating label		
	<b>Item no.: 211-855</b> Self-laminating labels; for Smart Printer; 9 x 18 mm; white	<a href="http://www.wago.com/211-855">www.wago.com/211-855</a>
	<b>Item no.: 211-856</b> Self-laminating labels; for Smart Printer; 15 x 22 mm; white	<a href="http://www.wago.com/211-856">www.wago.com/211-856</a>
	<b>Item no.: 211-857</b> Self-laminating labels; for Smart Printer; 18 x 44 mm; white	<a href="http://www.wago.com/211-857">www.wago.com/211-857</a>
Cable tie markers		
	<b>Item no.: 211-835</b> Cable tie marker; for Smart Printer; for use with cable ties; 25 x 10 mm; white	<a href="http://www.wago.com/211-835">www.wago.com/211-835</a>
	<b>Item no.: 211-836</b> Cable tie marker; for Smart Printer; for use with cable ties; 100 x 15mm; white	<a href="http://www.wago.com/211-836">www.wago.com/211-836</a>
	<b>Item no.: 211-837</b> Cable tie marker; for Smart Printer; for use with cable ties; 44 x 10 mm; white	<a href="http://www.wago.com/211-837">www.wago.com/211-837</a>
<b>Accessory for marking devices</b>		
Accessories for marking devices		
	<b>Item no.: 258-5009</b> Roller; for Smart Printer; for WMB-Inline Phoenix (2009-515); 1 grinding device	<a href="http://www.wago.com/258-5009">www.wago.com/258-5009</a>
	<b>Item no.: 258-5008</b> Roller; for Smart Printer; for Mini-WSB Inline WAGO (2009-145); 1 grinding device	<a href="http://www.wago.com/258-5008">www.wago.com/258-5008</a>

Subject to changes. Please also observe the further product documentation!



	<p><b>Item no.: 258-5010</b>                  Roller; for Smart Printer; for WMB-Inline Weidmüller (2009-615); 1 grinding device</p>	<a href="http://www.wago.com/258-5010">www.wago.com/258-5010</a>
	<p><b>Item no.: 258-5005</b>                  Thermal transfer ink ribbon; for Smart Printer; black</p>	<a href="http://www.wago.com/258-5005">www.wago.com/258-5005</a>
	<p><b>Item no.: 258-5006</b>                  Roller; for Smart Printer; for marking strips, device and equipment markers, conductor and cable markers</p>	<a href="http://www.wago.com/258-5006">www.wago.com/258-5006</a>
	<p><b>Item no.: 258-5007</b>                  Roller; for Smart Printer; for WMB-Inline WAGO (2009-115, -114, -113); 1 grinding device</p>	<a href="http://www.wago.com/258-5007">www.wago.com/258-5007</a>
	<p><b>Item no.: 258-5014</b>                  Thermal transfer ink ribbon; for Smart Printer; for self-laminating labels; black</p>	<a href="http://www.wago.com/258-5014">www.wago.com/258-5014</a>
	<p><b>Item no.: 258-5015</b>                  Carrying case; white</p>	<a href="http://www.wago.com/258-5015">www.wago.com/258-5015</a>
	<p><b>Item no.: 258-5030</b>                  Cutter; for Smart Printer; for marking strips, equipment markers, conductor and cable markers;                  Durable; High accuracy</p>	<a href="http://www.wago.com/258-5030">www.wago.com/258-5030</a>
	<p><b>Item no.: 258-5005/000-005</b>                  Thermal transfer ink ribbon; for Smart Printer; red</p>	<a href="http://www.wago.com/258-5005/000-005">www.wago.com/258-5005/000-005</a>
	<p><b>Item no.: 258-5011</b>                  Roller; for Smart Printer; for Micro WSB Inline roller (2009-141); 1 grinding device</p>	<a href="http://www.wago.com/258-5011">www.wago.com/258-5011</a>

## Downloads Documentation

Manual			
smartPRINTER operating instructions	003.10.2017 Sep 25, 2020	pdf 3.2 MB	Download
WAGO Smart Script Benutzerhandbuch	1 Mar 3, 2020	pdf 3.6 MB	Download
Operating Instructions			
211-502 Information on printing material	1	pdf	Download

Subject to changes. Please also observe the further product documentation!



	Aug 28, 2020	1.1 MB	
211-821 Information on printing material	1 Aug 28, 2020	pdf 1.3 MB	Download
2009-145 Information on printing material	1 Aug 28, 2020	pdf 1.3 MB	Download
210-811 Handhabungshinweis zum Druckmaterial	1 Aug 28, 2020	pdf 1.4 MB	Download
210-813 Information on handling print material	1 Aug 28, 2020	pdf 1.4 MB	Download
211-856 Information on printing material	1 Aug 28, 2020	pdf 1.3 MB	Download
211-836 Information on printing material	1 Aug 28, 2020	pdf 1.5 MB	Download
210-831 Information on handling print material	1 Aug 28, 2020	pdf 1.2 MB	Download
2009-110 Information on printing material	1 Aug 28, 2020	pdf 1.2 MB	Download
211-835 Information on printing material	1 Aug 28, 2020	pdf 1.4 MB	Download
210-852 Information on handling print material	1 Aug 28, 2020	pdf 1.0 MB	Download
2009-615 Information on printing material	1 Aug 28, 2020	pdf 1.3 MB	Download
210-804 Information on handling print material	1 Aug 28, 2020	pdf 1.4 MB	Download
210-805 Information on handling print material	1 Aug 28, 2020	pdf 1.3 MB	Download
2009-515 Information on printing material	1 Aug 28, 2020	pdf 1.3 MB	Download
211-861 Information on printing material	1 Aug 28, 2020	pdf 1.3 MB	Download

2009-115 Information on printing material

Subject to changes. Please also observe the further product documentation!

WAGO Corporation  
 Germantown, WI 53022  
 Phone: 1-800-DIN-RAIL (346-7245) | Fax: (262) 255-6222  
 Email: [info.us@wago.com](mailto:info.us@wago.com) | Web: [www.wago.us](http://www.wago.us)

Do you have any questions about our products?  
 We are always happy to take your call at (262) 255-6222 or 1 800-DIN-RAIL.



258-5000 Information on printing material	1 Aug 28, 2020	pdf 1.3 MB	Download
<b>Additional Information</b>			
Overview software versions	1 Feb 22, 2021	pdf 733.7 kB	Download
Allocation roller printing material	001.12.2016 Sep 10, 2020	pdf 143.3 kB	Download
Instructions external unwinder	001.12.2016 Sep 8, 2020	pdf 1.0 MB	Download
FAQ fault description and troubleshooting	002.07.2017 Apr 27, 2020	pdf 83.9 kB	Download
Cutting Unit V2	1 Apr 27, 2020	pdf 620.4 kB	Download
IT infrastructure requirements	002.09.2017 Aug 15, 2019	pdf 36.6 kB	Download
Smart Printer accessories	30.01.2017 Jun 30, 2019	pdf 873.7 kB	Download

## Software Solutions (Applications)

### Smart Script 4.x Marking Software

Smart Script 4.x Marking Software	4.8.1.1 Oct 25, 2021	zip 162.5 MB	Download
-----------------------------------	-------------------------	-----------------	----------

Use the new Smart Script 4.x marking software to easily create and print custom marking strips, markers and labels for any WAGO component. This software version is tailored to our Smart Printer thermal transfer printer and comes with all the drivers and settings you need with this printer.

#### Overview of Features:

- Modern design and intuitive use
- Fast and easy to use, with all applications such as printer drivers and settings integrated.
- Ideal for professional marking of terminal blocks, labels, type plates and conductor markers
- Optimized data interfaces for Smart Designer configuration software, EPLAN, Microsoft Excel, CSV

#### Supported operating systems:

—

Subject to changes. Please also observe the further product documentation!



- Windows 10, Windows 8, Windows 7 64 Bit

System requirements:

- 3 Gigahertz (GHz) or faster, 64-bit (x64) processor
- 4 GB RAM, recommended 8 GB
- 400 MB available storage space on hard drive
- Screen resolution of 1360 x 864 or higher (100 % scaling)
- Smart Printer Firmware starting from Version 1.UW7v

---

### SmartScript 3.9 Marking Software

Smart Script 3.9 Marking Software

3.9

ZIP

Download

Jul 10, 2019

47.2 MB

Use the Smart Script 3.9 marking software to easily create and print marking strips, markers and labels for any WAGO component. You may need the current driver (Smart Printer Driver) and the easy-to-use "Printer Setting Tool" to use the Smart Printer thermal transfer printer.

NOTE: Version 3.9.0.0 can only be used together with the Smart Printer thermal transfer printer and resolves the font width issue for Windows 10 Version 1809.

Supported operating systems:

- Windows 10, Windows 8, Windows 7 64 Bit

System requirements:

- 3 Gigahertz (GHz) or faster, 64-bit (x64) processor
- 4 GB RAM, recommended 8 GB
- 400 MB available storage space on hard drive
- Screen resolution of 1360 x 864 or higher
- Smart Printer Firmware starting from version 1.UW7q

---

### Smart Script 3.8 Marking Software

Smart Script 3.8 Marking Software

3.88.23.4

ZIP

Download

Jul 10, 2019

47.5 MB

Use the Smart Script 3.8 marking software to easily create and print marking strips, markers and labels for any WAGO component. You may need the current driver (Smart Printer Driver) and the easy-to-use "Printer Setting Tool" to use the Smart Printer thermal transfer printer.

NOTE: Version 3.88.23.4 supports the WAGO Plotter, WAGO Engraver and standard A4 printers.

Supported operating systems:

—

Subject to changes. Please also observe the further product documentation!



- Windows 10, Windows 8, Windows 7 64 Bit

System requirements:

- 3 Gigahertz (GHz) or faster, 64-bit (x64) processor
- 4 GB RAM, recommended 8 GB
- 400 MB available storage space on hard drive
- Screen resolution of 1360 x 864 or higher
- Smart Printer Firmware starting from version 1.UW7q

---

**Installation Package 3.9 Smart Printer**

Installation Package 3.9 Smart Printer	3.9	ZIP	Download
Installation package for the Smart Printer thermal transfer printer:	Jul 10, 2019	69.8 MB	

- Smart Script 3.9 marking software
- Smart Printer driver
- Printer setting tool

Use the Smart Script 3.9 marking software to easily create and print marking strips, markers and labels for any WAGO component. You may need the current driver (Smart Printer Driver) and the easy-to-use "Printer Setting Tool" to use the Smart Printer thermal transfer printer.

NOTE: Version 3.9.0.0 can only be used together with the Smart Printer thermal transfer printer and resolves the font width issue for Windows 10 Version 1809.

Supported operating systems:

- Windows 10, Windows 8, Windows 7 64 Bit

System requirements:

- 3 Gigahertz (GHz) or faster, 64-bit (x64) processor
- 4 GB RAM, recommended 8 GB
- 400 MB available storage space on hard drive
- Screen resolution of 1360 x 864 or higher
- Smart Printer Firmware starting from version 1.UW7q

---

**Installation Package 3.8 Smart Printer**

Installation Package 3.8 Smart Printer	3.8	ZIP	Download
Installation package for the Smart Printer thermal transfer printer:	Jul 10, 2019	70.1 MB	

- Smart Script 3.8 marking software
- Smart Printer driver

Subject to changes. Please also observe the further product documentation!



- Printer setting tool

Use the Smart Script 3.8 marking software to easily create and print marking strips, markers and labels for any WAGO component. You may need the current driver (Smart Printer Driver) and the easy-to-use "Printer Setting Tool" to use the Smart Printer thermal transfer printer.

NOTE: Version 3.88.23.4 supports the WAGO Plotter, WAGO Engraver and standard A4 printers.

Supported operating systems:

- Windows 10, Windows 8, Windows 7 64 Bit

System requirements:

- 3 Gigahertz (GHz) or faster, 64-bit (x64) processor
- 4 GB RAM, recommended 8 GB
- 400 MB available storage space on hard drive
- Screen resolution of 1360 x 864 or higher
- Smart Printer Firmware starting from version 1.UW7q

---

## Device Files

### additional software

WAGO-EPLAN-Interface 64Bit	1.5.2	zip	Download
The new interface for EPLAN Electric P8 incl. ProPanel (from version 2.5) from WAGO as plug-in for more efficiency in digital engineering.	Aug 10, 2021	1.7 MB	

The advantages:

Continuity along the value chain  
Reuse of data without media disruption  
time and cost savings

The properties of the EPLAN interface:

Automatic terminal strip layout from the circuit diagram or installation space navigator of EPLAN in the WAGO Smart Designer  
Automated terminal block labeling, plausibility check, automatic completion of missing components and ordering options in Smart Designer  
Reimport from Smart Designer to EPLAN for a complete bill of materials in the CAE tool  
Automated terminal labeling and direct printing from EPLAN

---

WAGO Firmware for Thermotransferdrucker Smart Printer	V1.UW7v	zip	Download
	Jun 24, 2020	3.9 MB	

Subject to changes. Please also observe the further product documentation!



**ATTENTION: Firmware 1.UW7y is currently not available. Please install the update later. Thank you for your understanding.**

Version V1.UW7v is a completely functional firmware outside the use of Data Matrix Codes.

---

WAGO Smart Label	2.5 Oct 25, 2017	zip 37.6 MB	Download
WAGO GoDoctor	1.005	zip 810.4 kB	Download

---

## Environmental Product Compliance

### Compliance Search

---

Environmental Product Compliance 258-5000 Thermal transfer printer; Smart Printer; for complete control cabinet marking; 300 dpi; With marking material	URL	Download
--	-----	----------

---

## Installation Notes

Subject to changes. Please also observe the further product documentation!

---

WAGO Corporation  
Germantown, WI 53022  
Phone: 1-800-DIN-RAIL (346-7245) | Fax: (262) 255-6222  
Email: [info.us@wago.com](mailto:info.us@wago.com) | Web: [www.wago.us](http://www.wago.us)

Do you have any questions about our products?  
We are always happy to take your call at (262) 255-6222 or 1 800-DIN-RAIL.