Conoral ordering data	
General ordering data Order No.	1579050000
Part designation	WQB B/10
Version	Cross-connector / link for modular terminal, Cross-
EAN	connector, No. of poles: 10
EAN	4008190094508
Qty.	20 pc(s).
Additional technical data	
Explosion-tested version "Ex e"	No
Cross-connector	
Height	12 mm
No. of cross-connected terminals	10
Pitch	5.1 mm
Rated current, multi-pole	24 A
Rated voltage	0 V
Туре	Cross-connector
Type of fixing	Screwed
Function	Cross-connector
No. of poles	10
Rating data	
Rated voltage	0 V
Downloads	
DXF	18599_WQB_B-10_DXF.dxf
STEP	1579050000_18599_WQB_B-10_STP.stp
Classifications	
ETIM 2.0	EC000489
ETIM 3.0	EC000489
eClass 4.1	27-14-11-99
eClass 5.0	27-14-11-40
eClass 5.1	27-14-11-40

Similar products

1579010000	WQB B/2	Cross-connector / link for modular terminal, Cross-connector, No. of poles: 2
1579020000	WQB B/3	Cross-connector / link for modular terminal, Cross-connector, No. of poles: 3
1579030000	WQB B/4	Cross-connector / link for modular terminal, Cross-connector, No. of poles: 4
1579040000	WQB B/6	Cross-connector / link for modular terminal, Cross-connector, No. of poles: 6
1579060000	WQB B/24	Cross-connector / link for modular terminal, Cross-connector, No. of poles: 24

