

Black Finish Long Arm Hex L-keys



[SHOP](#)

352 Metric L-wrench Hex Key, Long Arm, high alloy CVM steel, hardened, black finish. Precision machined, burr free chamfered ends.

Item							
No.	mm	mm	Inch	mm	Inch	lbs.	pkg.
352 00	0.7	66	2.6	5	.2	.01	10
352 03	0.9	68	2.7	8	.3	.01	10
352 05	1.3	72	2.8	12	.5	.01	10
352 15	1.5	89	3.5	14	.6	.01	10
352 20	2.0	99	3.9	16	.6	.01	10
352 25	2.5	110	4.3	18	.7	.02	10
352 30	3.0	124	4.9	20	.8	.02	10
352 40	4.0	138	5.4	25	1.0	.04	10
352 50	5.0	158	6.2	28	1.1	.07	10
352 60	6.0	178	7.0	32	1.3	.12	10
352 70	7.0	187	7.4	34	1.3	.18	10
352 80	8.0	196	7.7	36	1.4	.24	10
352 82	10.0	219	8.6	40	1.6	.40	10
352 84	12.0	245	9.6	45	1.8	.77	1
352 85	14.0	277	10.9	56	2.2	1.13	1
352 86	17.0	316	12.4	63	2.5	1.80	1
352 88	19.0	355	14.0	70	2.8	2.45	1



[SHOP](#)

352 Inch L-wrench Hex Key, Long Arm

Item					
No.	Inch	mm	Inch	lbs.	pkg.
352 00	.028	67	2.6	.01	10
352 03	.035	69	2.7	.01	10
352 13	.050	75	3.0	.01	10
352 16	1/16	78	3.1	.01	10
352 18	5/64	82	3.2	.01	10
352 22	3/32	85	3.3	.01	10
352 24	7/64	92	3.6	.02	10
352 26	1/8	95	3.7	.02	10
352 28	9/64	100	3.9	.03	10
352 32	5/32	105	4.1	.04	10
352 34	3/16	113	4.4	.05	10
352 36	7/32	122	4.8	.07	10
352 38	1/4	135	5.3	.10	10
352 42	5/16	152	6.0	.18	10
352 44	3/8	173	6.8	.30	10
352 45	1/2	209	8.2	.75	1
352 46	9/16	230	9.1	.99	1
352 47	5/8	245	9.6	1.26	1
352 48	3/4	286	11.3	2.02	1
352 49	1"	359	14.1	4.38	1



[SHOP](#)

352 90 Metric Hex L-wrench Set, 9 Pc. in Plastic Holder

Equipped with 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0, 8.0, 10.0mm

Item		
No.	lbs.	pkg.
352 90	.97	1



[SHOP](#)

352 91 Inch Hex L-wrench Set, 13 Pc. in Plastic Holder

Equipped with .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8"

Item		
No.	lbs.	pkg.
352 91	.96	1