

ND 909 CHROME

About Item

1. **Industry-standard:**The 5 Core dynamic microphone is the preferred choice of performers worldwide, providing an industry standard for bringing any performance to life, whether in a club or stadium setting. It has a dedicated On/ Off switch button.
2. **Clarity & care:**Delivering warm and crisp sound with clarity and care, this XLR microphone features a uniform cardioid polar pattern reproducing every note as intended, ensuring consistent performance after performance.
3. **Unidirectional:**With a unidirectional cardioid pickup pattern, the microphone captures the intended source signal, whether it be from a guitarist's amplifier or a vocalist's voice, while minimizing unwanted off-axis sound, background noise and feedback, producing interference-free audio.
4. **Leave background noise behind:**Keep background noise out of the mix with the 5 Core dynamic microphone, equipped with a spherical mesh grille and built-in pop filter, ensuring that only the intended sound is captured.
5. **Drop the mic:**Built to last, the 5 Core wired microphone features durable construction with a chrome finish and can withstand the rigors of regular use. Making it the ideal companion for performers on the road, able to withstand the most demanding performance.

Product Description

Whether performing live or recording in a studio, the music from your instrument can connect with your audience. This includes the sharp sound of a snare drum, the melodious notes of an arpeggiated chord, or the energetic solo of a saxophone. These sounds require a microphone that can handle these notes. The 5 Core dynamic microphone is built to capture your performance's power and deliver it to every listener.

Built with rugged material and a metal mesh windscreen with an anti-dent ring, this XLR microphone is designed for maximum reliability, ensuring that it will come through for you time and time again, even after countless gigs and studio applications. Whether you are a seasoned professional or just starting, this versatile, dynamic microphone is a must-have for any performer or recording artist.

At 5 Core, Customer satisfaction is our priority with a proven track record of delivering the highest quality product since 1984.

Features

Compatibility	XLR Cable	Premium Sound	Reliable
The dynamic microphone is compatible with most audio systems, including DVD players, mixers, and home theater.	Fully shielded XLR cable for minimal interference over long distances.	The dynamic microphone provides power and clarity, ideal for studio and stage use.	5 Core microphones are trusted by performers of all levels for their professional utility & high performance.

Technical Specifications:

- Type: Dynamic
- Polar Pattern: Cardioid
- Material: Metal
- Sensitivity: -54(±3)dB (at 1KHz)0dB=1V/Pa)
- Frequency response: 60Hz~14KHz
- Cable Length: 5.0*4 meters

Package includes:

- 1x Dynamic Microphone
- 1x Mic clip/ holder
- 1x 16 ft mic cable

Usages

Wire microphone is ideal for recording instruments.

Use the dynamic microphone for live vocal performance.

A durable microphone is perfect for public events or rallies.

The XLR microphone can be used for podcasts or voice-overs.

The dynamic microphone can be used during a meeting or video conferencing.

Benefits of products

Provides optimal clarity and punch.

Compatible with most PA audio systems.

Minimizes background noise and feedback.

Captures source signal with high accuracy.

Reproduces audio without interference from other instruments or speakers on stage.

Benefits of 5 Core over other products

4.5m coaxial, shielded low noise cable.

Premium-quality ferrite magnet in cartridge.

Universally-matched 3-pin professional XLR connector.

Metal with thick foam for shock/dust proofing cartridge.

5 Core dynamic microphone offers professional-grade sound recording capabilities.

Why 5 Core

5 Core has been known for producing high-quality, premium products since 1984.

We are committed to using only the best materials and components to ensure the longevity of our products.

The best deals compared to other brands in the market without compromising on quality.

The trust worthy choice for thousands of customers scattered worldwide in more than 65 countries.

Backed by a proven track record of happy customers and peace of mind.

Comparison

Specification	5 Core Product	Other Product
XLR cable	Yes	No
Durable	Yes	No
Best Deal	Yes	No

About Brand

5 Core, headquartered in California, warehouse in Bellefontaine, OH, USA, has a reputation for being a trusted and reliable brand, offering products designed to meet the highest industry standards. Our products are thoroughly tested and inspected before they are sent to the end user, ensuring that the customers receive products of the highest quality and reliability. With a commitment to quality, affordability, and customer satisfaction, 5 Core is a brand people can trust for all their needs and wants.

Q&A

Question:What is the impedance of the microfono?

Answer:The microfono has 600 Impedance.

Question:What kind of events is this microphone suitable for?

Answer:This microphone is perfect for all kinds of live events, including presentations, weddings, conferences, singing, and more.

Question:Can I use the XLR microphone for recording in a studio?

Answer:Yes, this XLR microphone is versatile and can be used for stage and recording applications.

Question:What is the frequency response of the dynamic microphone?

Answer:The dynamic microphone has a 60Hz~14KHz frequency response.

Question:What is a cardioid pickup pattern?

Answer:A cardioid pickup pattern is a directional microphone that captures sound mainly from the front of the microphone while minimizing sound from the side and rear. This is ideal for live situations where noise cancellation is needed.