

## PACKET 250

### About Item

1. **Pa System with Mic:** The 5 Core portable PA system set is an ideal PA solution for various applications as it includes a powerful & versatile audio amplifier, PA horns, and a mic. It can be used in large outdoor areas and comes with six professional 8-inch horn speakers and all the necessary accessories for a large crowd.
2. **Powerful Amplifier:** With a 2-channel professional paging amplifier of 600W 4/8 ohm and 60W RMS, this system is perfect for live stages, DJ setups, studios, auditoriums, places of worship, and, of course, outdoor meetings or announcements. The amplifier features 600W peak power sufficient for outdoor audio requirements. It also has base, treble, balance, master volume controllers, and a 70 Micron Glass Epoxy printed circuit board.
3. **Clear & loud sound:** The kit comes with a PA horn speaker designed to provide clear and loud sound amplification for speeches and music. Its impedance is 16 ohms, and it has an output SPL (1W/1M) - 108 dB, making it ideal for indoor and outdoor use.
4. **2 Dynamic Microphone:** The PA set features a dynamic microphone made by 5 Core(MM 05 B); this meeting microphone is a versatile and highly optimized mic with heavy metal housing and textured powder coating. Its molded body makes it easy to handle, and the metal gooseneck adds a professional look and ease of speech.
5. **Powerful & portable:** The 5 Core high-powered PA sound system is both powerful and easy to use, making it an excellent choice for conducting outdoor meetings, venues, parties, and more. This pack includes all necessary accessories, and it's one of the best kits available in the market that will give you a massive reach at ease.



Product Description

Looking for a powerful and portable sound system that can deliver clear and loud sound for a meeting, events, or large gatherings? Look no further than our PA sound kit. This setup comes equipped with all the necessary accessories and equipment to make your events a success, including a powerful amplifier, mic, and PA horns. Its six professional 16-inch horn speakers can handle large outdoor areas, while its 600W amplifier is sufficient for outdoor audio requirements. And with its bass, treble, balance, and master volume controls, you can easily adjust the sound to suit your preferences.

Whether you are hosting an outdoor meeting, venue, or party, this PA kit will help you easily reach thousands of people. Get the PA set now and experience the power and convenience of our compact and high-powered sound system.

At 5 Core, Customer satisfaction is our priority—a proven track record of delivering the highest quality product since 1984.

Features

Remote control	EQ control	Clear & loud sound	Build to last
This magnificent amplifier comes with a Fully-functional remote control; it is convenient for you to remotely control the machine at any angle and get rid of the shackles of wires. (CD/DVD/VCD/MP3/MP4).	The improved professional compact bookshelf sound amplifier features crisp, responsive buttons for mode controls. Rotary knob controls for mic echo/volume balance, bass, treble, master volume, input source, and the unique folder/track.	This heavy-duty PA horn speaker is excellent for amplifying your speech or music. It has an impedance of 16 ohms and a power output of SPL (1W/1M) - 108 dB, making this horn speaker ideal for outdoor and indoor use.	Engineered by professionals, the Rectangular-shaped Horn is powerful, rugged, lightweight, and made in tough ABS Plastic to deliver clean, intelligible sound.

**Technical Specifications of Mic:**

- Type: Desktop microphone
- Mic. Unit: 9x7 mm
- Mic. Directivity: Omni Direction
- Mic. Sensitivity: -58dB±2dB
- Mic. Impedance: Low
- Freq. resp: 30 Hz to 16,000 Hz
- Cable: Approx 1.2m±0.3m
- Plug Type: 3.5 mm stereo plug x 2

**Technical Specifications of PA Horn:**

- Input Power - 25W RMS/35W Max.
- Freq. Resp. - 275-10000 Hz
- SPL (1W/1M) - 108 dB

**Specification Amplifier:****Power Source**

- AC: 220-240V 50/60Hz, DC: 12V (Car battery)
- Power Output: 92W Max, 60W RMS at 10% THD
- Output regulation: 2db, no load to full load at 1kHz
- Input/Sensitivities of PMPO 600W Amplifier: 3xMIC 0.65mV/4.7kΩ, 1xAux 125mV/470kΩ

**Tone Controls:**

- BASS: - ±10db at 100Hz
- TREBLE: ±10db at 10kHz
- Signal to Noise ratio: 60db
- Line Output: Pre Amp 125mV/470Ω
- Power Consumption: AC: 140VA, DC: 6 Amps
- Speaker output: 4Ω, 8Ω, 100V
- Dimensions: (355x135x284)MM
- Frequency Response: 50 to 15000Hz ±3dB
- Weight: 6.60Kg

**Package includes:**

6 Pieces Outdoor PA Horn Speaker with 2 Pc Mic & 1 60W Amplifier

## Usages

Outdoor meetings or conferences.

Public announcements in large areas.

Well suited for worship services or religious events.

Studios or auditoriums for amplifying music or speeches.

Sporting events or competitions where clear announcements are necessary.

## Benefits of products

Portable and easy to transport.

Provides clear and loud sound amplification.

Versatile and suitable for various applications.

Ideal for public announcements in large areas.

Perfect for outdoor meetings, venues, and parties.

## Benefits of 5 Core over other products

Fully-functional remote control.

Generates a robust 60-watt sound.

High Output Neodymium Magnet in Cartridge.

Heavy-weight housing with anti-skid feet ensures stability.

600W RMS is perfect for Live Stage, DJ, studio, Auditorium, Outdoor announcement, and Worship.

### Why 5 Core

5 Core has been known for producing high-quality, premium products since 1984.

We are committed to using only the best materials and components to ensure the longevity of our products.

The best deals compared to other brands in the market without compromising on quality.

The trustworthy choice for thousands of customers scattered worldwide in more than 65 countries.

Backed by a proven track record of happy customers and peace of mind.

### Comparison

Specification	5 Core Product	Other Product
All in one set	Yes	No
Durable	Yes	No

Best deal	Yes	No
-----------	-----	----

## About Brand

5 Core, headquartered in California, warehouse in Bellefontaine, OH, USA, has a reputation for being a trusted and reliable brand, offering products designed to meet the highest industry standards. Our products are thoroughly tested and inspected before they are sent to the end user, ensuring that the customers receive products of the highest quality and reliability. With a commitment to quality, affordability, and customer satisfaction, 5 Core is a brand people can trust for all their needs and wants.

## Q&A

**Question:** Can the system be used indoors?

**Answer:** The system is suitable for indoor and outdoor use.

**Question:** Is the system easy to set up?

**Answer:** Yes, the system is designed to be user-friendly and easy to set up. It comes with all the necessary accessories and instructions to help you get started quickly.

**Question:** Is the system compatible with Bluetooth devices?

**Answer:** No, the system does not have Bluetooth connectivity. However, you can connect external devices using the AUX input.

**Question:** Is the microphone included with the system wireless or wired?

**Answer:** The PA kit comes with a wired microphone, which allows you to address the crowd or audience.

**Question:** Can I connect an external microphone other than the packaged one?

**Answer:** Yes, the amplifier has an AUX port that lets you connect any compatible mic with the system other than the mic which we have provided.