



## **A75**

Android POS

A Versatile, Light Choice for Multifunctional Payment Terminal

































Smart handheld POS terminal, this is a powerful functional mobile payment terminal with a high-definition multimedia color touch screen and has a fingerprint scanner(Optional). It supports various communication technologies such as 4G, WIFI, and Bluetooth. The operating system is Android 10 and adopts the security chip required by PCI. It recognizes all financial payment and consumption functions such as magnetic stripe card, contactless card, two-dimensional code drawing, and payment, etc.A75 POS comes in a sleek and attractive design, combines the full features of an Android tablet with a powerful payment terminal, and compatible with all leading intelligent technology.

## **Features**



Light weight and slim design



5" IPS Color Screen, 1280\*720



Speed up work flow



Improve accuracy



High Speed Thermal Printer

32bit, Quad-Core



Card Readers



5200mAh



Camera

## **Smart Applications**



Restaurant





Entrance

Scenic Spot Convenience Store



Toll

station



Parking Supermarket lot

Specifications	
OS	: Android 10
CPU	: Quad-core Cortex-A7, 1.1GHz
Memory	: RAM :1G;ROM:8G FLASH, Optional Maximum 32GB SD card
Display	: 5" IPS Screen 1280×720 pixels
Screen	: Capacitive Touchscreen
Card Readers	: Chip & PIN   NFC Contactless   Magnetic Stripe
Camera	: 2 MP Front. 5MP Rear, Flashlight, Barcode Scanner
Comm Config	: 4G/3G/2G
Wifi	: 802.11 b/g/n 2.4 GHz, optional 5GHz
Bluetooth	: 4.2
GPS	: Supports GPS/GLONASS/BeiDou
NFC	: Yes
IC Card Reader	: Yes
Magnetic Crad Reader	: Yes
PSAM	: 2 PSAM Slots (optional)
Printer	: High Speed Thermal Printer, Diameter:40mm, paper width : 58mm
Audio	: 1 Speaker
Memory Extension	: 1 micro SD Card
USB Port	: 1 Type C USB OTG   5V
SIM/SAM	: 1 SIM
Keys / Buttons	: 1 Power Key, 1 Printer Key, 3 Touch Keys
Battery	: 5200 mAh   3.6V
Power	: Input: 100 - 240V AC, 50Hz / 60Hz   Output: 5.0V DC, 2.0A
Environmental	: Operating Temperature -10°C ~ 50°C Storage Temperature 5% ~ 95%
Weight	: 400g
Certifications	: PCI PTS 6.x
Indicator Lights	: 4 contactless indicators, 1 charging indicator







sales@mantratec.com

