

**Accessories**  
**ZQV 2.5/4**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Product image****Spring connection with tension clamp Technology**

Tension clamp technology is a universal contact system for all common conductor connection types. Its fantastic level of flexibility makes the tension clamp a profitable alternative connection.

**General ordering data**

Type	ZQV 2.5/4
Order No.	<a href="#">1608880000</a>
Version	Accessories, Cross-connector, 24 A
GTIN (EAN)	4008190082208
Qty.	60 pc(s).

## Accessories ZQV 2.5/4

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technical data

### Dimensions and weights

Width	2.8 mm	Width (inches)	0.11 inch
Height	18.7 mm	Height (inches)	0.736 inch
Depth	27.6 mm	Depth (inches)	1.087 inch
Net weight	2.45 g		

### Temperatures

Continuous operating temp., min.	-60 °C	Continuous operating temp., max.	130 °C
----------------------------------	--------	----------------------------------	--------

### Material data

Material	Wemid	Colour	Yellow
UL 94 flammability rating	V-0		

### System specifications

Version	For the terminals	Mounting rail	none
---------	-------------------	---------------	------

### Additional technical data

Explosion-tested version	Yes	Type of fixing	Plugged
--------------------------	-----	----------------	---------

### Dimensions

Pitch in mm (P)	5.1 mm
-----------------	--------

### Rating data

Rated current	24 A
---------------	------

### Classifications

ETIM 3.0	EC000489	ETIM 4.0	EC000489
ETIM 5.0	EC000489	ETIM 6.0	EC000489
UNSPSC	30-21-18-01	eClass 5.1	27-14-11-40
eClass 6.2	27-14-11-40	eClass 7.1	27-14-11-40
eClass 8.1	27-14-11-40	eClass 9.0	27-14-11-40
eClass 9.1	27-14-11-40		

### Approvals

ROHS	Conform
------	---------

### Downloads

Brochure/Catalogue	<a href="#">CAT 1 TERM 16/17 EN</a>
Engineering Data	<a href="#">EPLAN, WSCAD, Zuken E3.S</a>
Engineering Data	<a href="#">STEP</a>
User Documentation	<a href="#">Operating instructions_ZDU1.5-ZDU35_ZQV.pdf</a>