

## **SAID-M8B-5-THR**

#### Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16 D-32758 Detmold

Germany

Fon: +49 5231 14-0 Fax: +49 5231 14-292083 www.weidmueller.com





Weidmüller is now one of the industry's leading international providers of connectors. An important mainstay in this product family are the circular connectors, which Weidmüller groups under the product name SAI. In the development of SAI products, Weidmüller engineers have always concentrated on achieving rational, cost-effective installation concepts, and – in cooperation with major users – have supplied the markets with well-conceived products which set standards in terms of functionality and quality across the globe. The best examples are the new power distributors with S and T coded M12. These modules are characterised by particularly high currents and voltages. This enables them to also be used, for example, with three-phase motors.

## General ordering data

Type	SAID-M8B-5-THR
Order No.	<u>2424000000</u>
Version	Built-in plugs, M8, Socket connector, M 12, No. of poles: 5
GTIN (EAN)	4050118430271
Qty.	25 pc(s).



## **SAID-M8B-5-THR**

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16 D-32758 Detmold

Germany

Fon: +49 5231 14-0 Fax: +49 5231 14-292083 www.weidmueller.com

# **Technical data**

Dim	ensions	and	weights
	011010110	uiiu	***********

Net weight	2.64 g

## **Environmental Product Compliance**

REACH SVHC Lead 7439-92-1

## **Technical data of PCB plug-in connector**

Coding	В	Housings	M8 socket
No. of poles	5	Shield connection	No
Rated voltage	20.1/	Rated voltage (text)	60 V (3-pole) / 30 V (4-,5-
Rated current	30 V	Rated current	and 8-pole) 4 A (3-, 4- and 5-pole) /
	4 A		1.5 A (8-pole)
Temperature range	-2595 ℃	Protection degree	IP67
Contact surface	Au (Gold)	Housing main material	LCP
Connection thread	M8	Tightening torque	M8: 0.5 Nm
Insulation strength		Pollution severity	3 (2 within the sealed
	100 ΜΩ		area)
Plugging cycles	≥ 100	Contact material	CuZn
Lock nut material	Nickel-plated CuZn	Material of the flange-mounted housing	Nickel-plated CuZn

### **Material data**

Contact material	CuZn	Contact surface	Au (Gold)

## **System parameters**

Insulation strength	100 ΜΩ	No. of poles	5	
Pin series quantity	1	Plugging cycles	≥ 100	
Protection degree	IP67			

## Classifications

ETIM 6.0	EC000438	eClass 6.2	27-26-07-02
eClass 9.1	27-44-02-05		

## **Approvals**

ROHS	Conform

## **Downloads**

Brochure/Catalogue	FL FIELDWIRING EN
Engineering Data	<u>STEP</u>



# **SAID-M8B-5-THR**

Weidmüller Interface GmbH & Co. KG


Klingenbergstraße 16 D-32758 Detmold

Germany


Fon: +49 5231 14-0 Fax: +49 5231 14-292083 www.weidmueller.com

# **Drawings**

# **Dimensioned drawing**



# **PCB** design



### Pole scheme

