

# Fuse Cartridges and Gauge Rings for Weidmuller Fuse Terminals

Fuse Inserts For Terminal Type	Size (mm)	Rated voltage (VAC)	Rated current (A)	Part No.
SAKS 1 SAKS 7 ASK 1 WSI 6 ZSI 2.5 	5 x 20	250	0.1 (F)	0430300000
			0.2 (F)	0430400000
			0.25 (F)	0430500000
			0.5 (F)	0430600000
			0.63 (F)	0439000000
			1.0 (F)	0430700000
			1.6 (F)	0430800000
			2.0 (F)	0430900000
			2.5 (F)	0431000000
			3.15 (F)	0431100000
			4.0 (F)	0431200000
			5.0 (F)	0431300000
			6.3 (F)	0431400000
(F) = Fast-acting				
<b>G fuse inserts 5 x 25 with indicator to DIN 41576*</b>				
SAKS 1 SAKS 7 ASK 1 WSI 6 ZSI 2.5 	5x25 with indicator* Breaking capacity 80 A at 250 V, 50 Hz, cos φ = 1	250	0.25 (M)	0546900000
			0.5 (M)	0510300000
			0.8 (M)	0646400000
			1 (M)	0265800000
			10 (M)†	0193100000
			2 (F)	0192700000
			4 (F)	0192800000
			6.3 (F)	0192900000
			(M) = Medium time lag (F) = Fast-acting	
<b>Fuse inserts 11/4" x 1/4" to DEF 63 / size 0 without indicator</b>				
SAKS 3** SAKS 6 WSI 6/2 ZSI 2.5/2 	33 kA short circuit rating fast speed	440	E 0.5 A	0533800000
			E 1 A	0525500000
			E 2 A	0294500000
			E 3 A	0295700000
			E 5 A	0294600000
			E 7 A	0295800000
			E 10 A	0293900000
			<b>D fuse inserts E 16 with indicator to DIN 49360 (Diazed)</b>	
SAKS 2 	E 10 A E 16 A E 20 A E 25 A	500	10	0208500000
			16	0208600000
			20	0208700000
			25	0208800000
<b>D fuse inserts E 14, size D 01, and E 18, size D 02, with indicator to DIN 49522 (Neozed)†</b>				
SAKS 4†† 	E 14/2 E 14/4 E 14/6 E 14/10 E 14/16	380	2	0137400000
			4	0137500000
			6	0328300000
			10	0328400000
			16	0328500000
SAKS 5 	E 18/20 E 18/25 E 18/35 E 18/50 E 18/63	380	20	0361300000
			25	0361400000
			35	0361500000
			50	0361600000
			63	0361700000

Notes: \*The company SIBA supplies 5 x 25 G fuse cartridges also in a shipbuilding version for 450 VAC.




\*\*5 x 30 (500 VAC) fuse cartridge for SAK 3 are available from WICKMANN.

†LINDNER supplies the Neozed fuse cartridges also in a shipbuilding version for 440 VAC.

††Fuse cartridges with the dimensions 1" x 1/4" = 25.4 x 6.35 mm and 13/32" x 1 1/2" = 10.3 x 38.1 mm are not included in our product range.

‡Only for SAKS 1 and SAKS 7.

## Gauge Ring

For Terminal Type	Gauge ring type	Amp.	Color	Part No.
SAKS 4 and 4/35 	P 14/2	2	Pink	0138000000
	P 14/4	4	Brown	0138100000
	P 14/6	6	Green	0328600000
	P 14/10	10	Red	0328700000
SAKS 5 and 5/35 	P 18/20	20	Blue	0361800000
	P 18/25	25	Yellow	0361900000
	P 18/35	35	Black	0362000000
	P 18/50	50	White	0362100000
	P 16/10	10	Red	0208900000
SAKS 2 and 2/35 	P 16/16	16	Gray	0209000000
	P 16/20	20	Blue	0209100000