LTD-6000 SERIES

0.56" DUAL DIGIT NUMERIC DISPLAYS

T.41-33


FEATURES

- 0.56 INCH (14,2mm) DIGIT HEIGHT.
- CHOICE OF SIX BRIGHT COLORS-RED/BRIGHT RED/GREEN/YELLOW/ORANGE/HIGH EFFICIEN-CY RED.
- . LOW POWER REQUIREMENT.
- EXCELLENT CHARACTERS APPEARANCE.
- CATEGORIZED FOR LUMINOUS INTENSITY.
- I.C. COMPATIBLE.
- EASY MOUNTING ON P.C. BOARD OR SOCKETS.

DESCRIPTION

The LTD-6000, series are 0.56 inch (14.2mm) heigh, dual digit displays.

The red series devices utilize LED chips which are made from GaAsP on a GaAs substrate. The bright red and green series devices utilize LED chips which are made from GaP on a transparent GaP substrate. The yellow, orange and high efficiency red series devices are utilize LED chips which are made from GaAsP on a transparent GaP substrate. Red and bright red displays have black face and red segment color. Green and yellow displays have gray face and white segment color. Orange displays have orange face and orange segment color. High efficiency red displays have red face and red segment color.






DEVICES

		PART N	O. LTD.				INTERNAL
RED	BRIGHT RED	GREEN	YELLOW	ORANGE	HIEFF. RED	DESCRIPTION	CIRCUIT DIAGRAM
6710R	6710P	6410G	6810Y	6610E	6910HR	Common Anode, Rt. Hand Decimal	Α
6730R	6730P	6430G	6830Y	6630E	6930HR	Common Anode, ±1.8 Overflow	В
6740R	6740P	6440G	6840Y	6640E	6940HR	Common Cathode, Rt. Hand Decimal	c
6750R	6750P	6450G	6850Y	6650E	6950HR	Common Cathode, ±1.8 Overflow	D

5-128

PACKAGE DIMENSIONS

LTD-6×10/6×30/6×40/6×50



NOTE: All dimensions are in millimeters (inches) tolerance are:

1. Lead length (from seating plane):

minimum value
$$\frac{+1.00 \text{ mm}}{-0.00}$$

$$(\frac{+0.040''}{-0.000''})$$


2. $\frac{\pm 0.25 \text{ mm}}{(0.010'')}$ unless otherwise noted.


PIN CONNECTION

PIN		CONI	NECTION	
NO.	A. LTD-6x10	B. LTD-6x30	C. LTD-6x40	D, LTD-6x50
1. 1.	Cathode E (Digit 1)	Cathode G (Digit 1)	Anode E (Digit 1)	Anode G (Digit 1)
2	Cathode D (Digit 1)	Cathode J. H (Digit 1)	Anode D (Digit 1)	Anode J. H (Digit 1)
3	Cathode C (Digit 1)	Cathode C (Digit 1)	Anode C (Digit 1)	Anode C (Digit 1)
4	Cathode D.P. (Digit 1)	Cathode D.P. (Digit 1)	Anode D.P. (Digit 1)	Anode D.P. (Digit 1)
5	Cathode E (Digit 2)	Cathode E (Digit 2)	Anode E (Digit 2)	Anode E (Digit 2)
6	Cathode D (Digit 2)	Cathode D (Digit 2)	Anode D (Digit 2)	Anode D (Digit 2)
7	Cathode G (Digit 2)	Cathode G (Digit 2)	Anode G (Digit 2)	Anode G (Digit 2)
- 8	Cathode C (Digit 2)	Cathode C (Digit 2)	Anode C (Digit 2)	Anode C (Digit 2)
9	Cathode D.P. (Digit 2)	Cathode D.P. (Digit 2)	Anode D.P. (Digit 2)	Anode D.P. (Digit 2)
10	Cathode B (Digit 2)	Cathode B (Digit 2)	Anode B (Digit 2)	Anade B (Digit 2)
11	Cathode A (Digit 2)	Cathode A (Digit 2)	Anode A (Digit 2)	Anode A (Digit 2)
12	Cathode F (Digit 2)	Cathode F (Digit 2)	Anode F (Digit 2)	Anode F (Digit 2)
13	Common Anode (Digit 2)	Common Anode (Digit 2)	Common Cathode (Digit 2)	Common Cathode (Digit 2)
14	Common Anode (Digit 1)	Common Anode (Digit 1)	Common Cathode (Digit 1)	Common Cathode (Digit 1)
15	Cathode B (Digit 1)	Cathode B (Digit 1)	Anode B (Digit 1)	Anode B (Digit 1)
16	Cathode A (Digit 1)	No Connection	Anode A (Digit 1)	No Connection
17	Cathode G (Digit 1)	No Connection	Anode G (Digit 1)	No Connection
18	Cathode F (Digit 1)	No Connection	Anode F (Digit 1)	No Connection


5-129 792

INTERNAL CIRCUIT DIAGRAM






C. LTD-6x40



D. LTD-6x50





ABSOLUTE MAXIMUM RATINGS AT TA = 25°C

S PARAMETER	RED	BRIGHT RED	GREEN	YELLOW	ORANGE	HIEFF. RED	UNIT
Power Dissipation Per Segment	55,	40	75	60	75	75	mW
Peak Forward Current Per Segment (1/10 Duty Cycle, 0.1ms Pulse Width)	160	60	100	80	100	100	mA
Continuous Forward Current Per Segment	25	15	25	20	25	25	mA
Derating Linear From 25°C Per Segment	0.3	0.18	0.3	. 0.24	0.3	0,3	mA/°C
Reverse Voltage Per Segment	5	5	5	5	5	5	٧
Operating Temperature Range				–25°C to +8	5°C		
Storage Temperature Range				25°C to +8	5°C		la j sa
Solder Temperature 1/16 inch Below Seatin	ng Plane	for 3 Secon	ds at 260°	c ·			


5-130

ELECTRICAL/OPTICAL CHARACTERISTICS AT TA = 25°C LTD-6700R SERIES

PARAMETER	SYMBOL	MIN.	түр.	MAX.	UNIT	TEST CONDITION
Average Luminous Intensity	İv	200	600		μcd	IF = 10 mA
Peak Emission Wavelength	λρ		655		nm	IF = 20 mA
Spectral Line Half-Width	Δλ		24		nm	IF = 20 mA
Forward Voltage, any Segment	Vŕ		1.7	2.0	V	(F = 20 mA
Reverse Current, any Segment	Į R			100	μА	VR = 5 V
Luminous Intensity Matching Ratio	lv-m			2:1		IF = 20 mA

TYPICAL ELECTRICAL/OPTICAL CHARACTERISTIC CURVES

(25°C Ambient Temperature Unless Otherwise Noted)



Ambient Temperature (Ta) - °C Duty Cycle %


Fig. 4 MAX. ALLOWABLE DC CURRENT PER SEG. Fig. 5 MAX. PEAK CURRENT Vs. DUTY CYCLE.% Fig. 6 LUMINOUS INTENSITY Vs. DUTY CYCLE% (AVERAGE I_F = 10mA PER SEG.)

ELECTRICAL/OPTICAL CHARACTERISTICS AT TA = 25°C LTD-6700P SERIES


PARAMETER	SYMBOL	MIN,	TYP.	MAX.	UNIT	TEST CONDITION
Average Luminous Intensity	lv	300	950		μcđ	1F = 10 mA
Peak Emission Wavelength	λр		697		nm	IF = 20 mA
Spectral Line Half-Width	Δλ		90		nm	IF = 20 mA
Forward Voltage, any Segment	VF		2,1	2.8	V	IF = 20 mA
Reverse Current, any Segment	l R			100	μΑ	VR=5V
Luminous Intensity Matching Ratio	lv-m			2:1		IF = 20 mA

TYPICAL ELECTRICAL/OPTICAL CHARACTERISTIC CURVES

(25° C Ambient Temperature Unless Otherwise Noted)




80 Relative Output 60 40 20 720




 $\label{eq:forward_voltage} Forward\ \mbox{Voltage}\ (\mbox{V}_{\mbox{\sc F}})\ -\ \mbox{Volts}$ Fig. 1 FORWARD CURRENT Vs. FORWARD VOLTAGE.

Wavelength (λ) — nm. Fig. 2 SPECTRAL RESPONSE.

Forward Current (IF) — mA Fig. 3 RELATIVE, LUMINOUS INTENSITY Vs. FORWARD CURRENT (PER SEGMENT).





Ambient Temperature (Ta) - °C Duty Cycle % Fig. 4 MAX. ALLOWABLE DC CURRENT PER SEG. Fig. 5 MAX. PEAK CURRENT Vs. DUTY CYCLE.% Vs AMBIENT TEMPERATURE. (REFRESH RATE - F = 1 KHz)


5-132

ELECTRICAL/OPTICAL CHARACTERISTICS AT TA = 25°C LTD-6400G SERIES

PARAMETER	SYMBOL	MIN.	TYP,	MAX.	UNIT	TEST CONDITION
Average Luminous Intensity	lv .	-800,	2400		μcd	l F = 10 mA
Peak Emission Wavelength	λρ		565		nm	IF = 20 mA
Spectral Line Half-Width	Δλ		30		nm	IF = 20 mA
Forward Voltage, any Segment	V F		2.1	2,8	V	1F = 20 mA
Reverse Current, any Segment	lR ,			100	μΑ	VR = 5 V
Luminous Intensity Matching Ratio	lv-m			2:1		IF = 20 mA

TYPICAL ELECTRICAL/OPTICAL CHARACTERISTIC CURVES

(25°C Ambient Temperature Unless Otherwise Noted)



Ambient Temperature (Ta) - °C Duty Cycle %


Fig. 4 MAX. ALLOWABLE DC CURRENT PER SEG. Fig. 5 MAX. PEAK CURRENT Vs. DUTY CYCLE.% Fig. 6 LUMINOUS INTENSITY Vs. DUTY CYCLE% Vs. AMBIENT TEMPERATURE. (REFRESH RATE - F = 1 KHz) (AVERAGE I_F = 10mA PER SEG.)

ELECTRICAL/OPTICAL CHARACTERISTICS AT TA = 25°C LTD-6800Y SERIES


PARAMETER	SYMBOL	MIN.	TYP.	MAX.	UNIT	TEST CONDITION
Average Luminous Intensity	ίν	800	2400		μcd	1F = 10 mA
Peak Emission Wavelength	λр		585		nm	IF = 20 mA
Spectral Line Half-Width	Δλ		35		em	I = 20 mA
Forward Voltage, any Segment	Vε		2.1	2.8	V	IF = 20 mA
Reverse Current, any Segment	ſŖ			100	μA	VR = 5 V
Luminous Intensity Matching Ratio	lv-m			2:1		IF = 20 mA

TYPICAL ELECTRICAL/OPTICAL CHARACTERISTIC CURVES

(25°C Ambient Temperature Unless Otherwise Noted)




60 40 720





Forward Voltage $\{V_{\rm F}\}$ — Volts Fig. 1 FORWARD CURRENT Vs. FORWARD VOLTAGE.

Wavelength (λ) - nm. Fig. 2 SPECTRAL RESPONSE.

Forward Current (I_F) — mA Fig. 3 RELATIVE LUMINOUS INTENSITY Vs. FORWARD CURRENT (PFR SEGMENT),







Ambient Temperature (Ta) -- °C Duty Cycle % Duty Cycle %

Fig. 4 MAX. ALLOWABLE DC CURRENT PER SEG. Fig. 5 MAX. PEAK CURRENT Vs. DUTY CYCLE.% Fig. 6 LUMINOUS INTENSITY Vs. DUTY CYCLE% Vs AMBIENT TEMPERATURE. (REFRESH RATE - F = 1 KHz) (AVERAGE I_F = 10mA PER SEG.)


5-134

ELECTRICAL/OPTICAL CHARACTERISTICS AT TA = 25°C LTD-6600E SERIES

PARAMETER	SYMBOL	MIN.	TYP,	MAX.	ÚNIT	TEST CONDITION
Average Luminous Intensity	ly .	800	2400		μcd	IF = 10 mA
Peak Emission Wavelength	λр		630		nm	IF = 20 mA
Spectral Line Half-Width	Δλ		40		nm	[F = 20 mA
Forward Voltage, any Segment	Vπ		2,1	2.8	٧	IF = 20 mA
Reverse Current, any Segment	l F			100	μΑ	Vn = 5 V
Luminous Intensity Matching Ratio	lv-m			2:1		IF = 20 mA

TYPICAL ELECTRICAL/OPTICAL CHARACTERISTIC CURVES

(25°C Ambient Temperature Unless Otherwise Noted)



Ambient Temperature (Ta) - °C Duty Cycle % Duty Cycle %


Fig. 4 MAX. ALLOWABLE DC CURRENT PER SEG. Fig. 5 MAX. PEAK CURRENT Vs. DUTY CYCLE.% Fig. 6 LUMINOUS INTENSITY Vs. DUTY CYCLE% (AVERAGE I_F = 10mA PER SEG.)

ELECTRICAL/OPTICAL CHARACTERISTICS AT TA = 25°C LTD-6900HR SERIES


PARAMETER	SYMBOL	MIN.	TYP,	MAX.	UNIT	TEST CONDITION
Average Luminous Intensity	lv	800	2400		µсd	IP = 10 mA
Peak Emission Wavelength	λρ		635		nmı	lF = 20 mA
Spectral Line Half-Width	Δλ		40		nm	IF = 20 mA
Forward Voltage, any Segment or D.P.	VF		2.1	2.8	V	LF = 20 mA
Reverse Current, any Segment or D.P.	l R			100	μA	Vn = 5 V
Luminous Intensity Matching Ratio	lv-m			2:1		tr = 20 mA

TYPICAL ELECTRICAL/OPTICAL CHARACTERISTIC CURVES

(25°C Ambient Temperature Unless Otherwise Noted)




Relative Output 60 40





Forward Voltage (V_F) - Volts Fig. 1 FORWARD CURRENT Vs. FORWARD VOLTAGE.

Wavelength (λ) - nm. Fig. 2 SPECTRAL RESPONSE.

Forward Current (Is) - mA Fig. 3 RELATIVE, LUMINOUS INTENSITY Vs. FORWARD CURRENT (PER SEGMENT).







Ambient Temperature (Ta) -- °C Duty Cycle %

Fig. 4 MAX. ALLOWABLE DC CURRENT PER SEG. Fig. 5 MAX. PEAK CURRENT Vs. DUTY CYCLE.% Fig. 6 LUMINOUS INTENSITY Vs. DUTY CYCLE%

Vs AMBIENT TEMPERATURE. (REFRESH RATE - F = 1 KHz)

15-136

PACKAGING E

T.90-20

Reel Packaging (Axial Lead Units)


DEVICE	COMPONENT SPACE (MM)	TAPE SPACE (MM)	REEL DIA (MM)	QUANTITY (EA)		CARTON		
TYPE	"A"	"B"	"D"	REEL	CARTON	SIZE (MM)	WEIGHT (KG)	
DO-41 . DO-41L	5±0.5	52.4±1.5	326~336	5000	20K	355 x 355 x 355	10.5	
DO-201AD	10 4.5	52.4±1.5	326~336	1200	4.8K	355 x 355 x 355	9.0	
P6(Aleg)	10. ±0.5	52.4±1.5	326~336	700	2.8K	355 x 355 x 355	8,8	


The C dimension of Fig. 3 is between 3.17m.m. and 635mm greater than the length of the component involved.



FIG.2

FIG. 3







Bulk Packaging (Axial Lead Devices and Bridge Rectifiers)

DEVICE	PACKAGIN	G SIZE (MM)	QUAN	NTITY (EA)	APPROX GRO	SS WEIGHT (KG
TYPE	вох	CARTON	вох	CARTON	вох	CARTON
DO-41L	196 x 84 x 20	450 x 210 x 250	1000	50K	0.38	20
DO-201AD	305 x 93 x 59	. 355 x 355 x 355	1000	20K	1,35	28
P6(Aleg)	305 x 93 x 59	355 x 355 x 355	500	10K	1.2	24.5
PBM	357 x 125 x 60	530 x 360 x 340	1000	20K	1.5	32.3
PBDF	495 x 155 x 145	500 x 325 x 305	5000	20K	5.1	21,5
РВР	357 x 125 x 60	530 x 360 x 340	500	10K	1.5	31.5
PBL	375 x 220 x 155	470 x 385 x 455	1000	5K	5.7	30.5
PBPC-6	357 x 125 x 60	560 x 360 x 340	250	5K	1.1	22
PBPC-8	357 x 125 x 60	560 x 360 x 340	250	5K	1.7	35
KBPC	375 x 220 x 365	470 x 390 x 385	500	1K	15.1	31.5
KBPC-W	375 x 220 x 365	470 x 390 x 385	500	1K	14.5	30.0

AMMO BOX PACKAGING

BOX SIZE





Unit:m. m.


Packaging	Products Outline	Dimension *A*	. Dimension	Dimension	Q'ty per BOX
26MM Horizontal	00-41	255	. 50	0.5	3K
Ammo Pack	DO-41L(0.6mm Lead)	200	50	95	3K
'52MM Horizontal	DO -41and DO -41L	250	76		3 ['] K
Ammo Pack	DO 201AD ·	250	75	92	0.8K

CARTON SIZE

Unit:M. m.

Packaging	Products Outline	length	Width	High	Q'ty Per Carton	
26MM Horizontal Ammo Pack	DO-41 DO-41L(0.6mm Lead)	330	310	268	42K	
52MM Horizontal Ammo Pack	DO-41and DO-41L	355	255	240	48K	
	DO 201AD		355	340	12K	

PREFORMED LEAD DRAWING



Case type	Preformed type	A _(mm)		B _ (mm)		·C (mm)			D (mm)		R (mm)
		range	tolerance	range	tolerance	range	tolerance	range	tolerance	range	tolerance
D041	М	9.0-20.0	1.0	8.0-22.0	±0.5	-	-	1.5	max	_	_
	E	11.0-20.0	±1.0	11.0-16.0	±1.0	4.0-5.0	±0.5	1.5	max		-
	В	7.5	±0.5	19.0-22.0	±0,5	7.5	±0.5	1.5	max	2,5-4,0	Тур
	С	4.5	±0.8	18,0-19.0	±0.5	9 0	±0,5	1.5	max	2,5-4.0	Тур
D O201AD	M	15.0-20.0	±1.0	8.0-22.0	±1.0	→	_	2.0	max	_	_
	. E	15.0-20.0	±1.0	10.0-22.0	±1.0	3.0-15.0	±0.5	2.0	max	-	-
P6(Aleg)	М	15.0-20.0	±1.0	8.0-22.0	±1.0			2.0	max		_