

Search Results

- Evaluate
 - FAQ's
- Design a Solution
 - Part Drawings
- How to Buy
 - Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click to remove) Search Tips Within Results

Right Angle Female Disconnect, Nylon Fully Insulated – Funnel Entry > Text Search: 'DNFR14-205FIB-L'

Refine By

- RoHS Compliancy St ..
- Product Type
- Depth (In.)
- Depth (mm)
- Height (In.)
- Height (mm)
- Length (In.)
- Length (mm)
- Width (In.)
- Width (mm)
- Insulation
- Max. Ins. (mm)
- Plating Type
- Tab Size (In.)
- Tab Size (mm)
- Wire Range
- Wire Range (mm) ..


Search Results

2 Records found.

1. [DNFR14-205FIB-L](#)



- RoHS Compliancy Status Compliant
 - Note DNFR14-205FIB-L replaces DNFR14-205FIB-C
 - Part Description Female Disconnect, right angle, nylon fully insulated, funnel entry, 16 – 14 AWG, .205 x .032 tab size.
- Product Type Disconnects
- Depth (In.) 0.60
- Depth (mm) 15.2
- Height (In.) 0.21
- Height (mm) 5.3
- Length (In.) 0.58
- Length (mm) 14.7
- Width (In.) 0.37
- Width (mm) 9.4
- Insulation nylon
- Max. Ins. (mm) 4.58
- Plating Type Tinned
- Tab Size (In.) 0.205/0.187 x 0.032
- Tab Size (mm) 5.2/4.7 x 0.8
- Wire Range 16 – 14 AWG
- Min. Order UOM PC
- Min. Order Qty. 50

2.  [Part Drawings: Right Angle Female Disconnect, Nylon Fully Insulated - Funnel Entry - DNFR-FIB - pdf](#)