







| PART NUMBER   | SEE DETAIL | MATERIAL | "A"  | "B"  | MARKER ACROSS | TUBING COLOR |
|---------------|------------|----------|------|------|---------------|--------------|
| H200X025H1T   | A          | GMUHS    | 2.00 | 3.50 | 1             | WHITE        |
| H100X025H1T   | B          | GMUHS    | 1.00 | 3.50 | 2             | WHITE        |
| H050X025H1T   | C          | GMUHS    | 0.50 | 3.50 | 4             | WHITE        |
| H150X025H1T   | A          | GMUHS    | 1.50 | 3.50 | 1             | WHITE        |
| H075X025H1T   | B          | GMUHS    | 0.75 | 3.50 | 2             | WHITE        |
| H200X025H2T   | A          | GMUHS    | 2.00 | 3.50 | 1             | YELLOW       |
| H100X025H2T   | B          | GMUHS    | 1.00 | 3.50 | 2             | YELLOW       |
| H050X025H2T   | C          | GMUHS    | 0.50 | 3.50 | 4             | YELLOW       |
| H200X025H3T   | A          | GMUHS    | 2.00 | 3.50 | 1             | BLACK        |
| H200X025H1T-B | A          | GMUHS    | 2.00 | 3.50 | 1             | WHITE        |
| H100X025H1T-B | B          | GMUHS    | 1.00 | 3.50 | 2             | WHITE        |
| H050X025H1T-B | C          | GMUHS    | 0.50 | 3.50 | 4             | WHITE        |
| H150X025H1T-B | A          | GMUHS    | 1.5  | 3.50 | 1             | WHITE        |
| H075X025H1T-B | B          | GMUHS    | 0.75 | 3.50 | 2             | WHITE        |

NOTE:  
1. SEE MFG. DRAWING NO. A61336.

|                                                                                                                    |  |  |  |  |                                                                                              |  |  |                  |  |
|--------------------------------------------------------------------------------------------------------------------|--|--|--|--|----------------------------------------------------------------------------------------------|--|--|------------------|--|
| CAD FILENAME/LAYERS<br>100472MP_C10432_HxxxxX025HxT_00.PRT                                                         |  |  |  |  |                                                                                              |  |  |                  |  |
| PANDUIT CORP TINLEY PARK, ILLINOIS                                                                                 |  |  |  |  |                                                                                              |  |  |                  |  |
| CUSTOMER DRAWING H***X025H** OPTIMUM<br>COMPUTER PRINTABLE MIL. SPEC.<br>HEAT SHRINK MARKERS                       |  |  |  |  |                                                                                              |  |  |                  |  |
| UNLESS OTHERWISE SPECIFIED,<br>DIMENSIONAL TOLERANCES ARE:<br>(.X) ± 0.1 (XXX) ± 0.005<br>(.XX) ± 0.01 ANGLES ± 1° |  |  |  |  | UNLESS OTHERWISE SPECIFIED,<br>ALL DIMENSIONS ARE GIVEN IN<br>INCHES, THIRD ANGLE PROJECTION |  |  |                  |  |
| DRAWN BY<br>RVU                                                                                                    |  |  |  |  | MAT'L:<br>SEE TABLE                                                                          |  |  | SCALE<br>NTS     |  |
| DATE<br>8-1-06                                                                                                     |  |  |  |  | DRAWING NO.<br>C10432                                                                        |  |  | DWG<br>SIZE<br>C |  |
| REV<br>O                                                                                                           |  |  |  |  | DATE<br>8-1-06                                                                               |  |  | CHK'D            |  |
| BY<br>RVU                                                                                                          |  |  |  |  | DESCRIPTION<br>DRAWING RELEASE.                                                              |  |  | ECN<br>4613      |  |
| CHK<br>RVU                                                                                                         |  |  |  |  | R<br>R                                                                                       |  |  | CUST<br>CUST     |  |
|                                                                                                                    |  |  |  |  |                                                                                              |  |  | SUP<br>SUP       |  |
|                                                                                                                    |  |  |  |  |                                                                                              |  |  | GMBH<br>GMBH     |  |