



# Si50122-Ax-EVB USER'S GUIDE

#### Description

Si50122-Ax is a high performance, crystal-less PCIe clock generator with internal CMEMS that can generate two 100 MHz HCSL and one 25 MHz LVCMOS clock outputs.

This document is intended to be used in conjunction with the Si50122-Ax-EVB, Si50122 device, and data sheet for the following tests:

- PCIe Gen 1, Gen 2, Gen 3 compliancy
- Power consumption test
- Jitter performance


The Si50122-Ax-EVB is used to evaluate the Si50122-Ax. Table 1 shows the device part number and corresponding evaluation board part number.

| Device Part<br>Number | PCIe Compliant | Spread Spectrum | EVB Orderable Part<br>Number |  |
|-----------------------|----------------|-----------------|------------------------------|--|
| Si50122-A1-GM         | Gen 1          | No              | Si50122-A3-EVB               |  |
| Si50122-A2-GM         | Gen 1          | Yes             | Si50122-A4-EVB               |  |
| Si50122-A3-GM         | Gen 1/2        | No              | Si50122-A3-EVB               |  |
| Si50122-A4-GM         | Gen 1/2        | Yes             | Si50122-A4-EVB               |  |
| Si50122-A5-GM         | Gen 1/2/3      | No              | Si50122-A5-EVB               |  |
| Si50122-A6-GM         | Gen 1/2/3      | Yes             | Si50122-A6-EVB               |  |

 Table 1. Evaluation Board Orderable Part Number

# Si50122-Ax-EVB

## 1. Front Panel



### Figure 1. Evaluation Module Front Panel

To use Si50122-Ax-EVB:

- 1. Check to confirm that the device part number to be evaluated corresponds to the evaluation board refer to Table 1.
- 2. Power up the EVB using the VCC and GND pins.
- 3. View and measure the outputs via the SMA connectors.



## 2. Schematics





Figure 2. Si50122 Device Connection



## 3. Bill of Materials

| ltem | Qty | Ref | Part       | Rating | Tol     | PCB             | Manufacturer Part | Mfr        |
|------|-----|-----|------------|--------|---------|-----------------|-------------------|------------|
|      |     |     |            |        |         | Footprint       | Number            |            |
| 1    | 1   | C1  | 0.1 µF     | 16 V   | ±10%    | 0402            | C0402X7R160-104K  | Venkel     |
|      |     | C2  | 2.2 pF     | 50 V   | ±0.1 pF | 0402            | C0402C0G500-2R2B  |            |
|      |     | C3  | 2.2 pF     |        |         |                 |                   |            |
| 2    | 4   | C4  | 2.2 pF     |        |         |                 |                   | Venkel     |
|      |     | C5  | 2.2 pF     |        |         |                 |                   |            |
|      |     | C6  | 2.2 pF     |        |         |                 |                   |            |
|      |     | JP1 | HEADER 1x2 | NA     | NA      | NA              | TSW-102-07-G-S    |            |
| 3    | 2   |     |            |        |         |                 |                   | Samtec     |
|      |     |     |            |        |         |                 |                   |            |
| 4    | 5   | J1  | SMA        | NA     | NA      | NA              | 142-0701-801      | Johnson    |
|      |     |     |            |        |         |                 |                   | Components |
|      |     | J2  | SMA        |        |         |                 |                   |            |
|      |     | J3  | SMA        |        |         |                 |                   |            |
|      |     |     |            |        |         |                 |                   |            |
|      |     | J4  | SMA        |        |         |                 |                   |            |
|      |     | J5  | SMA        |        |         |                 |                   |            |
|      |     |     | _          |        |         |                 |                   |            |
| 5    | 1   | C7  | 1 µF       | 6.3 V  | ±10%    | 0402            | C0402X5R6R3-105K  | Venkel     |
| 6    | 1   | R1  | 33 Ω       | 1/16 W | ±5%     | 0402            | CR0402-16W-330J   | Venkel     |
| 7    | 1   | FB1 | 1000 Ω     | 200 mA |         | 0402            | BLM15AG102SN1     | Murata     |
| 8    | 1   | U1  | Si50122    | NA     | NA      | 3X3 10-<br>TDFN | Si50122           | Si Labs    |





#### Disclaimer

Silicon Laboratories intends to provide customers with the latest, accurate, and in-depth documentation of all peripherals and modules available for system and software implementers using or intending to use the Silicon Laboratories products. Characterization data, available modules and peripherals, memory sizes and memory addresses refer to each specific device, and "Typical" parameters provided can and do vary in different applications. Application examples described herein are for illustrative purposes only. Silicon Laboratories reserves the right to make changes without further notice and limitation to product information, specifications, and descriptions herein, and does not give warranties as to the accuracy or completeness of the included information. Silicon Laboratories shall have no liability for the consequences of use of the information supplied herein. This document does not imply or express copyright licenses granted hereunder to design or fabricate any integrated circuits. The products must not be used within any Life Support System without the specific to result in significant personal injury or death. Silicon Laboratories products are generally not intended to support or sustain life and/or health, which, if it fails, can be reasonably expected to result in significant personal injury or death. Silicon Laboratories products are generally not intended for military applications. Silicon Laboratories shall under no circumstances be used in weapons of mass destruction including (but not limited to) nuclear, biological or chemical weapons, or missiles capable of delivering such weapons.

#### **Trademark Information**

Silicon Laboratories Inc., Silicon Laboratories, Silicon Labs, SiLabs and the Silicon Labs logo, CMEMS®, EFM, EFM32, EFR, Energy Micro, Energy Micro logo and combinations thereof, "the world's most energy friendly microcontrollers", Ember®, EZLink®, EZMac®, EZRadio®, EZRadioPRO®, DSPLL®, ISOmodem ®, Precision32®, ProSLIC®, SiPHY®, USBXpress® and others are trademarks or registered trademarks of Silicon Laboratories Inc. ARM, CORTEX, Cortex-M3 and THUMB are trademarks or registered trademarks of ARM Holdings. Keil is a registered trademark of ARM Limited. All other products or brand names mentioned herein are trademarks of their respective holders.



Silicon Laboratories Inc. 400 West Cesar Chavez Austin, TX 78701 USA

### http://www.silabs.com