

SPECIFICATION FOR APPROVAL

CUSTOMER

DESCRIPTION: DC BRUSHLESS BLOWER

DIMENSIONS : 35X35X7 mm

MODEL: GB0535ADV3-8

APPROVED NO :

APPROVED BY:

(AUTHORIZED)

研發部型	· (外銷部 文件轉發行章 89.6.12
DAWN Yuchen 4/8 CHKD. (APPD. APPD.)	SPEC. NO. ISSUE DATE EDITION	B350106 01.17.2000
建準電機工業股份有限公司	REVISE DATE E.SPEC	EB10107

SUNONWEALTH ELECTRIC MACHINE INDUSTRY CO., LTD.

12FL., 120 CHUNG CHENG 1ST RD., TEL:886-7-7163069(41 LINES)

KAOHSIUNG, TAIWAN, R. O. C. FAX:886-7-7163086~89

外銷部

DC BRUSHLESS BLOWER

MODEL: GB0535ADV3-8

CHARACTERISTICS

1. Motor Design

Patented single-coil DC brushless 8 poles motor

design.

2. Insulation Resistance

More than 500M ohm between internal stator and

lead wire(+) measured by DC 500V.

3. Dielectric Strength

Applied AC 500V for one minute or AC 600V for

2 seconds between housing and lead wire(+)

4. Noise Level

Measured in an semi-an echoic chamber

with background noise level below 15

dB(A). The fan is running in free air with

microphone at a distance of one meter

from the fan intake.

5. Input power, Current & Speed

Measured after continuous 30 minutes

operation at rated voltage in clean air

at ambient temperature of 25 degree 文件轉發行章

6. Tolerances

±15% on rated power and current.

7. Motor Protection

Locked rotor protected.

8. Air Performance

Measured by a double chamber. The value

are recorded when the fan speed is stabilize

at rated voltage.

建準電機工業股份有限公司 SUNONWEALTH ELECTRIC MACHINE INDUSTRY CO., LTD.

			_	-
SPEC. NO.	B350106	REVISE DA	TE	8
ISSUE DATE	01. 17. 2000	EDITIO	1 7	0
PAGE	2 OF 6		12	•

MODEL: GB0535ADV3-8

1-1. Rated Voltage : 5 VDC

1-2. Operating Voltage Range : 3-6 VDC

1-3. Starting Voltage : 3 VDC

1-4. Speed (Reference Value) : 5000 RPM

1-5. Air Delivery : 0.8 CFM

1-6. Static Pressure : 0.13 Inch-H₂O

1-7. Rated Current : 0.05 AMP

1-8. Rated Power : 0.25 WATTS

1-9. Noise Level : 19.5 dB(A)

1-10. Direction of Rotation : Counter-clockwise viewed front fan blade

14

1-11. Operating Temperature : -10 to +90 Deg.C

1-12. Storage Temperature : -40 to +90 Deg.C

1-13. Bearing System : Vapo bearing system

1-14. Weight : 12g

1-15. Safety : UL/CUR/TUV/CE Approva

1-16. Vibration : Vibration of acceleration 1.5G and

Frequency 5~50~5Hz is applied in the 3 directions(X,Y,Z) for 30 minutes, each

外銷部


Direction at the cycle of 1 minut

			<i>-</i>	工 赞 部 辿
建準電機工業股份有限公司	SPEC. NO.	B350106	REVISE DAT	ΓΕ 804.40872 000
	ISSUE DATE	01. 17. 2000	EDITION	311/-
MACHINE INDUSTRY CO., LTD.	PAGE	3 OF 6	\	14 11 11

MODEL: GB0535ADV3-8

PERFORMANCE CURVES

STATIC PRESSURE



				Top B	开發部門
建準電機工業股份有限公司	SPEC. NO.	B350106	REVISE DA	E g	0 1 22
SUNONWEALTH ELECTRIC	ISSUE DATE	01. 17. 2000	EDITION	0	7, 4, 21
MACHINE INDUSTRY CO., LTD.	PAGE	4 OF 6		【被	1

MATERIAL


2-1. Frame : DIE-CAST ALUMINUM


2-2. Impeller : Thermoplastic PBT of UL 94V-0

2-3. Bobbin : Thermoplastic PBT of UL 94V-0

2-4. Lead Wire : UL3265,28AWG,+RED;-BLACK

DIMENSIONS





外銷部 文件轉發行章 89.6.12

1.One directional exhaust

2. The Best Mounting Direction: Fan blade face up or shaft horizontal

			OMILO	TITI I	一致部多
建準電機工業股份有限公司	SPEC. NO.	B350106	REVISE DA	ΓE	89. 4 27
SUNONWEALTH ELECTRIC	ISSUE DATE				X
MACHINE INDUSTRY CO., LTD.	PAGE	5 OF 6		7	技术

Notes

- 1. SUNON will not guarantee the products if the application of our products is exceeded the limitation which is specified on this specification.
- 2. In case of change of the specification specified on this document, a written notice is requested in advance.
- 3. Please do not touch the impeller with pressure and never bring the fan with lead wire. The bearings and lead wire may be damaged.
- 4. No guarantee on the products against the safety problem or failure caused by powder dust, drop of water or insect.
- 5. If there is any data or related documentation different from this data sheet, this data sheet is the principal reference.
- 6. For the purpose of MIS, please indicate SPEC No. on every order.
- 7. In case of the fan has no polarity protection function, wires with same color (electrode) must be connected together during the assembly. (i.e. red + red, black + black) or the fan will be damaged immediately.
- 8. Please do not use the fan in the environment of corrosive gas or liquid or any detrimental gas.
- 9. Please do not store the fan in the environment of high / low temperature, high humidity or any detrimental gas. Please store the fan within 6 months, every 6 months, there shall be a linkage of electric current to the fan, even though the fan is stored in room temperature.
- 10. While the fan is in operation, please do not lock the fan intentionally for a long period of time, since the continuous stoppage will result in over-heat and thus burn-out of the fan intentionally for a long period of
- 11. During the installation of the fan, please pay substantial attention to possible noise 6. 12 cause by resonance vibration and vibration.
- 12. During the testing of the fan, please be sure to use finger guard to insure safety.
- 13. Unless otherwise specified, if there is any doubt in the judgement, the temperature particles relative humidity range of environment will be take in according to the standard test condition as 25°C and 65%.

建準電機工業股份有限公司	SPEC. NO.	B350106	REVISE DAT	B9, 4, 27
	ISSUE DATE	01. 17. 2000	EDITION	整行
MACHINE INDUSTRY CO., LTD.	PAGE	6 OF 6		7