

VME64-M EXTENDER VECTORBORD®



6U Overall, VME64x J1/J2/J0 (click on image to enlarge)

KEY FEATURES:

- Excellent performance with a multi layer design
- Individual signal tracking with interruption option
- Voltage & Current measuring facilities
- Full ground plane
- Signal pin-out identification silkscreen onto outer PCB layers
- Jumper Blocks provided to allow signal line interrogation
- Max. current per contact @ nominal 50° C = 1.75A
- Controlled impedence, Signal trace shielding
- Voltage rating 200 RMS or 300 VDC
- DOWNLOAD DATASHEET

BOARD SPECIFICATIONS:

- Material: FR-4 Epoxy Glass
- PCB UL94V-0, PCB RoHS Compliant
- PCB exposed Copper areas plated with Immersion Gold

MECHANICAL SPECIFICATIONS:

- → Board Height 6U (9.187") (233.35mm)
- Board Length 11.75" (298mm)
- → PCB Thickness 0.062" (1.6mm)
- Card Extender brackets (arms) on top & bottom (P/N: 5210211)