

NOTES:


1) LABEL REQUIREMENT:

- LABELS ARE M23053/5 ,WHITE. ACCEPTABLE SUBSTITUTION IS DAT-38-292 OR TRANSVINYL (DAT-63-292-2.5).
- LOCATE APPROXIMATELY AS SHOWN.

2) TEST REQUIREMENT:

IL @ 1310 nm SHALL BE 3.25 dB MAX.

REVISION HISTORY - ALL SHEETS ARE AT THE SAME REVISION			
REV	DESCRIPTION	DATE	APPROVED
-	INITIAL RELEASE	2017/11/13	



4	BSFT0600	FURCATION TUBE, 2MM ID600UM, BLACK	2 FEET
3	WTTO-0400	CABLE, 4 FIBER 9/125 TACTICAL DISTRIBUTION	17.06 FEET
2	BFCC2000-BL-1	FC SM CONNECTOR, METAL BODY W/CERAMIC FERRULE; BLUE BOOT	4
1	EB4H1000-3445	PLUG ASSY, BLACK ALUM, 4 CH, 1310/1550 SM, TACBEAM 4.5-6.0 MM	1
ITEM NO.	PART NO.	DESCRIPTION	QTY/ LENGTH

P1	PINOUT DIAGRAM	B LABEL INFORMATION
A1		A1
B1		B1
A2		A2
B2		B2

MATERIAL:		DFTR/Designer: C. Hoang 2017/10/20	Amphenol FSI				
		Check By: B. Waite 2017/10/24					
		Manufacturing: B. Waite 2017/10/24	TITLE: 4 CHANNEL TACBEAM PLUG TO FC ASSEMBLY, SM				
		Market Manager/PLM: Q. Abraham 2017/10/25					
		Configuration Management: L. Brown 2017/11/13					
DO NOT SCALE DRAWING UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOL ON ANGLES ±3° 1 PL ±.1 2 PL ±.02 3 PL ±.010 INTERPRET DIM AND TOL PER ASME 14.5M-1994		This Document contains proprietary information and such information is prohibited from disclosure to others, publication or duplication in whole or in part without written permission from Amphenol Fiber Systems International. Copyright © 2017 Amphenol Fiber Systems International. Non published work. All rights reserved.		SIZE: A	CAGE CODE: 0YPM2	DWG NO: 2016040801TD-D5	REV: -
NEXT ASSY	USED ON	APPLICATION		SCALE: NONE	SHEET 1 OF 1		