

AMPHENOL PART NUMBER CONFIGURATION

U90-B205-XXX1-XX0

CAGE & CONNECTOR CONTACT PLATING

2 = 0.76 µm MIN. GOLD ON MATING AREA,
3.81-7.62 µm TIN/LEAD ON TERMINATION.
Ni PLATING FOR CAGE

3 = 0.38 µm MIN. GOLD ON MATING AREA,
3.81-7.62 µm TIN/LEAD ON TERMINATION.
Ni PLATING FOR CAGE

4 = 0.76 µm MIN. GOLD OVER 1.27-3.81 µm OF NICKEL
ON MATING AREA
0.381-1.52 µm OF MATTE TIN OVER 1.27-3.81
µm OF NICKEL ON PRESS FIT TAIL AREA.
Ni PLATING FOR CAGE
(RoHS COMPLIANT PER RoHS DIRECTIVE 2011/65/EU; OPTION 4 ONLY)

OPTIONAL DUST COVER

0 = WITHOUT DUST COVER
D = WITH DUST COVER

VENT HOLES AND EMI COVER

0 = WITH LARGE HOLES & WITH EMI COVER
1 = WITH LARGE VENT HOLES, NO EMI COVER
2 = WITH SMALL VENT HOLES & WITH EMI COVER
3 = WITH SMALL VENT HOLES, NO EMI COVER
4 = WITH RECTANGULAR VENT HOLES & WITH EMI COVER
5 = WITH RECTANGULAR VENT HOLES, NO EMI COVER

EMI GASKET

1 = CHOMERICS 1273 CONDUCTIVE ELASTOMER
2 = CHOMERICS S6305 CONDUCTIVE ELASTOMER

OPTIONAL LIGHT PIPES

6 = WITH LIGHT PIPE (TRIANGULAR OUTLET)
LEFT ARROW POINTING BOTTOM PORT &
RIGHT ARROW POINTING TOP PORT
7 = WITHOUT LIGHT PIPE
8 = WITH LIGHT PIPE (REVERSED DIRECTION)
LEFT ARROW POINTING TOP PORT &
RIGHT ARROW POINTING BOTTOM PORT


 REFERENCE VIEW FOR OPTION 6 ONLY

 REFERENCE VIEW FOR OPTION 8 ONLY


REVISIONS			
REV	DESCRIPTION, ECN, EAR NO.	DATE	APP'D
A	PROPOSAL DRAWING	JUL 06/11	ZLJ
B	OTHER CONFIGURATION ADDED	JAN 24/12	ZLJ
C	HEAT SINK CONFIGURATION ADDED	FEB 09/12	ZLJ
D	AHSI DESIGNATION ADDED	MAY 17/12	ZLJ
E	HEAT SINK OPTION REMOVED	SEP 12/12	ZLJ
F	RoHS DIRECTIVE ADDED	DEC 3/12	ZLJ

THIS IS A CAD DRAWING. DO NOT MANUALLY REVISE


PART # U90-B205-XD71-X30 SHOWN
(CAGE & CONNECTOR ASSEMBLY,
WITH DUST COVER AND WITHOUT LIGHT PIPE)



PART # U90-B205-X071-X10 SHOWN
(CAGE & CONNECTOR ASSEMBLY,
WITHOUT DUST COVER AND WITHOUT LIGHT PIPE)




PART # U90-B205-X071-X50 SHOWN
(CAGE & CONNECTOR ASSEMBLY,
WITHOUT DUST COVER AND WITHOUT LIGHT PIPE)




PART # U90-B205-X061-X30 SHOWN
(CAGE & CONNECTOR ASSEMBLY,
WITHOUT DUST COVER AND WITH LIGHT PIPE)


OPTIONAL DUST COVER
P/N U90-1401-8000-BP
(SHIPPED LOOSE)




PART # U90-B205-X061-X10 SHOWN
(CAGE & CONNECTOR ASSEMBLY,
WITHOUT DUST COVER AND WITH LIGHT PIPE)




PART # U90-B205-X061-X50 SHOWN
(CAGE & CONNECTOR ASSEMBLY,
WITHOUT DUST COVER AND WITH LIGHT PIPE)




PART # U90-B205-X081-X30 SHOWN
(CAGE & CONNECTOR ASSEMBLY,
WITHOUT DUST COVER AND WITH LIGHT PIPE)



PART # U90-B205-X081-X10 SHOWN
(CAGE & CONNECTOR ASSEMBLY,
WITHOUT DUST COVER AND WITH LIGHT PIPE)




PART # U90-B205-X081-X50 SHOWN
(CAGE & CONNECTOR ASSEMBLY,
WITHOUT DUST COVER AND WITH LIGHT PIPE)



NOTES:

- MATERIAL
CAGE/PRESS FIT: COPPER ALLOY, NICKEL PLATED
CONNECTOR/PRESS FIT: PLASTIC HOUSING, FLAMMABILITY RATING UL94 V-0.
CONTACTS: PHOSPHOR BRONZE
PLATING OPTION: SEE AMPHENOL PART NO CONFIGURATION
EMI GASKET: CONDUCTIVE ELASTOMER
EMI FINGERS: PHOSPHOR BRONZE WITH NICKEL PLATING
LIGHT PIPE: GE LEXAN, OPTICAL GRADE
- CONNECTOR AND CAGE ASSEMBLY IS RoHS COMPLIANT.

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING PURPOSES WITHOUT WRITTEN PERMISSION FROM AMPHENOL CANADA CORP.



UNLESS SPECIFIED OTHERWISE	DRAWN	M.HASAN	JUL 04/11
PRIMARY UNITS MILLIMETERS	CHECKED	ZLJ	JUL 06/11
SECONDARY MILLIMETERS	M.E. APP'D		
REFERENCE IN PARENTHESES	Q.A. APP'D		
GENERAL TOLERANCES	DWG APPR.	TBA	TBD
1. DECIMAL PLACE 0.X ±0.25	ENG. REL. NO.	ECN EXXXXX	
2. DECIMAL PLACES 0.XX ±0.13	REF.		
3. ANGULAR DEGREES X° ±1°	THIRD ANGLE PROJECTION		DO NOT SCALE DRAWING
4. ANGULAR DEGREES X.X° ±0.5°			

Amphenol High Speed Interconnects
A Division of Amphenol Corp. www.amphenol-highspeed.com




QSFP+ 2X2 STACKED
COMBO

DWG. NO.	P-U90-B205-XXX1-XX0	REV	F
CODE ID NO.	03554	DWG SIZE:	X
SCALE:	2:1	SHEET 1 OF 4	

REVISIONS			
REV	DESCRIPTION, ECN, EAR NO.	DATE	APP'D
F	SEE PAGE 1	DEC 3/12	ZLJ



PART # U90-B205-X061-X30 SHOWN



THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING PURPOSES WITHOUT WRITTEN PERMISSION FROM AMPHENOL CANADA CORP.

UNLESS SPECIFIED OTHERWISE	DRAWN	M.HASAN	JUL 04/11
PRIMARY UNITS MILLIMETERS	CHECKED	ZLJ	JUL 06/11
SECONDARY MILLIMETERS	M.E. APP'D		
REFERENCE IN PARENTHESES	Q.A. APP'D		
GENERAL TOLERANCES	DWG APPR.	TBA	TBD
1. DECIMAL PLACE 0.X±0.25	ENG. REL. NO.	ECN EXXXXX	
2. DECIMAL PLACES 0.XX±0.13	REF.		
3. ANGULAR DEGREES X°±1°	THIRD ANGLE PROJECTION		
4. ANGULAR DEGREES X.X°±0.5°	DO NOT SCALE DRAWING		



Amphenol High Speed Interconnects
A Division of Amphenol Corp. www.amphenol-highspeed.com

QSFP+ 2X2 STACKED COMBO

DWG. NO. **P-P-U90-B205-XXX1-XX0** REV **F**

CODE ID NO. 03554 DWG SIZE: X SCALE: 2:1 SHEET 2 OF 4

REVISIONS			
REV	DESCRIPTION, ECN, EAR NO.	DATE	APP'D
F	SEE SHEET 1	DEC 3/12	ZLJ



RECOMMENDED PCB BOARD LAYOUT
COMPONENT SIDE SHOWN

DETAIL A
SCALE 6 : 1

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING PURPOSES WITHOUT WRITTEN PERMISSION FROM AMPHENOL CANADA CORP.

UNLESS SPECIFIED OTHERWISE	DRAWN	MASROOR H.	JUL 04/11
PRIMARY UNITS MILLIMETERS	CHECKED	ZLJ	JUL 06/11
SECONDARY MILLIMETERS	M.E. APP'D		
REFERENCE IN PARENTHESES	Q.A. APP'D		
GENERAL TOLERANCES	DWG APPR.	TBA	TBD
1. DECIMAL PLACE 0.X ± 0.25	ENG. REL. NO.	ECN EXXXXX	
2. DECIMAL PLACES 0.XX ± 0.13	REF.		
3. ANGULAR DEGREES X° ± 1°	THIRD ANGLE PROJECTION		
4. ANGULAR DEGREES X.X° ± 0.5°	DO NOT SCALE DRAWING		





Amphenol High Speed Interconnects
A Division of Amphenol Corp. www.amphenol-highspeed.com

QSFP+ 2X2 STACKED COMBO

DWG. NO. **P-U90-B205-XXX1-XX0** REV **F**

CODE ID NO. 03554 DWG SIZE: C SCALE: 2:1 SHEET 3 OF 4

REVISIONS			
REV	DESCRIPTION, ECN, EAR NO.	DATE	APP'D
F	SEE SHEET 1	DEC 3/12	ZLJ



THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING PURPOSES WITHOUT WRITTEN PERMISSION FROM AMPHENOL CANADA CORP.

UNLESS SPECIFIED OTHERWISE	DRAWN	MASROOR H.	JUL 04/11
PRIMARY UNITS MILLIMETERS	CHECKED	ZLJ	JUL 06/11
SECONDARY MILLIMETERS	M.E. APP'D		
REFERENCE IN PARENTHESES	Q.A. APP'D		
GENERAL TOLERANCES	DWG APPR.	TBA	TBD
1. DECIMAL PLACE 0.X±0.25	ENG. REL. NO.	ECN EXXXXX	
2. DECIMAL PLACES 0.XX±0.13	REF.		
3. ANGULAR DEGREES X°±1°	THIRD ANGLE PROJECTION		
4. ANGULAR DEGREES X.X°±0.5°	DO NOT SCALE DRAWING		

Amphenol High Speed Interconnects
A Division of Amphenol Corp. www.amphenol-highspeed.com

QSFP+ 2X2 STAKED COMBO

DWG. NO. **P-U90-B205-XXX1-XX0** REV **F**

CODE ID NO. 03554 DWG SIZE: C SCALE: 2:1 SHEET 4 OF 4