## FPD-1012A3-SW **SHOCK ABSORBER - FIXED**





Model Description

FPD - 10 12 A3 - SW

2 3 4

- 1 Base model
- (2) External diameter
- ③ Stroke
- 4 Symbol indicating characteristics


A3: Medium-load specifications


- (5) Symbol indicating form
  - S: S type (Standard)
- \* Please refer to the external dimensions
- (6) Color symbol W: White

#### **SPECIFICATIONS**

Model	Load (kg)	Max Absorption Energy J(kgf∙m)	Speed Range (m/s)	Stroke mm
FPD-1012A3-SW	3	0.8(0.08)	0.5 or lower	12


Extension Force N(kgf)	Mass g	Main Unit Material	Operating Temp. C°	Cylinder Cap Color
3(0.3) or less	4.5	Resin	5~40	White






### **OPTIONAL PARTS**

# OP-200-01B/W S/C/R type



### OP-200-03B/W S/C/R/D type



■ These adaptors are dedicated for FPD-1012A series
■ They make it easy to install absorbers
■ There are 2 colors: white and black
■ Material: Polyacetal (POM)

### PRECAUTIONS FOR USE

- Do not use this product without carefully reading the attached owner's manual.
- Use with an external stopper.
- Ensure that sufficient mounting strength is secured for this product.
- 2 or more of this product can be used in parallel.
- Do not use this product in a vacuum or a location where it may come in contact with oil.
- Ensure that an eccentric load is not applied to the soft absorber.
  - •S/C/R type ··· Allowable eccentric angle: ±2.5° or less
  - •D type ..... Allowable eccentric angle: ±6° or less
- Do not pull the piston rod of the soft absorber. (This will cause air to get inside the soft absorber, causing ineffective stroke, abnormal sounds, and other damage to the soft absorber.)
- The difference between the speed of stroke and return of piston rod might influence the durability of the damper. So, please confirm sufficient performance on actual machine before use.

