## Bansbach easylift<sup>®</sup>


			SPECIFICATIONS								
			Model		Rated Torque		Max Rotation Speed	Max Cycle Rate			
			FRT-G2-200-G2		(2.0±0.7)X10 <sup>-3</sup> Nm (20±7gfcm)		50 RPM	10 cycles/ min.			
Operating Temperature	Weig	ht	Body & Cap Material		Rotating Shaft Material		Gear Material	Oil Type			
0~50°C	1.0g		Polycarbonate		Polyacetal		Polyacetal	Silicone Oil			

Note 1) Rated torque measured at a rotation speed of 20rpm at 23°C Note 2) Models with gears bear G1, G2 or G3 at the end of their model numbers Note 3) Torque can be customized by changing the oil viscosity


## **GEAR SPECIFICATIONS**

Model	Туре	Tooth Profile	Module	Pressure Angle	Number of Teeth	Pitch Circle Diameter	Addendum Modification Coefficient	Weight (damper+gear)
G2	Profile Shifted Spur Gear	Involute	1.0	20°	10	ø10	+0.375	1.0g (0.6g+0.4g)

## **DAMPING CHARACTERISTICS**



• **Speed characteristics:** A rotary damper's torque varies according to the rotation speed. In general, as shown in the graph above, the torque increases as the rotation speed increases, and the torque decreases as the rotation speed decreases. In addition, please note that the starting torque slightly differs from the rated torque.



**Temperature characteristics:** A rotary damper's torque varies according to the ambient temperature. In addition, as shown in the graph above, the torque decreases as the ambient temperature increases, and the torque increases as the ambient temperature decreases. This is because the viscosity of the silicone oil inside the damper varies according to the temperature. When the temperature returns to normal, the torque will return to normal as well.