

CS266-49-0-1A**Product SPEC.**

Application area	1U Server thermal solution.
Application for CPU Socket	LGA 2011(56 x 94 mm)
Application for CPU Type	Intel® Sandy Bridge EP/EX Processors E5-2600 / E5-4600 (for Narrow ILM Mounting Only)
Production technology	Copper Skiving plus DC fan.
Assembly Method	Screw plus spring.
Production dimension (mm)	106*78*28.5
Production weight (g)	494
Thermal interface material	AD66 (thermal conductivity>4.0)
Back bracket	N/A

Fan Spec.

Fan part number	FD7015H12D
Fan dimension (mm)	75*75*15
Rated voltage (V)	12
Bearing type	Two ball
Speed (RPM)	5000
Maximum air flow (CFM)	10.75
Acoustic (dBA)	55
Lifetime (H)	70,000
Fan line	4pins with PWM function



|