Description

## **PI3PCIE3415**

#### 3.3V, PCI Express® 3.0 2-Lane, 2:1 Mux/DeMux Switch

Diodes Incorporated PI3PCIE3415 is an 8 to 4 differential channel multiplexer/demultiplexer switch. This solution can switch

2 full PCI Express<sup>®</sup> 3.0, lanes to one of two locations. Using a

unique design technique, Diodes has been able to minimize

the impedance of the switch such that the attenuation observed through the switch is negligible. The unique design technique

also offers a layout targeted for PCI Express signals, which mini-

mizes the channel to channel skew as well as channel to channel

Routing of PCI Express 3.0, DP1.2, USB3.0, SAS2.0, SATA3.0,


crosstalk as required by the PCI Express specification.

XAUI, RXAUI signals with low signal attenuation.

### **Features**

- → 4 Differential Channel, 2:1 Mux/DeMux
- → PCI Express<sup>®</sup> 3.0 Performance, 8.0Gbps
- → Pinout optimized for placement between two PCIe slots
- → Bi-directional operation
- → Low Bit-to-Bit Skew, 10ps max
- → Low Crosstalk: -48dB @4GHz
- → High Off Isolation: -22dB @4GHz
- → Low Insertion Loss: -1.6dB @4GHz
- → Return Loss: -15dB @4GHz
- → V<sub>DD</sub> Operating Range: +3.3V
- → Industrial Temperature Range: -40°C to 85°C
- → ESD Tolerance: 2kV HBM
- → Low channel-to-channel skew, 20ps max
- → Packaging (Pb-free & Green):
  - <sup>a</sup> 42-contact, TQFN (ZH42), 3.5 x 9mm
  - 40-contact, TQFN (ZL40), 3 x 6mm


## **Block Diagram**



Truth Table

Application

Function	SEL
xIy to xOay	L
xIy to xOby	Н





PI3PCIE3415

# **Signal Descriptions**

Pin Number				
42-TQFN	40-TQFN	Pin Name	Туре	Description
1, 2	39, 40	AI+, AI-	Differential I/O	Differential I/O pair from PCIE signal source. Signal is routed to the AOa+, AOa- pin respectively when SEL=0. Signal is routed to the AOb+, AOb- pin respectively when SEL = 1.
37, 36	34, 33	AOa+, AOa-	Differential I/O	Differential analog pass-through I/O. Signal from AI+ and AI- is routed to AOa+ and AOa- respectively when SEL=0.
3, 4	1, 2	AOb+, AOb-	Differential I/O	Differential analog pass-through I/O. Signal from AI+ and AI- is routed to AOb+ and AOb- respectively when SEL=1.
5, 6	3, 4	BI+, BI-	Differential I/O	Differential I/O pair from PCIE signal source. Signal is routed to the BOa+, BOa- pin respectively when SEL=0. Signal is routed to the BOb+, BOb- pin respectively when SEL = 1.
33, 32	31, 30	BOa+, BOa-	Differential I/O	Differential analog pass-through I/O. Signal from BI+ and BI- is routed to BOa+ and BOa- respectively when SEL=0.
7, 8	5, 6	BOb+, BOb-	Differential I/O	Differential analog pass-through I/O. Signal from BI+ and BI- is routed to BOb+ and BOb- respectively when SEL=1.
10, 11	9, 10	CI+, CI-	Differential I/O	Differential I/O pair from PCIE signal source. Signal is routed to the COa+, COa- pin respectively When SEL=0. Signal is routed to the COb+, COb- pin respectively when SEL = 1.
28, 27	25, 24	COa+, COa-	Differential I/O	Differential analog pass-through I/O. Signal from CI+ and CI- is routed to COa+, COa- pin respectively when SEL = 0.
12, 13	11, 12	COb+, COb-	Differential I/O	Differential analog pass-through I/O. Signal from CI+ and CI- is routed to COb+, COb- pin respectively when SEL = 1.
14, 15	13, 14	DI+, DI-	Differential I/O	Differential I/O pair from PCIE signal source. Signal is routed to the DOa+, DOa- pin respectively When SEL=0. Signal is routed to the DOb+, DOb- pin respectively when SEL = 1.
24, 23	22, 21	DOa+, DOa-	Differential I/O	Differential analog pass-through I/O. Signal from DI+ and DI- is routed to DOa+, DOa- pin respectively when SEL = 0.
16, 17	16, 17	DOb+, DOb-	Differential I/O	Differential analog pass-through I/O. Signal from DI+ and DI- is routed to DOb+, DOb- pin respectively when SEL = 1.
18, 20, 22, 25, 29, 35, 38, 40, 42	15, 18, 20, 26, 29, 35, 37, 38, Center Pad	GND	Ground input	Ground
30	27	SEL	3.6V tolerant low-voltage single-ended input	SEL controls the mux through a flow-through latch.
9, 19, 21, 26, 31, 34, 39, 41	7, 19, 23, 28, 32, 36	VDD	Power supply	Power, 3.3V ±10%

**PI3PCIE3415** 

# **Maximum Ratings**

(Above which useful life may be impaired. For user guidelines, not tested.)

Storage Temperature	65°C to +150°C
Supply Voltage to Ground Potential	-0.5V to +4.6V
Channel DC Input Voltage	–0.5V to 1.5V
DC Output Current	
Power Dissipation	0.5W
SEL DC Input Voltage	0.5V to 4.6V

Note: Stresses greater than those listed under MAXIMUM RATINGS may cause permanent damage to the device. This is a stress rating only and functional operation of the device at these or any other conditions above those indicated in the operational sections of this specification is not implied. Exposure to absolute maximum rating conditions for extended periods may affect reliability.

## **Electrical Characteristics** Recommended Operating Conditions

Symbol	Parameter	Conditions		Min.	Typ.	Max.	Units
V <sub>DD</sub>	3.3V Power Supply			3.0	3.3	3.6	V
I <sub>DD</sub>	Total current from V DD3.3V supply	SEL = 0V or $V_{DD}$		0	0.15	1	mA
T <sub>A</sub>	Operating temperature range		1,9	-40		85	°C

# **DC Electrical Characteristics** ( $T_A = -40^{\circ}C$ to $+85^{\circ}C$ , $V_{DD} = 3.3V \pm 10\%$ )

Parameter	Description	Test Conditions	Min.	Typ. <sup>(1)</sup>	Max.	Units
V <sub>IH-SEL</sub>	Input high level, SEL input		2.0		3.6	V
V <sub>IL-SEL</sub>	Input Low Level, SEL input		0		0.8	V
I <sub>IN_SEL</sub>	Input Leakage Current, SEL input	Measured with input at VIH-SEL max and VIL-SEL min	-10		10	uA
I <sub>IH</sub>	Input High Current, xI, xO	$V_{DD} = Max, V_{IN} = 1.5V$	-10		10	uA
I <sub>IL</sub>	Input Low Current, xI, xO	$V_{DD} = Max, V_{IN} = 0V$	-10		10	uA
I <sub>IH</sub>	Input High Current, SEL	$V_{DD} = Max, V_{IN} = V_{DD}$	-5		5	uA
I <sub>IL</sub>	Input Low Current, SEL	$V_{DD} = Max, V_{IN} = 0V$	-5		5	uA
I <sub>OZH</sub>	HighZ High Current xOa, xOb	$V_{DD} = Max, V_{IN} = 1.5V$	-10		10	uA
I <sub>OZL</sub>	HighZ Low Current xOa, xOb	$V_{DD} = Max, V_{IN} = 0V$	-10		10	uA

Note:

1. Typical values are at  $V_{DD}$  = 3.3V,  $T_A$  = 25°C ambient and maximum loading.




**PI3PCIE3415** 

# Dynamic Electrical Characteristics for xI+/-, xOy+/-

	Test Conditions	Min.	Typ.(1)	Max.	Units
	f=50MHz -1.25GHz		-0.8	-1.0	
	f=1.25GHz - 2.5GHz		-1.1	-1.3	
Differential filser tion Loss	f=2.5GHz - 4GHz		-1.6	-1.9	
	f=5.0GHz		-1.7	-2.0	
Differential Off Isolation	f= 0 to 4.0GHz	-25.8 -20.6 -17.6 -15.4	-32.2 -25.8 -22.0 -19.3		
Differential Return Loss	f=50MHz - 1.25GHz f=1.25GHz - 2.5GHz f=2.5GHz - 4GHz f=5.0GHz	-18.2 -16.8 -12 -8	-22.7 -21.0 -15.0 -10.0		dB
Near End Crosstalk	f=50MHz -1.25GHz f=1.25GHz - 2.5GHz f=2.5GHz - 4GHz f=5.0GHz	-44.8 -41.6 -38.4 -36	-56 -52 -48 -45		
Bandwidth -3dB			8.7		GHz
	Differential Return Loss Near End Crosstalk	Differential Insertion Lossf=1.25GHz - 2.5GHz f=2.5GHz - 4GHz f=5.0GHzDifferential Off Isolationf= 0 to 4.0GHzDifferential Return Lossf=50MHz - 1.25GHz f=1.25GHz - 2.5GHz f=2.5GHz - 4GHz f=5.0GHzNear End Crosstalkf=50MHz - 1.25GHz f=1.25GHz - 2.5GHz f=1.25GHz - 2.5GHz f=1.25GHz - 2.5GHz f=1.25GHz - 4GHz f=1.25GHz - 2.5GHz f=1.25GHz - 4GHz f=1.25GHz - 4GHz f=1.25GHz - 4GHz f=1.25GHz - 4GHz f=2.5GHz - 4GHz f=1.25GHz - 4GHz f=1.25GHz - 4GHz f=2.5GHz - 4GHz f=5.0GHz	$ \begin{array}{c} \mbox{Differential Insertion Loss} & f=1.25 \mbox{GHz} - 2.5 \mbox{GHz} \\ f=2.5 \mbox{GHz} - 4 \mbox{GHz} \\ f=5.0 \mbox{GHz} \\ \end{array} \\ \begin{array}{c} -25.8 \\ -20.6 \\ -17.6 \\ -17.6 \\ -15.4 \\ f=0 \ to \ 4.0 \mbox{GHz} \\ \end{array} \\ \begin{array}{c} f=0 \ to \ 4.0 \mbox{GHz} \\ f=0 \ to \ 4.0 \mbox{GHz} \\ \end{array} \\ \begin{array}{c} f=0 \ to \ 4.0 \mbox{GHz} \\ -17.6 \\ -15.4 \\ f=1.25 \mbox{GHz} - 2.5 \mbox{GHz} \\ f=1.25 \mbox{GHz} - 2.5 \mbox{GHz} \\ f=2.5 \mbox{GHz} \\ f=2.5 \mbox{GHz} \\ f=2.5 \mbox{GHz} \\ f=2.5 \mbox{GHz} \\ f=5.0 \mbox{GHz} \\ f=2.5 \m$	$ \begin{array}{ccccc} \text{Differential Insertion Loss} & \begin{array}{c} \text{f=1.25GHz} & -2.5\text{GHz} \\ \text{f=2.5GHz} & -4\text{GHz} \\ \text{f=2.5GHz} & -4\text{GHz} \\ \text{f=5.0GHz} & -1.7 \\ -25.8 & -32.2 \\ -20.6 & -25.8 \\ -17.6 & -22.0 \\ -25.8 \\ -17.6 & -22.0 \\ -15.4 & -19.3 \\ -$	$ \begin{array}{c ccccccccccccccccccccccccccccccccccc$


# Switching Characteristics

Parameter	Description	Test Conditions	Min.	Тур.	Max.	Units
t <sub>PZH</sub> , t <sub>PZL</sub> Line Enable Time - SEL to xI+/-, xOy-		See "Test Circuit for	0.5	15	25	
	Line Enable Time - SEL to XI+/-, XOy+/-	Electrical Characteristics"	0.5	15		ns
L L	Line Disable Time - SEL to xI+/-, xOy+/-	See "Test Circuit for	0.5	5	25	
$t_{PHZ}, t_{PLZ}$	Line Disable Time - SEL to XI+/-, XOy+/-	Electrical Characteristics"	0.5	3	25	ns
4	Bit-to-bit skew within the same differential	See "Test Circuit for		4	10	
t <sub>b-b</sub>	pair	Electrical Characteristics"		4	10	ps
t <sub>ch-ch</sub>	Channel-to-channel skew	See "Test Circuit for			20	
		Electrical Characteristics"				ps






PI3PCIE3415




**Differential Return Loss** 



# **PI3PCIE3415**



# **Differential Off Isolation**




## **Differential Crosstalk**




PI3PCIE3415

# Test Circuit for Electrical Characteristics<sup>(1-5)</sup>




### Voltage Waveforms Enable and Disable Times





**PI3PCIE3415** 


### **Packaging Information**





PI3PCIE3415

### **Packaging Information**



Note: For latest package info, please check: http://www.pericom.com/support/packaging/packaging-mechanicals-and-thermal-characteristics/

# Ordering Information

Ordering Code	Package Code	Package Description
PI3PCIE3415ZHE	ZH	42-contact, Very Thin Quad Flat No-Lead (TQFN)
PI3PCIE3415ZHEX	ZH	42-contact, Very Thin Quad Flat No-Lead (TQFN), Tape & Reel
PI3PCIE3415ZLE	ZL	40-contact, Thin Fine Pitch Quad Flat No-Lead (TQFN)
PI3PCIE3415ZLEX	ZL	40-contact, Thin Fine Pitch Quad Flat No-Lead (TQFN), Tape & Reel

Notes:

• Thermal characteristics can be found on the company web site at www.pericom.com/packaging/

• "E" denotes Pb-free and Green

• Adding an "X" at the end of the ordering code denotes tape and reel packaging