

4502

15-20-25 liter Click Pack^x lid



Product part	Product code	Materials
Click Pack lid 15-20-25L	4502	HDPE
Gasket	/	TPE

Weight	Grams	Ounces
Click Pack lid 15-20-25L	350	12.35

Weight tolerance
All products have a tolerance of $\pm 4\%$ of the initial weight mentioned on this data sheet

Dimensional tolerance (mm) according to DIN16742-TG7																
Over	1	>3	>6	>10	>18	>30	>50	>80	>120	>180	>250	>315	>400	>500	>630	>800
up to	3	6	10	18	30	50	80	120	180	250	315	400	500	630	800	1000
NW (\pm)	0.20	0.29	0.35	0.42	0.50	0.60	0.90	1.25	1.45	1.60	1.80	2.60	3.50	4.00	4.50	5.00

Standard color(s)	Color code	PMS references
Click Pack lid 10-15-20L*	Blue 611	2767 C
Gasket	White 004	/

* Other colors available on request

Product identification	
Manufacturer ID	Outside
Product code	--
Recycle logo / Material type	Inside
Date clock	Inside
UN-mark	--
Food logo	--
Material track clock	--
CFR49-mark	--

Other information
<p>The container can be opened and closed with just a quarter-turn</p> <p>The lid is locked when it passes the safety button, confirmed by a 'click'</p> <p>Maximum filling temperature is 70°C/ 158°F</p> <p>Contents must have cooled to 30°C/ 86°F before containers can be closed and stacked</p> <p>DoC available on request</p> <p>UN certificate available on request</p> <p>MVTR declaration available on request</p> <p>User manual available on request</p>

DISCLAIMER

CurTec manufactures packaging material for a wide range of purposes. This declaration is restricted to the packaging material as it leaves the production facility. CurTec has neither control over final end use of the product nor over processing conditions. It is therefore the responsibility of the end user to check compliance with the relevant regulations and to validate material performance in the end application through proper end use testing.

© 2019 Property of CurTec International B.V. All rights explicitly reserved, it is not allowed to copy or communicate to other parties without written consent of CurTec.