



This electronic ballast is designed to operate various High Output 800mA ultraviolet quartz germicidal lamps. It has a 24VDC input voltage, and is equipped with flying leads for universal integration.



Contact Us for alternative solutions!



Electrical Specifications			
Lamp Type:	GHO212T5L4P	GHO357T5L4P	
Input Voltage:	24VDC	24VDC	
Lamps Operated:	1 / 1	1 / 1	
Input Power (W):	26	36	
Line Current (A):	1.1	1.5	
Power Factor:	1	1	
THD:	0	0	
Lamp Voltage (V):	29	49	
Ballast Type:	Program Start (PS)		Lamp Current: 800 mA (+/- 10%)
Current Crest Factor:	< 1.7		Voltage Transients: ANSI 62.41

Environmental Specifications			
Sound Rating:	Class A		Min. Operating Temp: 0°C / 32°F
			Max. Case Temp: 70°C / 158°F

Protections			
Input Protection:	Fuse		Approvals:
Output Protection:	EOL		

