



Our Hybrid Stepper Motors are a precise motion control solution providing excellent holding torque. They come in various sizes and step angles. With endless performance combinations, we have a fully tailored solution for you.



Contact Us for alternative solutions!

Specifications				
Motor Type:	Hybrid Stepper		Phase Inductance:	1.5 mH ($\pm 20\%$)
Step Angle:	1.8°		Holding Torque:	300 g-cm
Rated Voltage:	4.32 VDC		Phase Resistance:	5.4 Ω ($\pm 10\%$)
Number of Phases:	2		Induction Class:	B
Rated Current/Phase:	0.80 A (<i>peak</i>)		Motor Weight:	0.09 Kg
Number of Leads:	4			

