Datasheet for part number FRCIR06F-36-7SW-F80-V0

Our Catalog Part Number: FRCIR06F-36-7SW-F80-V0

 $\ \, \text{Brand: VEAM } \ \, \text{Product Category: Circular} \ \, \text{Product Line: Veam CIR, VBN, Other} \ \, \text{Series: CIR / FRCIR}$

Product Datasheet	
SERIES	Connector with Bayonet Coupling
Shell Style	Straight Plug Connector
Environmental Class	Backshell with A style clamp and bushing but includes wire sealing grommet and compression ring.
Shell Size	36
Contact Arrangement	36-7
Total Number of contacts	47 contacts
Number of Contacts Size 12	7 contacts size 12
Number of Contacts Size 16	40 contacts size 16
Insulator Rotation	80°
Gender	Socket
Contact Type	Crimp for AWG wire (used in F80 insert)
Contact Plating	Silver
Contact Material	Copper alloy
Shell Material	Aluminium alloy
Shell Plating	Chromate over Cadmium, olive drab, min. 500h salt spray resistance, conductive
Insulator Material	Flame Retardant rubber
Contacts included	no, delivery without contacts
Shock Resistance	Waterproof to 10 meteres (33 ft) 12 h (14.7 PSI)
Coupling	2000 couplings minimum
Service Rating Letter	A
Operating Voltage DC	700 V
Operating Voltage AC	500 V
Dielectric strength - Minimum Flashover AC RMS	2800 V
Dielectric strength - Test Voltage AC RMS (Hi Pot)	2000 V
Note	Voltages in excess of 30 V ac or 42.5 V dc are potentially hazardous and care should be taken to ensure that such voltages can't be transmitted in any way to exposed metal parts of the connector body.
General	Veam CIR series Connectors are produced in accordance with NATO Standard VG95234, which is based on MIL-C-5015 for physical size, layout and environment requirements.