



ISL Products designs and manufactures unique, application specific electromechanical components for a variety of applications and industries. If this product is not exactly what your looking for, contact us for a more suitable solution!



Contact Us for alternative solutions!

Electrical Specifications

Inductance (1-3):	145 mH
Inductance (1-2):	105 mH
Inductance (2-3):	2.6 mH
DC Current (max):	0.08 A
Test Frequency:	1KHz / 0.3V


DC Resistance (1-3):	163Ω (max.)
DC Resistance (1-2):	144Ω (max.)
DC Resistance (2-3):	17Ω (max.)
Tolerance:	± 20%

Environmental Specifications

Min. Operating Temp:	-40°C / -40°F
Max. Operating Temp:	125°C / 257°F

Max. Humidity:	70% (RH)
Storage Temp:	≤40°C / 104°F

Dimensions



units: mm

Schematic

