

InteliHeat® Thermulate® Full Coverage 30-gallon (100 Liter) Drum Heating Jacket (HPNA/C/OR)

Our InteliHeat® Thermulate® HPC Full Coverage 30-gallon Drum Heating Jacket for non-hazardous ordinary locations provides increased power to reach higher temperatures in a shorter time.

- Maximum power to reach highest temperatures. 32-320°F(0-160°C) adjustable thermostat fitted as standard.
- Special formulated high-temperature, chemically resistant silicon-coated glass-cloth used on both sides of the jacket to extend product life in demanding applications.
- High grade thermal insulation to reduce heat loss and increase efficiency while providing protection for the operator.
- Fitted with adjustable retaining straps and quick release buckles.
- Flexible - conforms to the container wall providing optimal thermal coupling
- Delivers heat over a large surface area, minimizing the possibilities of damaging the product.
- Fit and forget, built to last - no regular maintenance required.
- Safe to use 24/7.
- 7 ft. (2m) premium oil, water, and abrasion resistant power cable
- Fitted with NEMA 1-15P plug
- Double insulated product
- Ambient temperature: -40°F to +104°F (-40°C to +40°C)
- ETL approved to UL and CSA standards.
- Waterproof and custom sizes available.

To fit container: 30 Gallon / 100 Liter

Thermostat: Adjustable 0-160°C / 0-320°F

Size: Circumference 55" – 65" / Height 24" (1400 – 1650mm / 610mm)

120 Volts

1150 Watts

Part Number: HPNA/C/OR/# /EC/120/1150/0-160