


# Technical data sheet Safety light curtain transmitter

Part no.: 68000312

MLC500T30-1200



## Contents

- Technical data
- Dimensioned drawings
- Electrical connection
- Circuit diagrams
- Operation and display
- Suitable receivers
- Part number code
- Notes
- Accessories















## **Technical data**



#### Basic data

Series	MLC 500
Device type	Transmitter
Contains	2x BT-NC sliding block
Application	Hand protection

#### **Functions**

Functions	Range reduction
	Transmission channel changeover

## **Characteristic parameters**

Туре	4, IEC/EN 61496
SIL	3, IEC 61508
SILCL	3, IEC/EN 62061
Mission time T	20 years. EN ISO 13849-1

#### Protective field data

Resolution	30 mm	
Protective field height	1,200 mm	
Operating range	0 10 m	

#### **Optical data**

Synchronization	Optical between transmitter and receiver
Light source	LED, Infrared
Wavelength	940 nm
Transmitted-signal shape	Pulsed
LED risk group	Exempt group (in acc. with EN 62471:2008)

#### **Electrical data**

Protective circuit	Overvoltage protection
	Short circuit protected

#### Performance data

Supply voltage U <sub>B</sub>	24 V, DC, -20 20 %
Current consumption, max.	50 mA
Fuse	2 A semi time-lag

## Inputs

Number of digital switching inputs	1 Piece(s)
------------------------------------	------------

## **Switching inputs**

Туре	Digital switching input
Switching voltage high, min.	18 V
Switching voltage low, max.	2.5 V
Switching voltage, typ.	22.5 V
Voltage type	DC

## Connection

N	umber of connections	1 Piece(s)	
	Connection 1		
	F C	March to a fator for a	

Machine interface
Connector
M12
Metal
5 -pin

#### Cable properties

Permissible conductor cross section, typ.	0.25 mm <sup>2</sup>
Length of connection cable, max.	100 m
Permissible cable resistance to load, max.	200 Ω

#### **Mechanical data**

29 mm x 1,266 mm x 35.4 mm
Metal
Aluminum
Plastic / PMMA
Diecast zinc
1,350 g
Yellow, RAL 1021
Groove mounting
Mounting bracket
Mounting on Device Column
Swivel mount

## Operation and display

Type of display	LED
Number of LEDs	2 Piece(s)

#### **Environmental data**

Ambient temperature, operation	-30 55 °C
Ambient temperature, storage	-30 70 °C
Polativo humidity (non condensing)	0 05 %

#### Certifications

Degree of protection	IP 65
Protection class	III
Certifications	c CSA US
	c TÜV NRTL US
	S Mark
	TÜV Süd
Vibration resistance	50 m/s <sup>2</sup>
Shock resistance	100 m/s <sup>2</sup>
US patents	US 6,418,546 B

## Classification


Customs tariff number	85365019	
ECLASS 5.1.4	27272704	
ECLASS 8.0	27272704	
ECLASS 9.0	27272704	
ECLASS 10.0	27272704	
ECLASS 11.0	27272704	
ECLASS 12.0	27272704	
ETIM 5.0	EC002549	
ETIM 6.0	EC002549	
ETIM 7.0	EC002549	

# **Dimensioned drawings**



All dimensions in millimeters

Calculation of the effective protective field height  $H_{PFE}$  =  $H_{PFN}$  + B + C



 $H_{\mathrm{PFE}}$  Effective protective field height = 1228 mm

 ${\rm H}_{\rm PFN}$  Nominal protective field height = 1200 mm

A Total height = 1266 mm

R

B 19 mm


- C 9 mm
- R Effective protective field height H<sub>PFE</sub> goes beyond the dimensions of the optics area to the outer borders of the circles labeled with R.

## **Electrical connection**

## **Connection 1**

Function	Machine interface
Type of connection	Connector
Thread size	M12
Туре	Male
Material	Metal
No. of pins	5 -pin
Encoding	A-coded
Connector housing	FE/SHIELD


Pin	Pin assignment	Conductor color
1	VIN1	Brown
2	n.c.	White
3	VIN2	Blue
4	RNG	Black
5	FE/SHIELD	Gray



# **Circuit diagrams**




## Transmission channel C1, reduced range



- VIN1 = +24 V
- VIN2 = 0 V
- RNG = 0 V or open

## Transmission channel C1, standard range




- VIN1 = +24 V
- VIN2 = 0 V
- RNG = +24 V

# **Circuit diagrams**




## Transmission channel C2, reduced range



- 1 VIN1 = 0 V
- 3 VIN2 = +24 V
- 4 RNG = 0 V or open

## Transmission channel C2, standard range



- 1 VIN1 = 0 V
- 3 VIN2 = +24 V
- 4 RNG = +24 V

# **Operation and display**

LED	Display	Meaning
1	Off	Device switched off
	Red, continuous light	Device error
	Green, continuous light	Normal operation
2	Green, flashing, 10 s long after switching on	Reduced range selected by the wiring of pin 4
	Off	Transmission channel C1
	Green, continuous light	Transmission channel C2

Phone: +49 7021 573-0 • Fax: +49 7021 573-199

## Suitable receivers



Part no.	Designation	Article	Description
68001312	MLC510R30-1200	Safety light curtain receiver	Function package: Basic Resolution: 30 mm Protective field height: 1,200 mm Response time: 12 ms Connection: Connector, M12, Metal, 5 -pin
68002312	MLC520R30-1200	Safety light curtain receiver	Function package: Standard Resolution: 30 mm Protective field height: 1,200 mm Response time: 12 ms Connection: Connector, M12, Metal, 8 -pin
68003312	MLC530R30-1200	Safety light curtain receiver	Function package: Extended Resolution: 30 mm Protective field height: 1,200 mm Response time: 12 ms Connection: Connector, M12, Metal, 8 -pin
68009312	MLC530R30-1200- SPG	Safety light curtain receiver	Function package: Smart Process Gating Resolution: 30 mm Protective field height: 1,200 mm Response time: 100 ms Connection: Connector, M12, Metal, 8 -pin

## Part number code

MLC	Safety light curtain
х	Series 3: MLC 300 5: MLC 500
уу	Function classes  00: transmitter  01: transmitter (AIDA)  02: transmitter with test input  10: basic receiver - automatic restart  11: basic receiver - automatic restart (AIDA)  20: standard receiver - EDM/RES selectable  30: extended receiver - blanking/muting
z	Device type T: transmitter R: receiver
a	Resolution 14: 14 mm 20: 20 mm 30: 30 mm 40: 40 mm 90: 90 mm
hhhh	Protective field height 150 3000: from 150 mm to 3000 mm
е	Host/Guest (optional) H: Host MG: Middle Guest G: Guest

## Part number code



MLC	Safety light curtain
i	Interface (optional) /A: AS-i
000	Option  /V: high Vibration-proof  EX2: explosion protection (zones 2 + 22)  SPG: Smart Process Gating

#### Note



## **Notes**



## Observe intended use!



- \$ The product may only be put into operation by competent persons.

## **Accessories**

# Connection technology - Connection cables

	Part no.	Designation	Article	Description
•	50133860	KD S-M12-5A-P1-050	Connection cable	Connection 1: Connector, M12, Axial, Female, A-coded, 5 -pin Connection 2: Open end
				Shielded: Yes Cable length: 5,000 mm Sheathing material: PUR

# Mounting technology - Swivel mounts

	Part no.	Designation	Article	Description
Paga	429393	BT-2HF	Mounting bracket set	Fastening, at system: Through-hole mounting Mounting bracket, at device: Clampable Type of mounting device: Turning, 360° Material: Metal, Plastic

# Alignment aids

	Part no.	Designation	Article	Description
-1	520101	AC-ALM-M	Alignment aid	Housing material: Plastic

## **Accessories**



## Services

 Part no.	Designation	Article	Description
S981050	CS40-I-140	Safety inspection	Details: Checking of a safety light barrier application in accordance with current standards and guidelines. Inclusion of the device and machine data in a database, production of a test log per application.  Conditions: It must be possible to stop the machine, support provided by customer's employees and access to the machine for Leuze employees must be ensured.  Restrictions: Travel costs and accommodation expenses charged separately and according to expenditure.
S981046	CS40-S-140	Start-up support	Details: For safety devices including stopping time measurement and initial inspection.  Conditions: Devices and connection cables are already mounted, price not including travel costs and, if applicable, accommodation expenses.  Restrictions: Max. 2 h., no mechanical (mounting) and electrical (wiring) work performed, no changes (attachments, wiring, programming) to third-party components in the nearby environment.

#### Note



🔖 A list with all available accessories can be found on the Leuze website in the Download tab of the article detailed page.