

## Datasheet for part number CA3106E20-19PB14

|   | Our Catalog Part Number: CA3106E20-19P-B-14  |  |  |
|---|--|--|--|
| Our Global Manufacturing Part Number: 121141-0225 |  |  |  |
|   | Brand: Cannon Product Category: Circular Product Line: CA Bayonet Series: CA BAYONET |  |  |

| Product Datasheet                                   |   |
|---|---|
| Bayonet   | Connector with bayonet coupling   |
| Shell Style   | Plug, straight  |
| Endbell Style                                       | Shielded connector with endbell for shielded braids<br>and heat shrinkable boots  |
| Gender  | Pin   |
| Shell Size  | 20  |
| Contact Arrangement                                 | 20-19   |
| Number of contacts                                  | 3 contacts size 8   |
| Contact Type  | Metric Crimp  |
| Contact Plating                                     | Hard silver   |
| Contacts installed                                  | not assembled, packed separately  |
| Shielding   | yes   |
| Contact Rating at +20 °C (68 °F)<br>(Size 60/100/8) | 74 A  |
| Contact Resistance (Size 60/100/8)                  | 1 mΩ  |
| Operating Voltage                                   | In case of voltages greater than 50V the connector must be used in accordance with DIN VDE part 410, IEC 60364-4-41.        |
| Insulator Resistance                                | Acc. To VG95319, part 2, test no. 5.12<br>and VG95210, part 32, test conditions B,<br>standard insulator material > 1000 MΩ |
| Test Voltage  | 1600 Vrms   |
| Air and Creepage Paths (Min)                        | 1,1 mm  |
| Ambient Temperature                                 | Standard insulator material -55°/+125°C<br>(-67/257°F)  |
| Safety Provisions                                   | IP67 and IP68 (1 bar pressure after 12 hrs) acc. to DIN 40 050  |
| Salt Spray Resistance                               | 500 hours salt spray resistant  |
| Mating Cycles                                       | 500 min   |
| Sep. Force per Contact (Size 60/100/8)              | 3,0 N   |
| Gage  | For infos on Gage please see catalog<br>VG95234, part 1   |
| Coupling Torque                                     | Closing: 9 Nm max / Opening: 0,7 Nm min   |
| Contact Retention (Size 60/100/8)                   | 80 N  |
| Shell Material                                      | Aluminium alloy   |
| Shell Plating                                       | Olive drab chromate over cadmium plating (conductive)   |
| Insulator and Grommet Material                      | CR-Elastomere   |
| Contact Material                                    | Copper alloy  |
| Harnessing Info: Contact Cross-Section              | See assembly instruction  |
| Harnessing Info: Insulator Diameter                 | See assembly instruction  |
| Wire Stripping (Size 60/100/8)                      | 11,8 mm   |
| General Info  | All tests in accordance with VG95319 and/or if applicable with VG95210  |

Specifications and dimensions subject to change.