



d	r	b	I <sub>1</sub> ≈	I <sub>2</sub>	l <sub>3</sub> min.	I <sub>4</sub>	
17	40	10	5.5	16.5	21.5	11	
0.67	<i>1.57</i>	0.39	0.22	<i>0.65</i>	<i>0.85</i>	<i>0.43</i>	
17	55	10	5.5	16.5	21.5	11	
0.67	2.17	<i>0.39</i>	0.22	<i>0.65</i>	0.85	<i>0.43</i>	

## Specification

Zinc die-cast

Powder coated

Indexing mechanism

Latch arm

- Type A

- Type B, C

## Information

4

• SW

RS

GN 702 stop latches offer a fast and easy way to close and hold doors, flaps, slide-in modules, etc. They latch in four positions (90°).

Type C stop latches have the same connecting dimensions as GN 115.1 and GN 115.6 mini latches. The mounting bores are to be selected accordingly.

The installation bore hole in the door leaf is usually generated by punching or laser machining during a mass production run.

For small production runs and steel sheets below 2 mm thickness, the GN 123 sheet metal punches are the tool of choice.

The mounting bore holes can also be made by drilling or milling.

How to order	1	Handle diameter d
		Length r
	3	Туре
GN 702-17-40-C-SW	4	Color

## Steel / plastic, steel parts zinc plated, blue passivated finish • Screw-on flange Zinc die-cast

Zinc die-cast / plastic

Black, RAL 9005, textured finish

Red, RAL 3000, textured finish

- Powder coated Black, matte finish
- RoHS compliant