



Metric table

Ų	2 Dimensions in: millimeters - incl										
r	d₁ Thread	b	d ₂	d ₃	I ₁	I ₂	I ₃	I ₄	Max. load F		
45	M 6	13	19	9	12	13	8.5	0.5	500 N		
1.77		<i>0.51</i>	<i>0.75</i>	<i>0.35</i>	0.47	<i>0.51</i>	<i>0.33</i>	<i>0.02</i>	112 lbf		
65	M 8	18	25	14	14	16	10.5	0.6	1000 N		
2.56		0.71	0.98	0.55	<i>0.55</i>	<i>0.63</i>	<i>0.41</i>	0.02	225 lbf		

Specification

Stainless steel (A2) RoHS compliant

• Lever arm Zinc die-cast Powder coated Black, RAL 9005, textured finish Silver, RAL 9006, textured finish	● SW ● SR
Latch housing Stainless steel	
Countersunk screw DIN 7991	

Information

4

GN 720 stop latches may be used as stops, and feature a high degree of stability.

The internal ball spring latch housing has four latching positions at a distance of 90° each. Thanks to the bolt attachment using the countersunk screw, the latching position can be easily selected.

The latch arm is solid and may be machined, if required.

The countersunk screw is enclosed as part of the set.

^{3.10}

How to order		Length r		
	2	Handle diameter d ₁		
	3	Туре	~	
GN 720-65-M8-A-SW	4	Color	40	

3.1

3.7

3.6