

### **SPECIFICATION SHEET**

SPECIFICATION SHEET NO.	Q0130- YG50M00000S410				
DATE	Jan. 30, 2023				
REVISION	A1				
DESCRIPITION	MHz Plastic SMD Crystals, L8.0*W3.8*H2.5mm, 4 Pads, CCMD series				
	50.00000MHz, Tolerance +/-20ppm, Load Capacitor 10pF,				
	Frequency stability +/-30ppm @Operating Temp. Range -40°C ~+85°C,				
	ESR 40 ohm Max, Reflow Profile Condition 260 °C Max.				
	Tape/Reel, 3000pcs/Reel				
	RoHS/RoHS III compliant, RoHS Annex III lead Exemption (exempt per RoHS				
	EU 2015/863)				
CUSTOMER					
CUSTOMER PART NUMBER					
CROSS REF. PART NUMBER					
ORIGINAL PART NUMBER	TGS CCMD 50M0A20-10-30-40-40TLH				
PART CODE	YG50M00000S410				

#### **VENDOR APPROVE**

Issued/Checked/Approved







DATE: Jan. 30, 2023

CUSTOMER APPROVE					
DATE:					

1/30/2023



### MHZ PLASTIC SMD CRYSTALS 8038 TYPE CCMD SERIES

#### **MAIN FEATURE**

- SMD Package, 8038 Type, L8.0\*W3.8\*H2.5mm, 4 Pads
- Low cost and short lead time
- Industry standard
- Reflow Profile Condition 260 °C Max.
- Cross more competitors part
- RoHS/RoHS III compliant, RoHS Annex III lead Exemption (exempt per RoHS EU 2015/863)

#### **APPLICATION**

- Clock source for Portable
- Microcomputer & Automotive Equipment with Low power consumption

#### **PART CODE GUIDE**



YG	50M00000	50M00000 S	
1	2	3	4

- 1) YG: Part family Code for MHz Plastic SMD Crystals, L8.0\*W3.8\*H2.5mm, 4 Pads, CCMD series
- 2) 50M00000: Frequency range code for 50.000MHz
- 3) S: SMD type, Package Tape/Reel, 3000pcs/Reel
- 4) 410: Specification code for original part No.: TGS CCMD 50M0A20-10-30-40-40TLH

1/30/2023 2


### MHZ PLASTIC SMD CRYSTALS 8038 TYPE CCMD SERIES

### **DIMENSION (Unit: Inch/mm)**

#### Image for reference




#### **CCMD**




### Marking

Frequency Range




# 0.035 Ref (0.9)




#### Note:

- Do not connect pad 2 and Pad 3 to external devices.
- Metal inside may be exposed on the top or bottom of plastic case
- It isn't Quality problem. This will not affect any quality, reliability and electrical specification when used

#### **Recommend Pad Layout**





#### Pin Function

#1 Crystal

#2 Ground

#3 Ground

#4 Crystal

3



# MHZ PLASTIC SMD CRYSTALS 8038 TYPE CCMD SERIES

#### **ELECTRICAL PARAMETERS**

Paramet	ter	Part No. Symbol	Units	Value			Condition
				Min.	Typical	Max.	
Original	Manufacturer	TGS		TGS C	Crystals		
Holder T	<sup>-</sup> уре	CCMD	MHz SMD Ci	rystal, Plastic	case, L8.0*W3.8	3*H2.5mm	
Frequen	cy Range	50M0	MHz		50.0000		
Mode of	f Oscillation	А			AT Fundamenta	ıl	
Frequen	cy Tolerance	20	ppm	-20		+20	@25°C
Load Ca <sub>l</sub>	pacitance	-10	pF		10		
Stability Operation	over on Temperance	-30	ppm	-30		+30	
Operation	on Temperance	-40	°C	-40		+85	
Storage	Temperance		°C	-55		+125	
Equivale Resistan	ent Series ace (ESR)	-40	Ω			40	
Drive Le	vel		μW			100	
Shunt Ca	apacitance (CO)		pF	0		7.0	
Motiona (C1)	al Capacitance		fF	N/A			
DLD2			Ω	N/A			
FLD2			ppm	N/A			
RDL2			Ω	N/A			
SPDB			dB	N/A			
Aging			ppm/year			±5	@1 <sup>st</sup> year
Insulatio	on Resistance		ΜΩ	500			@100VDC ± 15VDC
	Package	Т	Tape/Reel				
RoHS Status Others		LH	RoHS III compliant, RoHS Annex III lead Exemption (exempt per RoHS EU 2015/863				
2	Add Value			N	I/A		
	Code *			Internal Co	ntrol or N/A		

Note: 1) Original Part Number: TGS CCMD 50M0A20-10-30-40-40TLH

2) \* Internal Control Code- 2 letter or digits; Blank: N/A

1/30/2023 4

### MHZ PLASTIC SMD CRYSTALS 8038 TYPE CCMD SERIES

#### **TEST STANDARD**

#### **General Electrical Characteristics And Visual testing**

1. LOT CLASSIFICATION: If The Quantity Is 1000 PCS Or More, 1000 PCS Is One Lot

2. Sampling Test Method: Mil-std-105e G-ii

3.Test Level

A) High Level Defect : AQL 0.065% [200 Pcs]
B) Medium Level Defect : AQL 0.25% [50 Pcs]

C) Low Level Defect :AQL 0.4% [32 Pcs]

4. Defect Classification:

A) High Level: @No Frequency; @Mixing; @Leak Defect


B) Medium Level - Electrical Characteristic Defect:


@Frequency; @Oscillation; @Electrical Current; @Other Electrical Characteristics Defect

C) Visual: @Marking; @Welding; @Leads; @Other Visual Defect

Testing Method And Its Standard Can Be Modified Depending On The Customer's Request

#### **EQUIVALENT CIRCUITS**





Symbol for crystal unit



### MHZ PLASTIC SMD CRYSTALS 8038 TYPE CCMD SERIES

#### **CHARACTERISTICS**

Units and values indicated with { } in this specification are the former units and the specified values.

#### **Standard Atmospheric Conditions:**

Unless otherwise specified the standard range of atmospheric conditions for making measurements and tests is as

follows:

Ambient temperature: 15°C to 35°C;

Relative humidity: 25% to 85%;

Air pressure: 86 to 106 k Pa

If there is any doubt about the results measurements shall be made within the following limits:

Ambient temperature : 25±1°C;

Relative humidity : 63% to 67%;

Air pressure: 86 to 106 k Pa

#### **Operating Temperature Range:**

The operating temperature range is the range of ambient temperatures at which the quartz crystal oscillator can be stored without damage. Conditions are as specified elsewhere on these specifications.

Operating temperature range: -40°C to +85°C

#### **Storage Temperature Range:**

The storage temperature range is the range of ambient temperatures at which the quartz crystal oscillator can be stored without damage. Conditions are as specified elsewhere on these specifications.

Storage temperature range: -55°C to +125°C



### MHZ PLASTIC SMD CRYSTALS 8038 TYPE CCMD SERIES

#### **CAUTION**

In Order To Maintain Quality. Without Change In Characteristics Of The crystal Units. Please Follow Below Recommendation

#### Shock

All Crystal Units Have A Thin Crystal Blanks Within If It Is Dropped Above The Recommended Dropping Height (500mm) The Specific Characteristics And Appearance Can Be Changed Please Pay Special Attention To External Shock

#### **Environmental**

- Crystal Units' Frequency Can Be Changed Due To Surrounding Temperature If It Is Stored Next To A High Temperature Heter (Above+85'c) Or Below 40'c.And A Strong Light Source For Long Period Of Time. The Electrical Characteristics Can Be Changed It Is Suggested That These Environment Be Avoided
   If The Unit Is Placed In A Humid Environment. Lead Terminal Can Be Damaged: Therefore. Do Not Store The Crystal Units In A Humid Environment
- 3) Crystal unit Has Vibrating Characteristics If It Is Placed Where Vibration Exists The Operating Characteristics Can Be Altered: Therefore This Environment Should Be Avoided

#### Leads

1) After Soldering Crystal Units Into A PCB Impacting The Unit From The top, bottom Left Or Right Side Of The Unit Can Shatter The Glass Portion Of The Base Aendering The Unit Useless

#### **Assembly Method**

- 1) Correct Ultrasonic Frequency For Cleaning Should Be Less Than 20khz
- 2) SOLDERING SHOULD BE BONE USING IEC 61760-1 OR Pb-free Products

#### **Storage**

5.5.1 If The Crystal Units Are Stored In Humid Or Salty Environment Appearance Can Be Changed And Solderability Can Deteriorate; Therefore avoid Storing In Such Environment Do Not Store The Crystal Unit More Than 3 Months



### MHZ PLASTIC SMD CRYSTALS 8038 TYPE CCMD SERIES

### **RELIABILITY (MECHANICAL AND ENVIRONMENTAL ENDURANCE)**

TEST ITEMS	TEST METHOD AND CONDITIONS	REQUIREMENTS
Vibration	(1) Vibration Frequency: 10 To 55hz	Frequency Change:
	(2) Vibration Amplitude: 1.5mm	±10ppm Max.
	(3) Cycle Time: 1~2min(10-55-10hz)	Resistance Change:
	(4) Direction: X.Y.Z	± 15% RRMax
	(5) Duration: 2h/Each Direction	
	(6) G-force: ≥5g	
SHOCK	3 Times Free Drop From 75cm Height To Hard Wooden	Frequency Change:
	Board Of Thickness More Than 30mm.	±10ppm Max.
		Resistance Change:
		± 15% RRMax.
LEAKAGE	Put Crystal Units Into A Hermetic Container And Helium	Leakage:1x10 <sup>-</sup> 8mbar.L/S
	For 0.5-0.6. MPA and Keep It For 1h;check The Leakage	Max.
	By A Helium Leak Detector.	
SOLDERABILITY	(1) Dip The Leads Into Flu X (ROJIN Methanol) For 3~5s.	The Dipped Part Of The
	(2) Dip The Leads Into 245±5°C 99% Sn Dipping Solution	Leads Should Have
	For 5s.	95% SN Coating.
SOLDERING HEAT RESISISTANCE	(1) Perform Electrical Characteristics Test Before Starting	Should Pass Sealing
TEST	This Procedure.	And Visual Test.
	(2) Dip The Leads Into Flux(rojin Methanol) 5±0.5s.	Frequency Change:
	(3) Dip The Leads Into 260±5°C 99% Sn Dipping Solution	±10ppm Max.
	For 5s.	
	(4) Take The Unit Out ,Store At Room Temper For 30s	
	Then Measure The Electrical Characteristics.	
LEAK TEST	Use Helium Leak Detector.	Gas Or Air Should Not
	Bombing Pressure:5kg/Cm <sup>2</sup>	Be Detected.
	Bombing Time: 2 Hours	
	Leak Should Be Less Than 1e-8 Atm. Cc/Sec.	



## MHZ PLASTIC SMD CRYSTALS 8038 TYPE CCMD SERIES

### RELIABILITY (MECHANICAL AND ENVIRONMENTAL ENDURANCE)

Test Items	Test Method And Conditions	Requirements
HIGH TEMPERATURE	The Crystal Units Shall Be Put In	Frequency Change:
ENDURANCE	Somewhere For 500 Hours At Temperature Of	±10ppm Max.
	125°C ±5°C ,Then Keep It For 1 To 2 Hours Under	Resistance Change:
	Room Temperature.	± 15%rrmax.
LOW TEMPERATURE	The Crystal Units Shall Be Put In Somewhere For 500 Hours	Frequency Change:
ENDURANCE	At Temperature Of -40°C ,Then Keep It For 1 To 2 Hours	±10ppm Max.
	Under Room.	Resistance Change:
		± 15% RRMax
HUMIDITY	Somewhere At 40°C ±5°C In Relative Humidity Of 90%~95%	Frequency Change:
ENDURANCE	For 72 Hours, Then Keep It For One Or Two Hours Under	±10ppm Max.
	Room Temperature	Resistance Change:
	·	± 15% RRMax
TEMPERATURE	Temperature Shift From Low(-40°C ) To High(100°C,keep 30	Frequency Change:
CYCLE	Minutes),satisfy High(100°C ) To Low(-40°C ,Keep 30	±10ppm Max.
	Minutes), then Go Up To Room Temperature For 10 Cycles.	Resistance Change:
		± 15% RRMax
LEAD	(1) Fix The Unit.	Should Pass
TENSILTY	(2) Apply 2lb Of Weight Axis To The Leads.	Sealing And Visual
	(3) Time:5s	Test.
LEAD BENDING	(1) Attach 1lb Of Weight To Each Of The Leads.	Should Pass
	(2) Bending Angle:90°(from The Nomal Position To	Sealing And Visual
	45°oppostte Direction)	Test.
	(3) Bending Time:3s(each Direction) Number Of	
	Bending:2times	
	(4) Number Of Bending:2times	
MARKING	Submerge The Unit Into Ipa [isopropyl Alcohol] Solution For	Marking Should Not
ERASE	10minutes And Brush The Marking 10 Times With A Tooth	Be Erased.
	Brush.	25 2.4564.
	DI WOITI	

1/30/2023

### MHZ PLASTIC SMD CRYSTALS 8038 TYPE CCMD SERIES

### **SUGGESTED REFLOW PROFILE (For Reference Only)**

Total time: 200 Sec. Max. Solder melting point: 220°C




Profile Feature		Pb-Free Assembly	
Average Ramp-up Rate (Ts Max to Tp)		3°C/second Max	
Preheat	Temperature Min (Ts Min.)	125°C	
	Temperature Max (Ts Max.)	200°C	
	Time (ts Min. to ts Max.)	60 ~ 180 seconds	
Time maintained above	Temperature (TL)	217°C	
	Time (tL)	60 ~ 150 seconds	
Peak/Classification Temperature (Tp)		260 °C	
Time within 5°C of actual Peak Temperature (tp)		20 ~ 40 seconds	
Ramp-down rate		6 °C /Second Max.	
Time 25 °C to Peak Temperature		8 minutes Max.	
Suggest reflow times		3 Times Max.	


1/30/2023

### MHZ PLASTIC SMD CRYSTALS 8038 TYPE CCMD SERIES

### TAPE/REEL (Unit: mm)

All Devices are packed in accordance with EIA standard RS-481-2 and specifications, 3000pcs/Reel





Pieces per reel	φm	φп	L	Carrier tape size	
3000/reel	330±3	80min	17.5	16	

#### **DISCLAIMER**

NextGen Components, Inc. reserves the right to make changes to the product(s) and or information contained herein without notice. No liability is assumed as a result of their use or application. No rights under any patent accompany the sale of any such product(s) or information

1/30/2023 11