

East Electronics



Product Specification

48273 Lakeview Blvd

Fremont, CA 94538, U.S.A

Tel: 510-413-0002

Fax: 510-413-0010

http://www.east-elec.com

Product Name:	Speaker	
Part Number:	SCM-36R4.8-8N1R	(8Ω 1W)
Version:	Rev. 1	
Date:	2020-3-31	
Note:		

Company passed ISO 9001 / ISO TS16949 / ISO 14001 Certifications


Revision History

- to the total metals					
Rev.	Description	Author/Date	Checked By	Approver	
1	Released	Lv Wenbin March 31. 2020	Gao Rong	Wang Jiancheng	

East Electronics 1/5

1. Part Number: SCM-36R4.8-2N1R

2. Dimension Drawing: (Unit: mm)



3. Specification:


No.	Items	Specification		
3-1	Rated impedance	8Ω± 15 % at 2 kHz		
3-2	Resonant frequency (f0)	570Hz ± 20 % 1.0 V		
3-3	SPL normal power input	100dB±3 0.1M/1W (800,1000,1200,1500,Hz average) 2.83 V		
3-4	Frequency range	f0 ~6 kHz SPL-10dB 2.83 V		
3-5	Distortion	< 10 % at 1kHz 2.83V		
3-6	Normal power	1 W @ Rated noise power operating continuously for 100 hours 2.83 V		
3-7	Maximum power	1.5 W @ Stimulant program signal for 1 min. on & 2 min. off, cycling for 10 times 3.46 V		
3-8	Appearance normal @ A.T. 15~35℃, H.M. 25~75%, B.P. 86~106kPa			
3-9	Buzzes & rattles no appearance	@ 0.3m with sine wave from 100Hz to 4 kHz input/rated noise power 2.83 V		
3-10	Diaphragm material	Mylar		
3-11	Weight	8.8 g		

NOTES:

- 1. Test in anechoic room and use the IEC standard baffler which size at: 1350 mm (W) X 1650 mm (H)
- 2. Test should be made under the conditions of room temperature (20 ± 10 °C), relative humidity ($60 \pm 20\%$) and normal atmospheric pressure. In this case, however, that the judgment is questionable, the test conditions are to be changed to room temperature 20 ± 2 °C, relative humidity $60 \sim 70\%$ and normal atmospheric pressure.

East Electronics 2/5

4. Typical Frequency Response Curve:



Frequency(Hz)	300-600	800-2K	2.5K-4.0K	4.2K-7K	7.1K-12K
Upper limit	+5	+3	+4	+6	+15
Lower limit	-5	-3	-4	-6	-15

5. Reliability Test:


No.	ltem	Method of Test	Tolerance after Testing
5-1	Operating temperature	-40 °C ~ +85 °C	
5-2	High-temperature loading & storage	@ $\frac{1}{4}$ rated noise power /85 ± 2 °C operating for 16 hours then depositing for 2 hours at constant temperature, completing testing within 1 hour after withdrawing.	Meet requirements of appearance Suzzes & rattles after test
5-3	Low-temperature loading & storage	@ $1/4$ rated noise power/-10 \pm 3 °C operating for 1 hours, depositing @ -25 \pm 3 °C for 2 hours, then resuming at normal atmosphere conditions (GB/T9396-1996 4.2) for 4 hours.	Meet requirements of appearance Buzzes & rattles, solderability after test
5-4	Static humidity /temperature	@ A.T. 40 ± 2 °C, H.M. 93 ± 2 % depositing for 48 hours, then resuming @ normal atmosphere conditions (GB/T9396-1996 4.2) for 24 hours.	Meet requirements of appearance, Buzzes & rattles, insulation resistance, bearing voltage after test
5-5	Temperature (high and low) cycle test	Storage in -40 °C \pm 5 °C for 2 hours, in 20 °C \pm 5 °C for 2 hours, in 85 °C \pm 5 °C for 2 hours then back in 20 °C \pm 5 °C 2 hours, as one cycle. 12 cycle in total.	Appearance: no obviously damage

East Electronics 3/5

5-6		Drop a product naturally from the height of 1000 mm onto the	Tone: no obviously noise
		surface of 100 mm thick wooden board. Two directions: upper	
	Drop test	and side of the product are to be applied for this drop test once	
		respectively.	SPL±3dB
5-7	Life test in the room temperature	Input the signal with the valid frequency range on the speaker in continuously for 100 hours, the room temperature should control in 15 °C to 35 °C.	F0 ±20%
		Conduct the test for the directions of XY and Z for 0.5 hour each	ACR±15%
5-8	N. Charles Co.	(total 1.5 hours). To-and Fri sweep time(from 10 to 55 Hz and	
3-0	Vibration test	then 55 to 10) under single amplitude of 0.75 mm is 3 minute,	
		then expose to the room temperature for 2 hours.	


 $\label{NOTE: NOTE: The frame is allowed to deform after drop test.}$

6. Electrical Testing Method:



East Electronics 4/5

7. Packing Information:



Packing information:

40pcs per tray

9trays for unit, 2units per carton

Total:720 pcs per box Size:42*32*35cm

East Electronics 5/5