	Date	04-Jun-2021	SPECIFICATION	OLE WOLFF
	Page	1 / 3		www.owolff.com
	CN	P/N: OWPB-2002-36-A		Revision: 06



SPECIFICATION FOR APPROVAL

Piezo Element

Part Number	OWPB-2002-36-A
Note	This item was compliance with the following requirements: 1. RoHS directive 2. REACH
Customer P/N	

		Prepared	Checked	Approved
	Signature / Date	Baoxin Yao 2021.6.4		

		Confirmation		
Customer	Signature / Date			

REVISION NOTES:

Date	Rev.	Description of Revision
20180312	00	Initial Release
20180709	01	Add Packing and Cool Gray paint area.
20180710	02	Remove Cool Gray paint area.
20181022	03	Diameter $\Phi 20 \pm 0.2$ changed to $\Phi 20 + 0 / - 0.2$
20190531	04	Add black paint area. Thickness(T) 0.205 ± 0.05 changed to 0.23 ± 0.05
20190611	05	Diameter $\Phi 17.5 + 0.2 / - 0.3$ changed to $\Phi 12 \pm 0.3 \text{mm}$
20210604	06	1.去除 5a。2.包装增加警示要求“CAUTION Please use it within 24hrs after open the package. If not, please keep in the vacuum package”。详见 Packing。

OLE WOLFF
ELEKTRONIK A/S
Roedengvej 25
4180 Soroe
Denmark
TEL: +45 57833830
FAX: +45 57820019

OLE WOLFF
ELECTRONICS INC.
1525 McCarthy Blvd,
Suite 1093
Milpitas, Ca 95035
USA
TEL: +1 408 888 8413


OLEWOLFF
ELEKTRONIK GmbH
Schulstrasse 15A. DE-25451
Quickborn,
Germany
TEL: +49 (0) 4106 765900
FAX: +49 (0) 4106 627297

OLEWOLFF ELECTRONICS
3 Bedford Street, Woburn,
Bedfordshire MK17 9QB,
ENGLAND
TEL: +44 (0) 1525 290755
FAX: +44 (0) 1525 290855


OLE WOLFF
ELEKTRONIK
Yliopistonkatu 26 (P.O.BOX
257)
FI-40101 Jyväskylä
Finland
TEL: +358 14 338 3050
FAX: +358 14 338 3059

OLE WOLFF (ASIA) LTD.
Unit B, 19/F.,
Bold Win Ind. Bldg.,
No. 16-18 Wah Sing St.,
Kwai Chung, N.T., H.K.
TEL: +852 2424 3274
FAX: +852 2424 2219


OLE WOLFF LTD.
Unit 7A08, Block 2, Elite
Building, Nanshan Avenue,
Nanshan District,
Shenzhen, PRC.
TEL: +86 755 82612542
TEL: +86 755 26406156

	Date	04-Jun-2021	SPECIFICATION	OLE WOLFF
	Page	3 / 3		www.owolff.com
	CN	P/N: OWPB-2002-36-A		Revision: 06

Concentricity and Roundness for Double-sided Tape.



Packing



1. 1080PCS per box
2. Total 12 boxes per carton
3. Total 12960 PCS carton
4. Volume: 33*21.5*13.5cm

OLE WOLFF ELEKTRONIK A/S Roedengvej 25 4180 Soroe Denmark TEL: +45 57833830 FAX: +45 57820019	OLE WOLFF ELECTRONICS INC. 1525 McCarthy Blvd, Suite 1093 Milpitas, Ca 95035 USA TEL: +1 408 888 8413	OLEWOLFF ELEKTRONIK GmbH Schulstrasse 15A. DE-25451 Quickborn, Germany TEL: +49 (0) 4106 765900 FAX: +49 (0) 4106 627297	OLEWOLFF ELECTRONICS 3 Bedford Street, Woburn, Bedfordshire MK17 9QB, ENGLAND TEL: +44 (0) 1525 290755 FAX: +44 (0) 1525 290855	OLE WOLFF ELEKTRONIK Yliopistonkatu 26 (P.O.BOX 257) FI-40101 Jyväskylä Finland TEL: +358 14 338 3050 FAX: +358 14 338 3059	OLE WOLFF (ASIA) LTD. Unit B, 19/F., Bold Win Ind. Bldg., No. 16-18 Wah Sing St., Kwai Chung, N.T., H.K. TEL: +852 2424 3274 FAX: +852 2424 2219	OLE WOLFF LTD. Unit 7A08, Block 2, Elite Building, Nanshan Avenue, Nanshan District, Shenzhen, PRC. TEL: +86 755 82612542 TEL: +86 755 26406156
---------------------------------------------------------------------------------------------------------------------	-----------------------------------------------------------------------------------------------------------------------------	------------------------------------------------------------------------------------------------------------------------------------------------	----------------------------------------------------------------------------------------------------------------------------------------------------	------------------------------------------------------------------------------------------------------------------------------------------------------	------------------------------------------------------------------------------------------------------------------------------------------------------------------------	-----------------------------------------------------------------------------------------------------------------------------------------------------------------------