20 V, single N-channel Trench MOSFET 12 September 2012

**Product data sheet** 

### 1. Product profile

### 1.1 General description

N-channel enhancement mode Field-Effect Transistor (FET) in a leadless medium power DFN2020MD-6 (SOT1220) Surface-Mounted Device (SMD) plastic package using Trench MOSFET technology.

### **1.2 Features and benefits**

- Trench MOSFET technology
- Small and leadless ultra thin SMD plastic package: 2 x 2 x 0.65 mm
- Exposed drain pad for excellent thermal conduction
- Tin-plated 100 % solderable side pads for optical solder inspection

### **1.3 Applications**

- Charging switch for portable devices
- DC-to-DC converters
- Power management in battery-driven portable devices
- Hard disk and computing power management

### **1.4 Quick reference data**

Table 1. Qui	ck reference data						
Symbol	Parameter	Conditions		Min	Тур	Max	Unit
V <sub>DS</sub>	drain-source voltage	T <sub>j</sub> = 25 °C		-	-	20	V
V <sub>GS</sub>	gate-source voltage			-8	-	8	V
I <sub>D</sub>	drain current	$V_{GS}$ = 4.5 V; $T_{amb}$ = 25 °C; t ≤ 5 s	[1]	-	-	9.4	А
Static characteristics							
R <sub>DSon</sub>	drain-source on-state resistance	V <sub>GS</sub> = 4.5 V; I <sub>D</sub> = 6.6 A; T <sub>j</sub> = 25 °C		-	19	25	mΩ

[1] Device mounted on an FR4 Printed-Circuit Board (PCB), single-sided copper, tin-plated, mounting pad for drain 6 cm<sup>2</sup>.





20 V, single N-channel Trench MOSFET

### 2. Pinning information

Table 2.	Pinning	information			
Pin	Symbol	Description	Simplified outline	Graphic symbol	
1	D	drain		D	
2	D	drain			
3	G	gate		G C C	
4	S	source		\$ 017aaa253	
5	D	drain	Transparent top view	Transparent top view	C T ABALOO
6	D	drain	DFN2020MD-6 (SOT1220)		
7	D	drain			
8	S	source			

### 3. Ordering information

Table 3. Orderin	g information		
Type number	Package		
	Name	Description	Version
PMPB20UN	DFN2020MD-6	plastic thermal enhanced ultra thin small outline package; no leads; 6 terminals	SOT1220

### 4. Marking

Table 4. Marking codes	
Type number	Marking code
PMPB20UN	1G

# 5. Limiting values

#### Table 5. Limiting values

In accordance with the Absolute Maximum Rating System (IEC 60134).

Symbol	Parameter	Conditions		Min	Max	Unit
V <sub>DS</sub>	drain-source voltage	T <sub>j</sub> = 25 °C		-	20	V
V <sub>GS</sub>	gate-source voltage			-8	8	V
I <sub>D</sub>	drain current	V <sub>GS</sub> = 4.5 V; T <sub>amb</sub> = 25 °C; t ≤ 5 s	[1]	-	9.4	А
		V <sub>GS</sub> = 4.5 V; T <sub>amb</sub> = 25 °C	[1]	-	6.6	А
		V <sub>GS</sub> = 4.5 V; T <sub>amb</sub> = 100 °C	[1]	-	4.1	А
I <sub>DM</sub>	peak drain current	$T_{amb}$ = 25 °C; single pulse; $t_p \le 10 \ \mu s$		-	27	А
P <sub>tot</sub>	total power dissipation	T <sub>amb</sub> = 25 °C	[1]	-	1.7	W
MPB20UN	All info	ormation provided in this document is subject to legal disclaimers.		©N	XP B.V. 2012. /	All rights reser


### **NXP Semiconductors**

### PMPB20UN


#### 20 V, single N-channel Trench MOSFET

Symbol	Parameter	Conditions		Min	Мах	Unit
		T <sub>amb</sub> = 25 °C; t ≤ 5 s	[1]	-	3.5	W
		T <sub>sp</sub> = 25 °C		-	12.5	W
Tj	junction temperature			-55	150	°C
T <sub>amb</sub>	ambient temperature			-55	150	°C
T <sub>stg</sub>	storage temperature			-65	150	°C
Source-drai	in diode					_
I <sub>S</sub>	source current	T <sub>amb</sub> = 25 °C	[1]	-	1.8	А

[1] Device mounted on an FR4 Printed-Circuit Board (PCB), single-sided copper, tin-plated, mounting pad for drain 6 cm<sup>2</sup>.



#### 20 V, single N-channel Trench MOSFET




### 6. Thermal characteristics

Table 6. Th	nermal characteristics						
Symbol	Parameter	Conditions		Min	Тур	Max	Unit
R <sub>th(j-a)</sub>	thermal resistance	in free air	[1]	-	235	270	K/W
	from junction to ambient		[2]	-	67	74	K/W
	ampient	in free air; t ≤ 5 s	[2]	-	33	36	K/W
R <sub>th(j-sp)</sub>	thermal resistance from junction to solder point			-	5	10	K/W

[1] Device mounted on an FR4 PCB, single-sided copper, tin-plated and standard footprint.

[2] Device mounted on an FR4 PCB, single-sided copper, tin-plated, mounting pad for drain 6 cm<sup>2</sup>.

#### 20 V, single N-channel Trench MOSFET



### 7. Characteristics


Parameter	Conditions	Min	Тур	Max	Unit
teristics					
drain-source breakdown voltage	$I_D$ = 250 µA; $V_{GS}$ = 0 V; $T_j$ = 25 °C	20	-	-	V
gate-source threshold voltage	$I_D$ = 250 µA; $V_{DS}$ = $V_{GS}$ ; $T_j$ = 25 °C	0.4	0.7	1	V
drain leakage current	$V_{DS}$ = 20 V; $V_{GS}$ = 0 V; $T_j$ = 25 °C	-	-	1	μA
gate leakage current	$V_{GS}$ = -8 V; $V_{DS}$ = 0 V; $T_j$ = 25 °C	-	-	-100	nA
	teristics drain-source breakdown voltage gate-source threshold voltage drain leakage current	teristicsdrain-source breakdown voltage $I_D = 250 \ \mu A; \ V_{GS} = 0 \ V; \ T_j = 25 \ ^C$ gate-source threshold voltage $I_D = 250 \ \mu A; \ V_{DS} = V_{GS}; \ T_j = 25 \ ^C$ drain leakage current $V_{DS} = 20 \ V; \ V_{GS} = 0 \ V; \ T_j = 25 \ ^C$	teristicsdrain-source breakdown voltage $I_D = 250 \ \mu\text{A}; \ V_{GS} = 0 \ V; \ T_j = 25 \ ^C$ 20gate-source threshold voltage $I_D = 250 \ \mu\text{A}; \ V_{DS} = V_{GS}; \ T_j = 25 \ ^C$ 0.4drain leakage current $V_{DS} = 20 \ V; \ V_{GS} = 0 \ V; \ T_j = 25 \ ^C$ -	teristicsdrain-source breakdown voltage $I_D = 250 \ \mu A; \ V_{GS} = 0 \ V; \ T_j = 25 \ ^C$ 20-gate-source threshold voltage $I_D = 250 \ \mu A; \ V_{DS} = V_{GS}; \ T_j = 25 \ ^C$ 0.40.7drain leakage current $V_{DS} = 20 \ V; \ V_{GS} = 0 \ V; \ T_j = 25 \ ^C$	teristicsdrain-source breakdown voltage $I_D = 250 \ \mu\text{A}; \ V_{GS} = 0 \ V; \ T_j = 25 \ ^C$ $20 \ -$ -gate-source threshold voltage $I_D = 250 \ \mu\text{A}; \ V_{DS} = V_{GS}; \ T_j = 25 \ ^C$ $0.4 \ 0.7 \ 1$ drain leakage current $V_{DS} = 20 \ V; \ V_{GS} = 0 \ V; \ T_j = 25 \ ^C$


Product data sheet

#### 20 V, single N-channel Trench MOSFET

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
		$V_{GS}$ = 8 V; $V_{DS}$ = 0 V; $T_j$ = 25 °C	-	-	100	nA
R <sub>DSon</sub>	drain-source on-state	$V_{GS}$ = 4.5 V; I <sub>D</sub> = 6.6 A; T <sub>j</sub> = 25 °C	-	19	25	mΩ
	resistance	V <sub>GS</sub> = 4.5 V; I <sub>D</sub> = 6.6 A; T <sub>j</sub> = 150 °C	-	30	39	mΩ
		$V_{GS}$ = 2.5 V; I <sub>D</sub> = 5.6 A; T <sub>j</sub> = 25 °C	-	25	34	mΩ
		$V_{GS}$ = 1.8 V; I <sub>D</sub> = 1.7 A; T <sub>j</sub> = 25 °C	-	36	57	mΩ
9fs	forward transconductance	V <sub>DS</sub> = 10 V; I <sub>D</sub> = 6.6 A; T <sub>j</sub> = 25 °C	-	25	-	S
R <sub>G</sub>	gate resistance	f = 1 MHz	-	1.2	-	Ω
Dynamic c	haracteristics			I		
Q <sub>G(tot)</sub>	total gate charge	$V_{DS}$ = 10 V; I <sub>D</sub> = 6.6 A; V <sub>GS</sub> = 4.5 V;	-	4.7	7.1	nC
Q <sub>GS</sub>	gate-source charge	T <sub>j</sub> = 25 °C	-	0.8	-	nC
Q <sub>GD</sub>	gate-drain charge		-	1.2	-	nC
C <sub>iss</sub>	input capacitance	V <sub>DS</sub> = 10 V; f = 1 MHz; V <sub>GS</sub> = 0 V;	-	460	-	pF
C <sub>oss</sub>	output capacitance	T <sub>j</sub> = 25 °C	-	135	-	pF
C <sub>rss</sub>	reverse transfer capacitance	_	-	75	-	pF
t <sub>d(on)</sub>	turn-on delay time	$V_{DS}$ = 10 V; I <sub>D</sub> = 6.6 A; V <sub>GS</sub> = 4.5 V;	-	7	-	ns
t <sub>r</sub>	rise time	R <sub>G(ext)</sub> = 6 Ω; T <sub>j</sub> = 25 °C	-	19	-	ns
t <sub>d(off)</sub>	turn-off delay time		-	17	-	ns
t <sub>f</sub>	fall time		-	26	-	ns
Source-dra	in diode	1	· · ·			
V <sub>SD</sub>	source-drain voltage	$I_{\rm S}$ = 1.8 A; $V_{\rm GS}$ = 0 V; $T_{\rm j}$ = 25 °C	-	0.7	1.2	V

1.2







gate-source voltage

© NXP B.V. 2012. All rights reserved

#### 20 V, single N-channel Trench MOSFET




#### 20 V, single N-channel Trench MOSFET




### **NXP Semiconductors**

## PMPB20UN

#### 20 V, single N-channel Trench MOSFET




### 8. Test information



20 V, single N-channel Trench MOSFET

### 9. Package outline




PMPB20UN

All information provided in this document is subject to legal disclaimers.

20 V, single N-channel Trench MOSFET

### 10. Soldering



### 20 V, single N-channel Trench MOSFET

# **11. Revision history**

Table 8. Revision his	e 8. Revision history				
Data sheet ID	Release date	Data sheet status	Change notice	Supersedes	
PMPB20UN v.1	20120912	Product data sheet	-	-	

#### 20 V, single N-channel Trench MOSFET

### **13. Contents**

1	Product profile1
1.1	General description1
1.2	Features and benefits1
1.3	Applications1
1.4	Quick reference data1
2	Pinning information2
3	Ordering information2
4	Marking2
5	Limiting values2
6	Thermal characteristics4
7	Characteristics5
8	Test information9
9	Package outline 10
10	Soldering 11
11	Revision history12
12	Legal information
12.1	Data sheet status
12.2	Definitions
12.3	Disclaimers
12.4	Trademarks

#### © NXP B.V. 2012. All rights reserved

For more information, please visit: http://www.nxp.com For sales office addresses, please send an email to: salesaddresses@nxp.com Date of release: 12 September 2012