



SPECIFICATION


(Reference sheet)

- Supplier : Samsung electro-mechanics
- Product : Multi-layer Ceramic Capacitor
- Samsung P/N :
- CL03C0R5BA3GNNC
- Description :
- CAP, 0.5pF, 25V, ±0.1pF, C0G, 0201

A. Samsung Part Number

			<u>CL</u>	<u>03</u>	<u>C</u>	<u>0R5</u>	<u>B</u>	<u>A</u>	<u>3</u>	<u>G</u>	<u>N</u>	N	<u>C</u>			
			1	2	3	4	5	6	1	8	9	10	1			
1	Series	Samsung	g Multi-la	iyer C	eran	nic Cap	oacito	or								
2	Size	0201	(inch co	ode)		L:	0.60	± 0.0	3	mm		W:	0.30	± 0.03	mm	
3	Dielectric	C00	6				8	Inner	. elec	trode	•		Cu			
4	Capacitance	0.5	рF					Term	inati	on			Cu			
5	Capacitance	±0.1	рF					Plati	ng				Sn 10	0%	(Pb F	ree)
	tolerance						9	Prod	uct				Norma	al		
6	Rated Voltage	25	V				10	Spec	ial				Reser	ved for	future	use
\bigcirc	Thickness	0.30	± 0.03	mm			1	Pack	aging	g			Cardb	oard Ty	/pe, 7"	reel

B. Structure and dimension



Samsung P/N	Dimension(mm)								
(Lead Free)	L	W	т	BW					
CL03C0R5BA3GNNC	0.60±0.03	0.30±0.03	0.30±0.03	0.15±0.05					

C. Samsung Reliability Test and Judgement condition

	Performance	Test condition				
Capacitance	Within specified tolerance	1M±±10% 0.5~5Vrms				
Q	410 min					
Insulation	10,000Mohm or 500Mohm <i>µ</i> F	Rated Voltage 60~120 sec.				
Resistance	Whichever is smaller					
Appearance	No abnormal exterior appearance	Microscope (×10)				
Withstanding	No dielectric breakdown or	300% of the rated voltage				
Voltage	mechanical breakdown					
Temperature	COG					
Characteristics	(From -55 $^{\circ}$ to 125 $^{\circ}$, Capacitance change should be within ±30PPM/ $^{\circ}$)					
Adhesive Strength	No peeling shall be occur on the	200g·F, for 10±1 sec.				
of Termination	terminal electrode					
Bending Strength	Capacitance change :	Bending to the limit (1mm)				
	within $\pm 5\%$ or $\pm 0.5 \text{pF}$ whichever is larger	with 1.0mm/sec.				
Solderability	More than 75% of terminal surface	SnAg3.0Cu0.5 solder				
	is to be soldered newly	245±5℃, 3±0.3sec.				
		(preheating : 80~120℃ for 10~30sec.)				
Resistance to	Capacitance change :	Solder pot : 270±5℃, 10±1sec.				
Soldering heat	within $\pm 2.5\%$ or ± 0.25 pF whichever is larger					
	Tan δ, IR : initial spec.					
Vibration Test	Capacitance change :	Amplitude : 1.5mm				
	within $\pm 2.5\%$ or ± 0.25 pF whichever is larger	From 10Hz to 55Hz (return : 1min.)				
	Tan δ, IR : initial spec.	2hours \times 3 direction (x, y, z)				
Moisture	Capacitance change :	With rated voltage				
Resistance	within $\pm 7.5\%$ or ± 0.75 pF whichever is larger	40±2℃, 90~95%RH, 500+12/-0hrs				
	Q : 101.67 min					
	IR : 500Mohm or 25Mohm $\cdot \mu F$					
	Whichever is smaller					
High Temperature	Capacitance change :	With 200% of the rated voltage				
Resistance	within $\pm 3\%$ or ± 0.3 pF whichever is larger	Max. operating temperature				
	Q : 205 min	1000+48/-0hrs				
	IR : 1,000Mohm or 50Mohm · μF					
	Whichever is smaller					
Temperature	Capacitance change :	1 cycle condition				
Cycling	within $\pm 2.5\%$ or ± 0.25 pF whichever is larger	Min. operating temperature \rightarrow 25 °C				
	Tan δ, IR : initial spec.	\rightarrow Max. operating temperature \rightarrow 25 °C				
		5 cycle test				

* The reliability test condition can be replaced by the corresponding accelerated test condition.

D. Recommended Soldering method :

Reflow (Reflow Peak Temperature : 260+0/-5°C, 10sec. Max)

A Product specifications included in the specifications are effective as of March 1, 2013.

Please be advised that they are standard product specifications for reference only.

We may change, modify or discontinue the product specifications without notice at any time.

So, you need to approve the product specifications before placing an order.

Should you have any question regarding the product specifications,

please contact our sales personnel or application engineers.