

SPECIFICATION

- Supplier : Samsung electro-mechanics
- Product : Multi-layer Ceramic Capacitor

- Samsung P/N : **CL21X226MQQNNNE**
- Description : **CAP, 22 μ F, 6.3V, \pm 20%, X6S, 0805**

A. Samsung Part Number

CL 21 X 226 M Q Q N N N E
 ① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨ ⑩ ⑪

| | | | | | | | | | | |
|-------------------------|---------------------------------------|----------------------|-----------------------|--------------------------------|--|--|--|--|--|--|
| ① Series | Samsung Multi-layer Ceramic Capacitor | | | | | | | | | |
| ② Size | 0805 (inch code) | L: 2.0 \pm 0.15 mm | W: 1.25 \pm 0.15 mm | | | | | | | |
| ③ Dielectric | X6S | ⑧ Inner electrode | | Ni | | | | | | |
| ④ Capacitance | 22 μ F | Termination | | Cu | | | | | | |
| ⑤ Capacitance tolerance | \pm 20 % | Plating | | Sn 100% (Pb Free) | | | | | | |
| ⑥ Rated Voltage | 6.3 V | ⑨ Product | | Normal | | | | | | |
| ⑦ Thickness | 1.25 \pm 0.15 mm | ⑩ Special | | Reserved for future use | | | | | | |
| | | ⑪ Packaging | | Embossed Type, 7"reel(2,000ea) | | | | | | |

B. Samsung Reliability Test and Judgement condition

| | Performance | Test condition |
|----------------------------------|---|--|
| Capacitance | Within specified tolerance | 120Hz \pm 20% 0.5 \pm 0.1Vrms |
| Tan δ (DF) | 0.1 max. | |
| Insulation Resistance | More than 100Mohm $\cdot\mu$ F | Rated Voltage 60~120 sec. |
| Appearance | No abnormal exterior appearance | Visual inspection |
| Withstanding Voltage | No dielectric breakdown or mechanical breakdown | 250% of the rated voltage |
| Temperature Characteristics | X6S (From -55 $^{\circ}$ C to 105 $^{\circ}$ C, Capacitance change should be within \pm 22%) | |
| Adhesive Strength of Termination | No peeling shall be occur on the terminal electrode | 500g \cdot F, for 10 \pm 1 sec. |
| Bending Strength | Capacitance change : within \pm 12.5% | Bending to the limit (1mm) with 1.0mm/sec. |
| Solderability | More than 75% of terminal surface is to be soldered newly | SnAg3.0Cu0.5 solder 245 \pm 5 $^{\circ}$ C, 3 \pm 0.3sec. (preheating : 80~120 $^{\circ}$ C for 10~30sec.) |
| Resistance to Soldering heat | Capacitance change : within \pm 7.5% Tan δ , IR : initial spec. | Solder pot : 270 \pm 5 $^{\circ}$ C, 10 \pm 1sec. |

| | Performance | Test condition |
|------------------------------------|--|--|
| Vibration Test | Capacitance change : within $\pm 10\%$ Tan δ , IR : initial spec. | Amplitude : 1.5mm From 10Hz to 55Hz (return : 1min.) 2hours \times 3 direction (x, y, z) |
| Moisture Resistance | Capacitance change : within $\pm 12.5\%$ Tan δ : 0.2 max IR : More than $12.5M\Omega \cdot \mu F$ | With rated voltage $40 \pm 2^\circ C$, 90~95%RH, 500+12/-0 hour |
| High Temperature Resistance | Capacitance change : within $\pm 12.5\%$ Tan δ : 0.2 max IR : More than $25M\Omega \cdot \mu F$ | With 100% of the rated voltage Max. operating temperature 1000+48/-0 hour |
| Temperature Cycling | Capacitance change : within $\pm 15\%$ Tan δ , IR : initial spec. | 1 cycle condition Min. operating temperature $\rightarrow 25^\circ C$ \rightarrow Max. operating temperature $\rightarrow 25^\circ C$ 5 cycles test |

C. Recommended Soldering method :

Reflow (Reflow Peak Temperature : $260 \pm 0/-5^\circ C$, 10sec. Max)

* For the more detail Specification, Please refer to the Samsung MLCC catalogue.