

2301P and 2501P Remote Airborne Particle Counters

0.1 CFM (2.83 LPM)





The 2301P and 2501P particle counters provide a range of particle size measurement from 0.3 to 25.0 μ m at 0.1 CFM (2.83 LPM) flow. These sensors allow for efficient particle counting with high accuracy and resolution that meet or exceed ISO 21501-4 and JIS B9921 for the calibration of a particle counter.

These units are equipped with an internal pump and manifold and do not require an external vacuum source. Integration into a building automation or facility monitoring system is easy via standard MODBUS RS-485 communication.

2301P and 2501P: Features and Benefits

- 2301P: Measures 0.3 μm to 25 μm
- 2501P: Measures 0.5 μm to 25 μm
- 0.1 CFM (2.83 LPM) flow rate
- · Long life laser diode technology
- · Measures up to 4 channels of simultaneous data
- Accurate in high particle concentration environments
- Internal vacuum pump
- Internal HEPA filter
- Connect using Modbus RTU/ASCII over isolated RS-485
- · Complies with ISO 21501-4 and JIS B9921 standards
- Easy to clean and wipe down with minimal particle traps
- Versatile mounting options
- · Alarm light
- LED Indicators
- · Seamless integration into a facility monitoring system
- · Lightweight stainless steel enclosure
- 2 year warranty. Extended warranties available.







Specifications

Model	2301P 2501P
Size Range	0.3 μm to 25 μm 0.5 μm to 25 μm
Size Channels	Factory calibrated at 0.3, 0.5, 1.0, 5.0 µm Factory calibrated at 0.5, 1.0, 2.5, 5.0 µm
Number of Channels	4 channels 64 channels
Counting Efficiency	50% @ 0.3μm; 100% for particles > 0.45 μm per JIS 50% @ 0.5μm; 100% for particles > 0.75 μm per JIS
Flow Rate	0.1 CFM (2.83 LPM)
Concentration Limits	10,000,000 particles/ft³ @ 10% coincidence (per ISO 21501-4), 20,000,000 particles/ft³ @ 10% coincidence (as tested and validated¹)
Light Source	Long life laser diode
Zero Count	< 1 count / 60 minutes (< 1 particles /6 ft³)
Calibration	NIST traceable
Vacuum Source	Internal vacuum pump with HEPA filter
Filtered Exhaust	Internal HEPA filter
Airflow	Internally monitored
Alarm	Alarm LED ring
Communication Modes	MODBUS™ RTU or ASCII outputs (over isolated RS-485)
Standards	ISO 21501-4 and JIS B9921
Instrument Calibration	Recommended minimum once per year
External Surface	Stainless steel
Dimensions (L x W x H)	3.59" x 1.83" x 5.66" (9.1 cm x 4.6 cm x 14.3 cm) including probes and connectors
Weight	1.94 lb. (0.88 kg)
Accessories	Wiring Connector, operating manual on USB flash drive
Optional Accessories	Power Supply, Remote Mounting Bracket, Stainless Steel Barbed Isoprobe (0.1 CFM/2.83 LPM), Purge Filter Assembly, and Sample & Vacuum Tubing
Sample Time	1 second to 18 hours
Power	9 - 24 VDC (< 2.5 watts)
Operating Conditions	41° to 104°F (5° to 40°C) / 20% to 95% non-condensing
Storage Conditions	32° to 122°F (0° to 50°C) / Up to 98% non-condensing
Warranty	2 year limited warranty. Extended warranties available.

¹⁻ Validated by independent analysis see paper available at www.particlesplus.com/aac2022_paper



