

K MOPL K21 STAHL

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16 D-32758 Detmold Germany

Fon: +49 5231 14-0 Fax: +49 5231 14-292083 www.weidmueller.com



For many years, the name Klippon® has stood for competence and quality in enclosures. The enclosures are ideal for turnkey customised solutions for standard industrial applications and for explosive-risk applications.

Improved products that meet all application requirements: this was Weidmüller's aim during the update of the Klippon® K housing series. Weidmüller delivers many types of aluminium enclosures; they are designed to fit precisely with a wide range of customer requirements and applications.

Our comprehensive product line provides the following advantages:

- Available in two different surfaces: natural and powdercoated (RAL 7001)
- Available normally with silicone or chloroprene gasket seal
- A uniform Torx-slotted screw head is used for over 19 different housing sizes.
- Mounting holes not within the sealed area
- High degree of protection: IP66, IP67 and IP68
- Impact resistance of up to 10 Joules
- The housings are certified by ATEX, GOST, GOST Ex, cULus, Russian Maritime Register, German Lloyd, as well as the empty housing standard.
- · Alloy is resistant to salt water

 Standardised distributor housings with threaded holes and a variety of terminal configurations

General ordering data

MOPL K21 STAHL		
<u>3073020000</u>		
Mounting plate, Mounting Plate, Sheet steel, galvanised, 114 mm		
4008190857950		
1 pc(s).		



K MOPL K21 STAHL

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16 D-32758 Detmold

Germany Fon: +49 5231 14-0

Fax: +49 5231 14-292083 www.weidmueller.com

Technical data

Dimensions and weights

Dimononono ana tronginto			
Width	114 mm	Mounting dimension - width	106 mm
Net weight	102.5 g		
General information			
Material thickness	2 mm	Material	Sheet steel, galvanised
Impact resistance	10.00 J		
General information on ac	cessories		
Material	Sheet steel, galvanised	Material thickness	2 mm
Mounting dimension - width	106 mm	Type of fixing	Screwed
Classifications			
ETIM 3.0	EC000318	UNSPSC	31-16-23-03
eClass 5.1	27-18-92-07	eClass 6.2	27-18-92-61
eClass 7.1	27-18-92-61		
Approvals			
Approvals			
ROHS	Conform		