

Rees, Inc.

405 S Reed Rd Fremont, IN 46737

Phone: 260.495.9811 Fax: 260.495.2186

Email: sales@reesinc.com
Website: www.reesinc.com

ITEM # 00662-001, 2.25 INCH PLASTIC MUSHROOM PLUNGER

Features/Applications

The following switch is a hand operated, control circuit device, rated 'Heavy Duty' normally for use with electromagnetic equipment. The black cover, painted with a dry powder paint, is made from die-cast zinc. The black mushroom shaped plunger is molded from DuPont Delrin 100ST Acetal for improved impact resistance and improved colors. The plunger head is solid color throughout.

- Ergonomic plunger design
- Improved DC performance
- Gold plated contacts eliminate high resistance tarnishing
- Nema 12/13, IP 65

Each captive terminal will accept (2) #14 AWG stranded wires. Each switch is supplied with all mounting hardware and a solid santoprene rubber gasket which provides an oil tight seal upon installation. The mechanical life of this device is 1,000,000 operations.

This switch can be found on a variety of machines such as punch presses, press brakes, and spot-welding equipment as "RUN", "START" or "STOP" buttons. They are also used on transfer machines. Its rugged construction and long term reliability make this switch extremely well suited to function within various industrial/commercial environments.

Electrical Ratings

"HEAVY DUTY – A600 / N300" Listed under UL 508 – File # E 58589 Certified under CSA C22.2 – File # LR 3648 List Price - \$192.40

CE Compliant IEC/EN 60947-5-1
Third party certified under DEMKO File # FI-17205

Environmental Temperature Range

Operating: $+32^{\circ}F$ to $+131^{\circ}F$ (0°C to $+55^{\circ}C$) Storage: $-40^{\circ}F$ to $+185^{\circ}F$ ($-40^{\circ}C$ to $+85^{\circ}C$)

Note: Operating temperatures at 0°C are based on the

absence of freezing moisture and liquids.

Normal Potential	Normal Current	Inrush Current
110-120 ac ^a volts	6.0 amp.	60.0 amp.
220-240 ac ^a	3.0 amp.	30.0 amp.
440-480 ac ^a	1.5 amp.	15.0 amp.
550-600 ac ^a	1.2 amp.	12.0 amp.
115-125 dc ^b	2.2 amp.	
230-250 dc ^b	1.1 amp.	

a Power factor 0.35 or less

WARNING - DANGER

These products should only be used where point-ofoperation guarding devices have been properly installed & maintained so that appropriate OSHA and ANSI B11.1 regulations & standards are met. Misapplication of the products on machinery lacking effective point-of operation safeguards can cause serious injury to the operator of that machinery.

AVERTISSMENT - DANGER

Ces produit doivent seulement être utilisés sur des postes à risque correctement sécurisés et entretenus afin d'être conforme aux standards et régulations en vigueur (CSA, CLC). Un mauvais usage de ces produits sur des machines et des postes de travail non sécurisés de manière efficace peut causer des blessures graves au technicien maniant ces machines.

b Inductive loads as specified in Section 125 of Industrial Control Devices, Controllers and Assemblies, ANSI / NEMA ICS 2-1988



SPECIFICATIONS	-
Plunger Color	Black
Cover Color	Black
Operating Force	4.3 lb
Positive Opening Contact	Yes ⊕
Contact Arrangement	#09 NO + NC
Contact Type	Slow-Make / Slow-Break
Operating Type	Momentary
Approx. Shipping Weight	1.25 lb
Old Catalog Number	662