



# SPECIFICATION

- Supplier : Samsung electro-mechanics
- Product : Multi-layer Ceramic Capacitor

- Samsung P/N : **CL21A225KPFNNWE**
- Description : **CAP, 2.2 $\mu$ F, 10V,  $\pm$ 10%, X5R, 0805**

## A. Samsung Part Number

**CL 21 A 225 K P F N N W E**  
 ① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨ ⑩ ⑪

① Series	Samsung Multi-layer Ceramic Capacitor		
② Size	0805 (inch code)	L: 2.0 $\pm$ 0.1 mm	W: 1.25 $\pm$ 0.1 mm
③ Dielectric	X5R	⑧ Inner electrode	Ni
④ Capacitance	2.2 $\mu$ F	Termination	Cu
⑤ Capacitance tolerance	$\pm$ 10 %	Plating	Sn 100% (Pb Free)
⑥ Rated Voltage	10 V	⑨ Product	Normal
⑦ Thickness	1.25 $\pm$ 0.1 mm	⑩ Special	Product for Network application
		⑪ Packaging	Embossed Type, 7" reel (2,000ea)

## B. Samsung Reliability Test and Judgement condition

	Performance	Test condition
Capacitance	Within specified tolerance	1kHz $\pm$ 10% 1.0 $\pm$ 0.2Vrms
Tan $\delta$ (DF)	0.05 max.	
Insulation Resistance	More than 100Mohm $\cdot\mu$ F	Rated Voltage 60~120 sec.
Appearance	No abnormal exterior appearance	Visual inspection
Withstanding Voltage	No dielectric breakdown or mechanical breakdown	250% of the rated voltage
Temperature Characteristics	X5R (From -55 $^{\circ}$ C to 85 $^{\circ}$ C, Capacitance change should be within $\pm$ 15%)	
Adhesive Strength of Termination	No peeling shall be occur on the terminal electrode	500g-F, for 10 $\pm$ 1 sec.
Bending Strength	Capacitance change : within $\pm$ 12.5%	Bending to the limit (1mm) with 1.0mm/sec.
Solderability	More than 75% of terminal surface is to be soldered newly	SnAg3.0Cu0.5 solder 245 $\pm$ 5 $^{\circ}$ C, 3 $\pm$ 0.3sec. (preheating : 80~120 $^{\circ}$ C for 10~30sec.)
Resistance to Soldering heat	Capacitance change : within $\pm$ 7.5% Tan $\delta$ , IR : initial spec.	Solder pot : 270 $\pm$ 5 $^{\circ}$ C, 10 $\pm$ 1sec.

	Performance	Test condition
<b>Vibration Test</b>	Capacitance change : within $\pm 5\%$ Tan $\delta$ , IR : initial spec.	Amplitude : 1.5mm From 10Hz to 55Hz (return : 1min.) 2hours $\times$ 3 direction (x, y, z)
<b>Moisture Resistance</b>	Capacitance change : within $\pm 12.5\%$ Tan $\delta$ : 0.075 max IR : More than $25M\Omega \cdot \mu F$	With rated voltage $40 \pm 2^\circ C$ , 90~95%RH, 500+12/-0 hours
<b>High Temperature Resistance</b>	Capacitance change : within $\pm 12.5\%$ Tan $\delta$ : 0.075 max IR : More than $50M\Omega \cdot \mu F$	With 200% of the rated voltage Max. operating temperature  1000+48/-0 hours
<b>Temperature Cycling</b>	Capacitance change : within $\pm 7.5\%$ Tan $\delta$ , IR : initial spec.	1 cycle condition Min. operating temperature $\rightarrow 25^\circ C$ $\rightarrow$ Max. operating temperature $\rightarrow 25^\circ C$  5 cycles test

**C. Recommended Soldering method :**

Reflow ( Reflow Peak Temperature :  $260+0/-5^\circ C$ , 10sec. Max )

\* For the more detail Specification, Please refer to the Samsung MLCC catalogue.