

# SPECIFICATION

- Supplier : Samsung electro-mechanics
- Product : Multi-layer Ceramic Capacitor

- Samsung P/N : **CL21C471JBANNND**
- Description : **CAP, 470pF, 50V, ±5%, COG, 0805**

## A. Samsung Part Number

CL   21   C   471   J   B   A   N   N   N   D  
 ①   ②   ③   ④   ⑤   ⑥   ⑦   ⑧   ⑨   ⑩   ⑪

① Series	Samsung Multi-layer Ceramic Capacitor									
② Size	0805 (inch code)	L: 2.0 ± 0.1 mm	W: 1.25 ± 0.1 mm							
③ Dielectric	COG			⑧ Inner electrode	Ni					
④ Capacitance	470 pF			Termination	Cu					
⑤ Capacitance tolerance	±5 %			Plating	Sn 100% (Pb Free)					
⑥ Rated Voltage	50 V			⑨ Product	Normal					
⑦ Thickness	0.65 ± 0.1 mm			⑩ Special	Reserved for future use					
				⑪ Packaging	Cardboard Type, 13" reel					

## B. Samsung Reliability Test and Judgement condition

	Performance	Test condition
Capacitance	Within specified tolerance	1MHz±10%      0.5~5Vrms
Q	1000 min	
Insulation Resistance	10,000Mohm or 500Mohm·μF Whichever is Smaller	Rated Voltage      60~120 sec.
Appearance	No abnormal exterior appearance	Microscope (×10)
Withstanding Voltage	No dielectric breakdown or mechanical breakdown	300% of the rated voltage
Temperature Characterisitcs	COG (From -55 °C to 125 °C, Capacitance change should be within ±30PPM/°C)	
Adhesive Strength of Termination	No peeling shall be occur on the terminal electrode	500g·F, for 10±1 sec.
Bending Strength	Capacitance change : within ±5% or ±0.5pF whichever is larger	Bending to the limit (1mm) with 1.0mm/sec.
Solderability	More than 75% of terminal surface is to be soldered newly	SnAg3.0Cu0.5 solder 245±5 °C, 3±0.3sec. (preheating : 80~120 °C for 10~30sec.)
Resistance to Soldering heat	Capacitance change : within ±2.5% or ±0.25pF whichever is larger Tan δ, IR : initial spec.	Solder pot : 270±5 °C, 10±1sec.

	Performance	Test condition
<b>Vibration Test</b>	Capacitance change : within $\pm 2.5\%$ or $\pm 0.25\text{pF}$ whichever is larger Tan $\delta$ , IR : initial spec.	Amplitude : 1.5mm From 10Hz to 55Hz (return : 1min.) 2hours $\times$ 3 direction (x, y, z)
<b>Moisture Resistance</b>	Capacitance change : within $\pm 7.5\%$ or $\pm 0.75\text{pF}$ whichever is larger Q : 200 min IR : 500Mohm or 25Mohm $\cdot \mu\text{F}$ Whichever is Smaller	With rated voltage 40 $\pm$ 2 $^{\circ}\text{C}$ , 90~95%RH, 500+12/-0hrs
<b>High Temperature Resistance</b>	Capacitance change : within $\pm 3\%$ or $\pm 0.3\text{pF}$ whichever is larger Q : 350 min IR : 1000Mohm or 50Mohm $\cdot \mu\text{F}$ Whichever is Smaller	With 200% of the rated voltage Max. operating temperature 1000+48/-0hrs
<b>Temperature Cycling</b>	Capacitance change : within $\pm 2.5\%$ or $\pm 0.25\text{pF}$ whichever is larger Tan $\delta$ , IR : initial spec.	1 cycle condition Min. operating temperature $\rightarrow$ 25 $^{\circ}\text{C}$ $\rightarrow$ Max. operating temperature $\rightarrow$ 25 $^{\circ}\text{C}$  5 cycle test

**C. Recommended Soldering method :**

Reflow ( Reflow Peak Temperature : 260+0/-5 $^{\circ}\text{C}$ , 10sec. Max )

\* For the more detail Specification, Please refer to the Samsung MLCC catalogue.