

SPECIFICATION

- Supplier : Samsung electro-mechanics
- Product : Multi-layer Ceramic Capacitor

- Samsung P/N : **CL31B106KPHN3NE**
- Description : **CAP, 10 μ F, 10V, \pm 10%, X7R, 1206**

A. Samsung Part Number

CL
31
B
106
K
P
H
N
3
N
E

①
②
③
④
⑤
⑥
⑦
⑧
⑨
⑩
⑪

① Series	Samsung Multi-layer Ceramic Capacitor		
② Size	1206 (inch code)	L: 3.2 \pm 0.2 mm	W: 1.6 \pm 0.2 mm
③ Dielectric	X7R	⑧ Inner electrode Termination	Ni Cu
④ Capacitance	10 μ F	Plating	Sn 100% (Pb Free)
⑤ Capacitance tolerance	\pm 10 %	⑨ Product	DC-Bias Improved product
⑥ Rated Voltage	10 V	⑩ Special	Reserved for future use
⑦ Thickness	1.6 \pm 0.2 mm	⑪ Packaging	Embossed Type, 7" reel(2,000ea)

B. Samsung Reliability Test and Judgement condition

	Performance	Test condition
Capacitance	Within specified tolerance	1kHz \pm 10% 1.0 \pm 0.2Vrms
Tan δ (DF)	0.1 max.	
Insulation Resistance	More than 100Mohm $\cdot\mu$ F	Rated Voltage 60~120 sec.
Appearance	No abnormal exterior appearance	Visual inspection
Withstanding Voltage	No dielectric breakdown or mechanical breakdown	250% of the rated voltage
Temperature Characteristics	X7R (From -55 $^{\circ}$ C to 125 $^{\circ}$ C, Capacitance change should be within \pm 15%)	
Adhesive Strength of Termination	No peeling shall be occur on the terminal electrode	500g \cdot F, for 10 \pm 1 sec.
Bending Strength	Capacitance change : within \pm 12.5%	Bending to the limit (1mm) with 1.0mm/sec.
Solderability	More than 75% of terminal surface is to be soldered newly	SnAg3.0Cu0.5 solder 245 \pm 5 $^{\circ}$ C, 3 \pm 0.3sec. (preheating : 80~120 $^{\circ}$ C for 10~30sec.)
Resistance to Soldering heat	Capacitance change : within \pm 7.5% Tan δ , IR : initial spec.	Solder pot : 270 \pm 5 $^{\circ}$ C, 10 \pm 1sec.

	Performance	Test condition
Vibration Test	Capacitance change : within $\pm 5\%$ Tan δ , IR : initial spec.	Amplitude : 1.5mm From 10Hz to 55Hz (return : 1min.) 2hours \times 3 direction (x, y, z)
Moisture Resistance	Capacitance change : within $\pm 12.5\%$ Tan δ : 0.125 max IR : More than 12.5M $\Omega \cdot \mu F$	With rated voltage 40 ± 2 °C, 90~95%RH, 500 +12/-0 hour
High Temperature Resistance	Capacitance change : within $\pm 12.5\%$ Tan δ : 0.125 max IR : More than 25M $\Omega \cdot \mu F$	With 150% of the rated voltage Max. operating temperature 1000+48/-0 hour
Temperature Cycling	Capacitance change : within $\pm 7.5\%$ Tan δ , IR : initial spec.	1 cycle condition Min. operating temperature \rightarrow 25°C \rightarrow Max. operating temperature \rightarrow 25°C 5 cycles test

C. Recommended Soldering method :

Reflow (Reflow Peak Temperature : 260+0/-5°C, 10sec. Max)

* For the more detail Specification, Please refer to the Samsung MLCC catalogue.