μClamp5011ZA Ultra Small μClamp® 1-Line, 5V ESD Protection

PROTECTION PRODUCTS - μClamp®

Description

μClamp® TVS diodes are designed to protect sensitive electronics from damage or latch-up due to ESD. They are designed to replace 0201 size multilayer varistors (MLVs) in portable applications such as cell phones, notebook computers, and other portable electronics. It features large cross-sectional area junctions for conducting high transient currents. This device offers desirable characteristics for board level protection including fast response time, low operating and clamping voltage, and no device degradation.

 μ Clamp®5011ZA features extremely good ESD protection characteristics highlighted by low typical dynamic resistance of 0.15 Ohms, low peak ESD clamping voltage, and high ESD withstand voltage (+/-15kV contact per IEC 61000-4-2). Low maximum capacitance (5pF at VR=0V) minimizes loading on sensitive cirucuits. Each device will protect one data or power line operating at 5 Volts.

 μ Clamp5011ZA is in a 2-pin SLP0603P2X3F package. It measures 0.6 x 0.3 mm with a nominal height of only 0.25mm. Leads are finished with NiAu. The small package gives the designer the flexibility to protect single lines in applications where arrays are not practical. The combination of small size and high ESD surge capability makes them ideal for use in portable applications such as cellular phones, digital cameras, and tablet PC's.

Features

- ◆ High ESD withstand Voltage: +/-15kV (Contact) and +/- 18kV (Air) per IEC 61000-4-2
- Ultra-small package
- Protects one data line
- Low ESD clamping voltage
- Working voltage: 5V
- Low capacitance: 5pF maximum
- ◆ Low leakage current
- Extremely low dynamic resistance: 0.15 Ohms (Typ)
- Solid-state silicon-avalanche technology


Mechanical Characteristics

- ◆ SLP0603P2X3F package
- ◆ Pb-Free, Halogen Free, RoHS/WEEE Compliant
- ◆ Nominal Dimensions: 0.6 x 0.3 x 0.25 mm
- Lead Finish: NiAu
- Marking: Marking code
- Packaging: Tape and Reel


Applications

- Cellular Handsets & Accessories
- Notebook Computers
- ◆ Tablet PC
- Portable Instrumentation
- Peripherals

Package Dimensions



Schematic & Pin Configuration





Absolute Maximum Ratings

Rating	Symbol	Value	Units
Peak Pulse Power (tp = 8/20µs)	P _{PK}	30	W
Peak Pulse Current (tp = 8/20µs)	I _{PP}	2.5	А
ESD per IEC 61000-4-2 (Air) ⁽¹⁾ ESD per IEC 61000-4-2 (Contact) ⁽¹⁾	V _{ESD}	±18 ±15	kV
Operating Temperature	T _J	-40 to +125	°C
Storage Temperature	T _{STG}	-55 to +150	°C

Electrical Characteristics (T=25°C unless otherwise specified)

Parameter	Symbol	Conditions		Min.	Тур.	Max.	Units
Reverse Stand-Off Voltage	$V_{_{\mathrm{RWM}}}$	Pin 1 to 2 or Pin 2 to 1				5	V
Reverse breakdown Voltage	$V_{_{BR}}$	I _{BR} = 1mA Pin 1 to 2 or Pin 2 to 1		6.5	8.5	10.5	V
Reverse Leakage Current	I _R	V _{RWM} = 5V Pin 1 to 2 or Pin 2 to 1			5	20	nA
Clamping Voltage	V _c	$I_{pp} = 2.5A, tp = 8/20\mu s$				12	V
ESD Clamping Voltage ²	V _c	I _{PP} = 4A tp = 0.2/100ns			8		V
ESD Clamping Voltage ²	V _c	I _{PP} = 16A tp = 0.2/100ns			9.8		V
Dynamic Resistance ^{2, 3}	R _{DYN}	tp = 100ns			0.15		Ohms
Junction Capacitance	C _J	I/O pin to GND f = 1MHz	V _R = 0V		4.2	5	pF

Notes

¹⁾Measured with a 20dB attenuator, 50 0hm scope input impedance, 2GHz bandwidth. ESD gun return path connected to ESD ground plane.


²⁾ Transmission Line Pulse Test (TLP) Settings: tp = 100ns, tr = 0.2ns, I_{TLP} and V_{TLP} averaging window: t1 = 70ns to t2 = 90ns.

³⁾ Dynamic resistance calculated from $I_{TLP} = 4A$ to $I_{TLP} = 16A$




Typical Characteristics


ESD Clamping (8kV Contact per IEC 61000-4-2)




ESD Clamping (-8kV Contact per IEC 61000-4-2)




TLP Characteristic (Positive Pulse)




TLP Characteristic (Negative Pulse)



Clamping Voltage vs. Peak Pulse Current (tp=8/20us)



Junction Capacitance vs. Reverse Voltage






Applications Information

Assembly Guidelines

The small size of this device means that some care must be taken during the mounting process to insure reliable solder joint. The table below provides Semtech's recommended assembly guidelines for mounting this device. The figure at the right details Semtech's recommended aperture based on the below recommendations. Note that these are only recommendations and should serve only as a starting point for design since there are many factors that affect the assembly process. The exact manufacturing parameters will require some experimentation to get the desired solder application.


Assembly Parameter	Recommendation	
Solder Stencil Design	Laser cut, Electro-polished	
Aperture shape	Rectangular with rounded corners	
Solder Stencil Thickness	0.100 mm (0.004")	
Solder Paste Type	Type 4 size sphere or smaller	
Solder Reflow Profile	Per JEDEC J-STD-020	
PCB Solder Pad Design	Non-Solder mask defined	
PCB Pad Finish	OSP OR NiAu	



Recommended Mounting Pattern



Outline Drawing - SLP0603P2X3F




DIMENSIONS					
DIM	MILI	_IMETE	IETERS		
וווטן	MIN	NOM	MAX		
Α	0.235	0.250	0.265		
A1	0.000	0.010	0.050		
b	0.200	0.220	0.240		
О	0.580	0.600	0.620		
Е	0.280	0.300	0.320		
е	0.355 BSC				
L	0.140	0.160	0.180		
Ν	2				
aaa	0.08				
bbb	0.10				

BOTTOM VIEW

NOTES:

1. CONTROLLING DIMENSIONS ARE IN MILLIMETERS (ANGLES IN DEGREES).

Land Pattern - SLP0603P2X3F




DIMENSIONS			
DIM MILLIMETERS			
G	0.177		
Χ	0.272		
Υ	0.247		
Z	0.671		

NOTES:

CONTROLLING DIMENSIONS ARE IN MILLIMETERS (ANGLES IN DEGREES). THIS LAND PATTERN IS FOR REFERENCE PURPOSES ONLY.
CONSULT YOUR MANUFACTURING GROUP TO ENSURE YOUR
COMPANY'S MANUFACTURING GUIDELINES ARE MET.



Marking



Notes: Device is Electrically Symmetrical


Ordering Information

Part Number	Qty per Reel	Reel Size
μClamp5011ZATFT	15000	7"

Notes:

1) MicroClamp, uClamp and μ Clamp are trademarks of Semtech Corporation.

Tape and Reel Specification



Contact Information

Semtech Corporation Protection Products Division 200 Flynn Rd., Camarillo, CA 93012 Phone: (805)498-2111 FAX (805)498-3804

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Semtech:

UCLAMP5011ZATFT UCLAMP5013V.TFT