

X-putty

Thermal Conductive Putty

LiPOLY X-putty is a one-part dispensable material with thermal conductivity 3.0W/m*K. High deformation can fill small air gaps perfectly to remove tolerance. It also can overcome overflow and drying problems to increase the thermal conductivity. X-putty is a great alternative to thermal grease and ideally suited for dispensing using the dispensing robot.

■ FEATURES

- / Thermal conductivity:3.0 W/m*K
- / Bond line thickness:100-3000μm
- / Designed to remove manufacturing tolerances
- / Does not produce stress on delicate components
- / No vertical flow
- / Dispensable for serial manufacture
- / For any high compression and low stress application

■ TYPICAL APPLICATION

- / Between CPU and heat sink
- / Between a component and heat sink
- / High speed mass storage drives
- / Telecommunication hardware
- / Flat-panel displays
- / Set-top box
- / IP CAM

■ CONFIGURATIONS

- / Cartridges: 30ml, 55ml, 330ml
- / Bucket: 1kg, 25kg

■ PRESERVATION



It can be preserved for 60 months under the condition of unopened and under room temperature 25°C

■ TYPICAL PROPERTIES

PROPERTY	X-putty	TEST METHOD	UNIT
Color	Gray	Visual	-
Resin base	Silicone	-	-
Viscosity	17000	DIN 53018	Pa.s
Density	2.8	ASTM D792	g/cm ³
Application temperature	-60~180	-	°C
Bond line thickness	100~3000	-	μm
Shelf life	60 months	-	-
ROHS & REACH	Compliant	-	-
ELECTRICAL			
Dielectric breakdown	12	ASTM D149	KV/mm
Volume resistivity	>10 ¹³	ASTM D257	Ohm-m
THERMAL			
Thermal conductivity	3.0	ASTM D5470	W/m*K
Thermal impedance@10psi	0.110	ASTM D5470	°C-in ² / W
Thermal impedance@30psi	0.080	ASTM D5470	°C-in ² / W
Thermal impedance@50psi	0.075	ASTM D5470	°C-in ² / W

■ VERTICAL RELIABILITY

Using 3.0mm pad as a gap control, put the putty between the aluminum and the glass panel mark the initial position. Then, place it in the oven with 125°C for 1,000 hours and observe its displacement after reliability test.



Material no dropped or changed after high temperature aging testing

Note: All specifications provided by LiPOLY are subject to change without notice. The test methods used by LiPOLY are based on the TIM Tester method and ASTM D5470 test method. These test methods are used as the definition standards for LiPOLY. Property values provided in this document are not for product specifications or guaranteed. This document does not guarantee the performance and quality required for the purchaser's specific purpose. The purchaser needs to evaluate and verify the safety before using the material. We strongly recommend the purchaser pre-test the product and verify the performance of the product under the purchaser's specific conditions. Liability and use of the product are the responsibility of the end user. LiPOLY makes no warranty as to the suitability, merchantability, or non-infringement of any LiPOLY material or product for any specific or general uses. LiPOLY shall not be liable for incidental or consequential damages of any kind. All LiPOLY products are sold in accordance with the LiPOLY Terms and Conditions in effect at the time of purchase and a copy of which will be furnished upon request. All rights reserved, including LiPOLY trademarks or registered trademarks of LiPOLY or its affiliates. Statements concerning possible or suggested uses made herein shall not be relied upon or be construed as a guaranty of patent infringement. Copyright 2022 LiPOLY.