

Table of Contents

Technical Information	4
How to Order	5
RJ45 Plug Molded Cable - Composite and Metal	
RJ45 Molded Straight Plug to RJ45 Plug Cable Assembly	6
RJ45 Molded Straight Plug Single Ended Cable Assembly	7
RJ45 Molded Straight Plug to Molded Straight Plug Cable Assembly	8
RJ45 Plug Field Wireable	
RJ45 Field Wireable Plug	9
RJ45 Receptacle Molded Cable	
RJ45 Molded Straight Jamnut Receptacle to RJ45 Plug Cable Assembly	10
RJ45 Molded Straight Jamnut Receptacle Single Ended Cable Assembly	10
RJ45 Molded Straight Jamnut Receptacle to Molded Straight Plug Cable Assembly	11
RJ45 Receptacles	
RJ45 Jamnut Receptacle to PCB	12
RJ45 Jamnut Receptacle to Female Feed Thru	13
RJ45 Jamnut Receptacle to RJ45 Plug	14
RJ45 Jamnut Receptacle to Blunt Cut	15
Accessories	
RJ45 Feedthru Adapter	16
RJ45 Receptacle Cap	17
RJ45 Receptacle Metal Cap	17
RJ45 Gasket	18
RJ45 Locknut	18
Assembly Instructions	
RJ45 Field Wireable Plug Assembly Instructions	19
Part Numbers	20





Technical Information

Wire Gauge Conversion Chart

Conversion between American Wire Gauge (AWG), Circular Mil Area (CMA), and approximate metric millimeter squared (mm2) wire sizes.

Diameter		Area		
AWG	in.	mm	CMA	mm²*
4/0 (0000)	0.46	11.68	212000	120
3/0 (000)	0.41	10.41	168000	95
2/0 (00)	0.365	9.27	133000	70
1/0 (0)	0.325	8.26	106000	50
1	0.289	7.34	83700	-
2	0.258	6.55	66400	35
3	0.229	5.82	52600	-
4	0.204	5.18	41700	25
5	0.182	4.62	33100	-
6	0.162	4.11	26300	16
7	0.144	3.66	20800	-
8	0.128	3.25	16500	10
9	0.114	2.90	13100	-
10	0.102	2.59	10400	6
11	0.091	2.31	8230	-
12	0.081	2.06	6530	4
13	0.072	1.83	5180	-

Diameter		Ar	rea	
AWG	in.	mm	CMA	mm²*
14	0.062	1.57	4110	2.5
15	0.057	1.45	3260	-
16	0.051	1.30	2580	1.5
17	0.045	1.14	2050	1
18	0.040	1.02	1620	0.75
19	0.036	0.91	1290	-
20	0.032	0.81	1020	0.5
21	0.0285	0.72	810	-
22	0.0253	0.643	642	0.34
23	0.0226	0.574	509	-
24	0.0201	0.511	404	0.25
25	0.0179	0.45	320	-
26	0.0159	0.404	254	0.14
27	0.0142	0.361	202	-
28	0.0126	0.320	160	0.08
29	0.0113	0.29	127	-
30	0.01	0.254	101	0.05

Use to Convert American Wire Gauge to Diameter and Circular Mil Area.

^{*}Nearest metric wire size





How to Order

RJ45 Plugs & Cable Assemblies

1		2	3		4
IPMOD	-	45	WPP	-	1M
SERIES		TYPE	CONNECTOR STYLE		LENGTH

SERIES

IPMOD = RJ45 COMPOSITE IPMODM = RJ45 METAL

TYPE

45 = RJ45 (Cat5e)

CONNECTOR STYLE*

WPP = RJ45 molded plug to RJ45 plug WPL = RJ45 molded plug to blunt cut

WPWP = RJ45 molded plug to RJ45 molded plug

WM-FT = RJ45 field installable plug

WJP = RJ45 molded receptacle to RJ45 plug WJL = RJ45 molded receptacle to blunt cut

WJWP = RJ45 molded receptacle to RJ45 molded plug

LENGTH**

05M = 0.5 meter 1M = 1 meter 5M = 5 meters 10 M = 10 meters

RJ45 Receptacle

1		2	3	4
IPMOD	-	-45	FSP	-0.5M
SERIES		TYPE	CONNECTOR STYLE	LENGTH

SERIES

IPMOD = RJ45 Composite IPMODM = RJ45 Metal

TYPE

-45 = RJ45 (Cat5e)

CONNECTOR STYLE

FSP = RJ45 jam nut receptacle to printed circuit board FSBHD = RJ45 jam nut receptacle to female RJ45 feed thru

FSLP = RJ45 jam nut receptacle to RJ45 plug FSL = RJ45 jam nut receptacle to blunt cut

LENGTH*

05M = 0.5 meter1M = 1 meter

*Length only required on "FSLP" and "FSL" options, otherwise leave blank.

^{*}Molded receptacle only available in composite.

^{**} Additional lengths are available upon request





RJ45 Molded Straight Plug to RJ45 Plug Cable Assembly


Composite

Connector series: RJ45

Gender: Plug

Performance: Cat 5e Mounting type: Straight Part No.: IPMOD-45WPP-XM

X refers to cable length





General Information

Standard:	IEC 60603-7
Temperature range:	-20°C ~ +80°C
Terminal:	Copper alloy, gold plated
Contact number:	8 contacts
Contact housing:	Nylon + CF
Screw nut:	Nylon + GF
Mating style:	Screw thread

Contact resistance:	$\leq 40M\Omega$
Withstanding voltage:	AC 1000V/1 minute
Salt spray:	48 hr.
Protection class:	IP67 (mated)
Durability:	1000 times
Current rating:	1A
Voltage rating:	48V
Wiring schematic:	T568-B

Metal


Connector series: RJ45

Gender: Plug

Performance: Cat 5e Mounting type: Straight

Part No.: IPMODM-45WPP-XM

X refers to cable length





General Information

Standard:	IEC 60603-7
Temperature range:	-20°C ~ +80°C
Terminal:	Copper alloy, gold plated
Contact number:	8 contacts
Contact housing:	Nylon + GF
Screw nut:	Zinc, nickel plated
Mating style:	Screw thread

Contact resistance:	$\leq 40M\Omega$
Withstanding voltage:	AC 1000V/1 minute
Salt spray:	48 hr.
Protection class:	IP67 (mated)
Durability:	1000 times
Current rating:	1A
Voltage rating:	48V
Wiring Schematic:	T568-B

[•] Please refer to Page 5 for part number breakdown.





RJ45 Molded Straight Plug Single Ended Cable Assembly


Composite

Connector series: RJ45

Gender: Plug

Performance: Cat 5e Mounting type: Straight Part No.: IPMOD-45WPL-XM

X refers to cable length





General Information

Standard:	IEC 60603-7
Temperature range:	-20°C ~ +80°C
Terminal:	Copper alloy, gold plated
Contact number:	8 Contacts
Contact housing:	Nylon + CF
Screw nut:	Nylon + GF
Mating style:	Screw thread

Contact resistance:	$\leq 40M\Omega$
Withstanding voltage:	AC 1000V/1 minute
Salt spray:	48 hr.
Protection class:	IP67 (mated)
Durability:	1000 times
Current rating:	1A
Voltage rating:	48V
Wiring Schematic:	T568-B

Metal


Connector series: RJ45

Gender: Plug

Performance: Cat 5e Mounting type: Straight

Part No.: IPMODM-45WPL-XM

X refers to cable length





General Information

Standard:	IEC 60603-7
Temperature range:	-20°C - +80°C
Terminal:	Copper alloy, gold plated
Contact number:	8 contacts
Contact housing:	Nylon + GF
Screw nut:	Zinc, nickel plated
Mating style:	Screw thread

Contact resistance:	$\leq 40M\Omega$	
Withstanding voltage:	AC 1000V/1 minute	
Salt spray:	48 hr.	
Protection class:	IP67 (mated)	
Durability:	1000 times	
Current rating:	1A	
Voltage rating:	48V	
Wiring Schematic:	T568-B	

[•] Please refer to Page 5 for part number breakdown.





RJ45 Molded Straight Plug to Molded Straight Plug Cable Assembly

Composite


Connector series: RJ45

Gender: Plug

Performance: Cat 5e Mounting type: Straight

Part No.: IPMOD-45WPWP-XM

X refers to cable length





General Information

Standard:	IEC 60603-7
Temperature range:	-20°C ~ +80°C
Terminal:	Copper alloy, gold plated
Contact number:	8 contacts
Contact housing:	Nylon+CF
Screw nut:	Nylon + GF
Mating style:	Screw Thread

Contact resistance:	$\leq 40M\Omega$
Withstanding voltage:	AC 1000V/1 minute
Salt spray:	48 hr.
Protection class:	IP67 (mated)
Durability:	1000 times
Current rating:	1A
Voltage rating:	48V

Metal


Connector series: RJ45

Gender: Plug

Performance: Cat 5e Mounting type: Straight

Part No.: IPMODM-45WPWP-XM

X refers to cable length





General Information

Standard:	IEC 60603-7
Temperature range:	-20°C ~ +80°C
Terminal:	Copper alloy, gold plated
Contact number:	8 contacts
Contact housing:	Nylon+GF
Screw nut:	Zinc, Nickel Plated
Mating style:	Screw Thread

Contact resistance:	$\leq 40M\Omega$
Withstanding voltage:	AC 1000V/1 minute
Salt spray:	48 hr.
Protection class:	IP67 (mated)
Durability:	1000 times
Current rating:	1A
Voltage rating:	48V

[•] Please refer to Page 5 for part number breakdown.





RJ45 Field Wireable Plug


Composite

Connector series: RJ45

Gender: Plug

Performance: Cat 5e Mounting type: Straight Part No.: IPMOD-45WM-FT







General Information

Standard:	IEC 60603-7
Temperature range:	-40°C ~ +85°C
Terminal:	Copper alloy, gold plated
Contact number:	8 contacts
Contact housing:	Nylon + GF
Screw nut:	Nylon + GF
Mating style:	Screw Thread

Contact resistance:	$\leq 40M\Omega$
Withstanding voltage:	AC 1000V/1 minute
Salt spray:	48 hr.
Protection class:	IP67 (mated)
Durability:	1000 times
Current rating:	1A
Voltage rating:	48V


Metal

Connector series: RJ45

Gender: Plug

Performance: Cat 5e Mounting type: Straight Part No.: IPMODM-45WM-FT







General Information

Standard:	IEC 60603-7
Temperature range:	-40°C ~ +85°C
Terminal:	Copper alloy, gold plated
Contact number:	8 contacts
Contact housing:	Nylon + GF
Screw nut:	Zinc, nickel plated
Mating style:	Screw thread

Contact resistance:	$\leq 40M\Omega$
Withstanding voltage:	AC 1000V/1 minute
Salt spray:	48 hr.
Protection class:	IP67 (mated)
Durability:	1000 times
Current rating:	1A
Voltage rating:	48V

- Please refer to Page 5 for part number breakdown.
- Please refer to Page 20 for assembly instructions.





RJ45 Molded Straight Jamnut Receptacle To RJ45 Plug Cable Assembly


Composite

Connector series: RJ45

Gender: Jack

Locking type: Fix screw Part No.: IPMOD-45WJP-XM

X refers to cable length





General Information

Standard:	IEC 60603-7
Temperature range:	-20°C ~ +80°C
Terminal:	Copper alloy, gold plated
Contact number:	8 contacts
Contact housing:	Nylon+CF
Screw nut:	Nylon + GF
Mating style:	Screw Thread

Contact resistance:	$\leq 40M\Omega$
Withstanding voltage:	AC 1000V/1 minute
Salt spray:	48 hr.
Protection class:	IP67 (mated)
Durability:	1000 times
Current rating:	1A
Voltage rating:	48V

RJ45 Molded Straight Jamnut Receptacle Single Ended Cable Assembly


Composite

Connector series: RJ45

Gender: Jack

Locking type: Fix screw Part No.: IPMOD-45WJL-XM

X refers to cable length





General Information

Standard:	IEC 60603-7
Temperature range:	-20°C ~ +80°C
Terminal:	Copper alloy, gold plated
Contact number:	8 contacts
Contact housing:	Nylon+CF
Screw nut:	Nylon + GF
Mating style:	Screw Thread

Contact resistance:	$\leq 40M\Omega$
Withstanding voltage:	AC 1000V/1 minute
Salt spray:	48 hr.
Protection class:	IP67 (mated)
Durability:	1000 times
Current rating:	1A
Voltage rating:	48V

Notes

• Please refer to Page 5 for part number breakdown.





RJ45 Molded Straight Jamnut Receptacle To RJ45 Plug Cable Assembly

Composite


Connector series: RJ45

Gender: Jack

Locking type: Fix screw

Part No.: IPMOD-45WJWP-XM

X refers to cable length





General Information

Standard:	IEC 60603-7
Temperature range:	-20°C ~ +80°C
Terminal:	Copper alloy, gold plated
Contact number:	8 contacts
Contact housing:	Nylon+CF
Screw nut:	Nylon + GF
Mating style:	Screw Thread

Contact resistance:	$\leq 40M\Omega$
Withstanding voltage:	AC 1000V/1 minute
Salt spray:	48 hr.
Protection class:	IP67 (mated)
Durability:	1000 times
Current rating:	1A
Voltage rating:	48V






RJ45 Jamnut Receptacle To PCB

Composite

Connector series: RJ45 Gender: Receptacle

Performance: Cat 5e & Cat 6a

Mounting type: Straight Part No.: IPMOD-45FSP





General Information

Standard:	IEC 60603-7
Temperature Range:	-40°C ~ +105°C
Terminal:	Copper alloy, gold plated
Contact Number:	8 contacts
Contact Housing:	Nylon+CF
Screw Nut:	Nylon + GF
Mating Style:	Screw Thread


Contact resistance:	$\leq 40M\Omega$
Withstanding Voltage:	AC 1000V/1 minute
Salt Spray:	48 hr.
Protection Class:	IP68 (mated)
Durability:	1000 times
Current Rating:	1A
Voltage Rating:	48V

Metal

Connector series: RJ45 Gender: Receptacle

Performance: Cat 5e & Cat 6a Mounting type: Straight

Part No.: IPMODM-45FSP





General Information

Standard:	IEC 60603-7
Temperature Range:	-40°C ~ +105°C
Terminal:	Copper alloy, gold plated
Contact Number:	8 contacts
Contact Housing:	Nylon+GF
Screw Nut:	Zinc, Nickel Plated
Mating Style:	Screw Thread

Contact Resistance:	$\leq 40M\Omega$
Withstanding Voltage:	AC 1000V/1 minute
Salt Spray:	48 hr.
Protection Class:	IP68 (mated)
Durability:	1000 times
Current Rating:	1A
Voltage Rating:	48V

Notes

• Please refer to Page 5 for part number breakdown.





RJ45 Jamnut Receptacle To Female Feed Thru


Composite

Connector series: RJ45

Gender: Plug

Performance: Cat 5e & Cat 6a

Mounting type: Straight Part No.: IPMOD-45FSBHD





General Information

Standard:	IEC 60603-7
Temperature range:	-40°C ~ +105°C
Terminal:	Copper alloy, gold plated
Contact number:	8 contacts
Contact housing:	Nylon+CF
Screw nut:	Zinc alloy, nickel plated
Mating style:	Screw Thread
Max panel thickness	4.0 mm (without cap chain)

Contact resistance:	$\leq 40M\Omega$
Withstanding voltage:	AC 1000V/1 minute
Salt spray:	48 hr.
Protection class:	IP68 (mated)
Durability:	1000 times
Current rating:	1A
Voltage rating:	48V
Insulation resistance	≥ 5000MΩ at DC 100v


Metal

Connector series: RJ45

Gender: Plug

Performance: Cat 5e & Cat 6a

Mounting type: Straight Part No.: IPMODM-45FSBHD





General Information

Standard:	IEC 60603-7
Temperature range:	-40°C ~ +105°C
Terminal:	Copper alloy, gold plated
Contact number:	8 contacts
Contact housing:	Nylon+CF
Screw nut:	Zinc alloy, nickel plated
Mating style:	Screw Thread
Max panel thickness	4.0 mm (without cap chain)

Contact resistance:	$\leq 40M\Omega$
Withstanding voltage:	AC 1000V/1 minute
Salt spray:	48 hr.
Protection class:	IP68 (mated)
Durability:	1000 times
Current rating:	1A
Voltage rating:	48V
Insulation resistance	≥ 5000MΩ at DC 100v

Notes

• Please refer to Page 5 for part number breakdown.






RJ45 Jamnut Receptacle To RJ45 Plug

Composite

Connector series: RJ45 Gender: Receptacle Performance: Cat 5e Mounting type: Straight Part No.: IPMOD-45FSLP-XM

X refers to cable length





General Information

Standard:	IEC 60603-7
Temperature Range:	-20°C ~ +80°C
Terminal:	Copper alloy, gold plated
Contact Number:	8 contacts
Contact Housing:	Nylon+CF
Screw Nut:	Nylon + GF
Mating Style:	Screw Thread
*Cable Length:	500 mm


Contact resistance:	$\leq 40M\Omega$
Withstanding Voltage:	AC 1000V/1 minute
Salt Spray:	48 hr.
Protection Class:	IP68 (mated)
Durability:	1000 times
Current Rating:	1A
Voltage Rating:	48V

Metal

Connector series: RJ45 Gender: Receptacle Performance: Cat 5e Mounting type: Straight

Part No.: IPMODM-45FSLP-XM

X refers to cable length





General Information

Standard:	IEC 60603-7
Temperature Range:	-40°C ~ +85°C
Terminal:	Copper alloy, gold plated
Contact Number:	8 contacts
Contact Housing:	Nylon+GF
Screw Nut:	Zinc alloy, nickel plated
Mating Style:	Screw Thread
*Cable Length:	500 mm

Contact resistance:	$\leq 40M\Omega$
Withstanding Voltage:	AC 1000V/1 minute
Salt Spray:	48 hr.
Protection Class:	IP68 (mated)
Durability:	1000 times
Current Rating:	1A
Voltage Rating:	48V

- Please refer to Page 5 for part number breakdown.
- * If no cable length is defined, the standard is 500 mm.






RJ45 Jamnut Receptacle To Blunt Cut

Composite

Connector series: RJ45 Gender: Receptacle Performance: Cat 5e Mounting type: Straight Part No.: IPMOD-45FSL-XM







General Information


Standard:	IEC 60603-7	
Temperature Range:	-20°C ~ +80°C	
Terminal:	Copper alloy, gold plated	
Contact Number:	8 contacts	
Contact Housing:	Nylon+CF	
Screw Nut:	Nylon + GF	
Mating Style:	Screw Thread	
*Cable Length:	500 mm	

Contact resistance:	$\leq 40M\Omega$
Withstanding Voltage:	AC 1000V/1 minute
Salt Spray:	48 hr.
Protection Class:	IP68 (mated)
Durability:	1000 times
Current Rating:	1A
Voltage Rating:	48V

Metal

Connector series: RJ45
Gender: Receptacle
Performance: Cat 5e
Mounting type: Straight
Part No.: IPMODM-45FSL-XM

X refers to cable length





General Information

Standard:	IEC 60603-7
Temperature Range:	-20°C ~ +85°C
Terminal:	Copper alloy, gold plated
Contact Number:	8 contacts
Contact Housing:	Nylon+GF
Screw Nut:	Zinc alloy, nickel plated
Mating Style:	Screw Thread
*Cable Length:	500 mm

Contact resistance:	$\leq 40M\Omega$
Withstanding Voltage:	AC 1000V/1 minute
Salt Spray:	48 hr.
Protection Class:	IP68 (mated)
Durability:	1000 times
Current Rating:	1A
Voltage Rating:	48V

- Please refer to Page 5 for part number breakdown.
- * If no cable length is defined, the standard is 500 mm.






RJ45 Feedthru Adapter

Connector series: RJ45

Gender: Adapter

Locking type: Fix screw

Part No.: IPMOD-45FSWBHD





General Information

Standard:	IEC 60603-7
Temperature range:	-20°C ~ +80°C
Terminal:	Copper alloy, gold plated
Contact number:	8 contacts
Contact housing:	Nylon+GF
Screw nut:	Nylon + GF
Mating style:	Screw Thread


Contact resistance:	$\leq 40M\Omega$
Withstanding voltage:	AC 1000V/1 minute
Salt spray:	48 hr.
Protection class:	IP67 (mated)
Durability:	1000 times
Current rating:	1A
Voltage rating:	48V





RJ45 Receptacle Cap

Connector series: RJ45 Part No.: IPCAP-1316





General Information

Temperature range: -40°C ~ +105°C

Material, cap: Nylon, black

Material, holder: Nylon, black


Protection class: IP67

Material, gasket: EPDM, black

Material, chain: Stainless steel

RJ45 Receptacle Metal Cap

Connector series: RJ45 Part No.: IPCAPM-1316





General Information

Temperature range: -40°C ~ +105°C Protection class: IP67

Material, cap: Copper alloy, nickel plated Material, gasket: EPDM, black


Material, holder: Nylon, black Material, chain: Stainless steel






RJ45 Gasket

Connector series: RJ45 Part No.: IPGSK-1316








General Information


Material: Silicone (UL94V-0) Color: Gray

Packaging: Pack of 10

RJ45 Lock Nut

Connector series: RJ45 Part No.: IPNT-1316







General Information


Material: Nylon Color: Black

Packaging: Pack of 10





RJ45 Field Wireable Assembly Instructions



Step 1

Strip the cable sheath and insulation.



Step 2

Insert the cable through the sealing nut, clip, seal, screw nut and housing.



Step 3

Insert cable into plug using hand tool.



Step 4

Insert the screw nut.



Step 5

Connect the seal and the clip respectively.



Step 6

Connect the sealing nut and tighten using hand tool (optional) or your hand while holding assy.



Step 7

Insert the gasket.







Part Numbers

All RJ45 Series P/Ns	Catalog Page
IPMOD-45WPP-1M	6
IPMOD-45WPP-3M	6
IPMOD-45WPP-5M	6
IPMODM-45WPP-1M	6
IPMODM-45WPP-3M	6
IPMODM-45WPP-5M	6
IPMOD-45WPL-1M	7
IPMOD-45WPL-3M	7
IPMOD-45WPL-5M	7
IPMODM-45WPL-1M	7
IPMODM-45WPL-3M	7
IPMODM-45WPL-5M	7
IPMOD-45WPWP-1M	8
IPMOD-45WPWP-3M	8
IPMOD-45WPWP-5M	8
IPMODM-45WPWP-1M	8
IPMODM-45WPWP-3M	8
IPMODM-45WPWP-5M	8
IPMOD-45WM-FT	9
IPMODM-45WM-FT	9
IPMOD-45WJP-1M	10
IPMOD-45WJP-3M	10
IPMOD-45WJP-5M	10
IPMOD-45WJL-1M	10
IPMOD-45WJL-3M	10
IPMOD-45WJL-5M	10

All RJ45 Series P/Ns	Catalog Page
IPMOD-45WJWP-1M	11
IPMOD-45WJWP-3M	11
IPMOD-45WJWP-5M	11
IPMOD-45FSP	12
IPMODM-45FSP	12
IPMOD-45FSBHD	13
IPMODM-45FSBHD	13
IPMOD-45FSLP	14
IPMOD-45FSLP-1M	14
IPMOD-45FSLP-3M	14
IPMOD-45FSLP-5M	14
IPMODM-45FSLP	14
IPMODM-45FSLP-1M	14
IPMODM-45FSLP-3M	14
IPMODM-45FSLP-5M	14
IPMOD-45FSL	15
IPMOD-45FSL-1M	15
IPMOD-45FSL-3M	15
IPMOD-45FSL-5M	15
IPMODM-45FSL	15
IPMODM-45FSL-1M	15
IPMODM-45FSL-3M	15
IPMODM-45FSL-5M	15
IPMOD-45FSWBHD	16
IPCAP-1316	17
IPCAPM-1316	17

All RJ45 Series P/Ns	Catalog Page
IPGSK-1316	18
IPNT-1316	18







European Headquarters & Production Facility, Southampton, UK



Production Facility, Zhuhai, China



North American Production Facility, South Bend, IN



FilConn, Chandler, AZ



PEI-Genesis has sales offices throughout the Americas, Europe and Asia. Visit www.peigenesis.com, call +1 800.675.1214 (North America), +44 (0) 23 8062 1260 (Europe), +86 756 7683 088 (Asia), +1 631.475.5050 (Rest of World), or email: sales@peigenesis.com.

www.peigenesis.com | www.peigenesis.cn

