



RESISTANCE * +25°C = 10,000 Ω \pm 1%
 RESISTANCE/TEMPERATURE CURVE = "J"
 TEMPERATURE COEFFICIENT * +25°C = -4.4%/°C NOMINAL
 BETA "B" (0 TO +50°C) = 3,892°K NOMINAL
 MAXIMUM TEMPERATURE RATING = +105°C

LEAD WIRE: 24 AWG, STRANDED CONDUCTOR,
 TWO CONDUCTOR, PVC INSULATED ZIPCORD

MOISTURE RESISTANT PROBE ASSEMBLY

SEE MANUFACTURING SPECIFICATION (LAYER 1)

REV	RELEASE TO PRODUCTION	DATE	04/02/10	APP	DD
	REVISION RECORD				

SCALE	NONE	U.S. SENSOR CORP.
DRAWN BY	DAN DANXERS	1832 W. COLLINS AVE.
DATE	04/02/10	ORANGE, CA. 92867
REV.	NONE	714-639-1000 www.ussensor.com
LAYER	0 OF 2	NTC THERMISTOR PROBE
		P/N USP10979

- \pm 1% Tolerance
- 105°C Max Temp
- Moisture Resistant
- PVC Insulated Zip Cord Lead Wire
- 0.250" Diameter Stainless Steel Flanged Housing